

Plug - QP 1,5/ 1 - 3051108

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Plug, Connection method: Quick connection, Number of positions: 1, Cross section: 0.25 mm² - 1.5 mm², AWG: 24 - 16, Width: 5.2 mm, Height: 40 mm, Color: gray

Illustration shows the product
version QP 1,5/ 6

Product Features

- ✓ The conductor is connected using the familiar IDC connection with no stripping, therefore saving time
- ✓ Tested for railway applications
- ✓ Just like the basic terminal blocks, the plugs also offer the right connection technology for every application
- ✓ The QP 1,5/... fast connector plug is designed for the connection of solid and stranded conductors

Key commercial data

package_quantity	50
GTIN	4046356082457

Technical data

General

Number of levels	1
Number of connections	1
Color	gray
Insulating material	PA
Inflammability class according to UL 94	V0
Area of application	Railway industry
Area of application	Mechanical engineering
Area of application	Plant engineering

General

Maximum load current	17.5 A (with 1.5 mm ² conductor cross section)
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 61984
Nominal current I _N	17.5 A
Nominal voltage U _N	500 V
Number of positions	1

Plug - QP 1,5/ 1 - 3051108

Technical data

Dimensions

Width	5.2 mm
Length	20 mm
Height	40 mm

Connection data

Conductor cross section solid min.	0.25 mm ²
Conductor cross section solid max.	1.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	16
Conductor cross section stranded min.	0.25 mm ²
Conductor cross section stranded max.	1.5 mm ²
Min. AWG conductor cross section, stranded	24
Max. AWG conductor cross section, stranded	16
Connection method	Quick connection
Material wire insulation	PVC / PE
Structure of individual litz in acc. with VDE 0295 / smallest wire diameter	VDE 0295 Cl.1-5

classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27141120

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC002021
ETIM 5.0	EC002021

UNSPSC

UNSPSC 6.01	30211802
UNSPSC 7.0901	39121402
UNSPSC 11	39121402
UNSPSC 12.01	39121402
UNSPSC 13.2	39121402

Plug - QP 1,5/ 1 - 3051108

approvals

CSA / UL Recognized / cUL Recognized / GL / cULus Recognized /

Approval details

CSA 			
Usegroups	B	C	D
Nominal voltage UN	300 V	300 V	600 V
Nominal current IN	10 A	10 A	5 A
mm²/AWG/kcmil	24-16	24-16	24-16

UL Recognized 				
Usegroups	B	C	D	
Nominal voltage UN	300 V	300 V	600 V	600 V
Nominal current IN	10 A	10 A	5 A	10 A
mm²/AWG/kcmil	24-16	24-16	24-16	24-16

cUL Recognized 				
Usegroups	B	C	D	
Nominal voltage UN	300 V	300 V	600 V	600 V
Nominal current IN	10 A	10 A	5 A	10 A
mm²/AWG/kcmil	24-12	24-12	24-12	24-12

GL

cULus Recognized 				
--	--	--	--	--

accessories

Screwdriver tools

Plug - QP 1,5/ 1 - 3051108

accessories

SZF 1-0,6X3,5 - 1204517



Test plug terminal block

RPS - 0201647



MPS-MT - 0201744



PS-5 - 3030983



PS-5/2,3MM RD - 3038723



Insulating sleeve

Plug - QP 1,5/ 1 - 3051108

accessories

MPS-IH WH - 0201663



MPS-IH RD - 0201676



MPS-IH BU - 0201689



MPS-IH YE - 0201692



MPS-IH GN - 0201702



MPS-IH GY - 0201728



Plug - QP 1,5/ 1 - 3051108

accessories

MPS-IH BK - 0201731



End cover

DP PS-5 - 3036725



Drawings

Circuit diagram



© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>