Plug - UP 4/ 3 - 3060131

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://download.phoenixcontact.com)



Plug, Connection method: Screw connection, Number of positions: 3, Cross section: 0.14 mm² - 6 mm², AWG: 24 - 10, Width: 18.6 mm, Height: 41.2 mm, Color: gray

Product Features

- Screw actuation from the side
- Conductor connection from above
- The plug design enables space-saving potential distribution by using four-conductor terminal blocks with two slots

Key commercial data

package_quantity	50
GTIN	4046356090308

Technical data

General

Number of levels	1
Number of connections	1
Color	gray
Insulating material	PA
Inflammability class according to UL 94	V0

General

Maximum load current	32 A (with 6 mm² conductor cross section)
Rated surge voltage	8 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 61984
Nominal current I_N	32 A
Nominal voltage U_N	800 V
Number of positions	3

Dimensions

Width	18.6 mm
Length	21 mm
Height	41.2 mm

Plug - UP 4/ 3 - 3060131

Technical data

Connection data

Conductor cross section solid min.	0.14 mm²
Conductor cross section solid max.	6 mm²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	10
Conductor cross section stranded min.	0.14 mm²
Conductor cross section stranded max.	6 mm²
Min. AWG conductor cross section, stranded	24
Max. AWG conductor cross section, stranded	10
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.14 mm²
Conductor cross section stranded, with ferrule without plastic sleeve max.	4 mm²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.14 mm²
Conductor cross section stranded, with ferrule with plastic sleeve max.	4 mm²
2 conductors with same cross section, solid min.	0.14 mm²
2 conductors with same cross section, solid max.	1.5 mm²
2 conductors with same cross section, stranded min.	0.14 mm²
2 conductors with same cross section, stranded max.	1.5 mm²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.5 mm²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	1.5 mm²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	0.14 mm²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	1.5 mm²
Connection method	Screw connection
Stripping length	9 mm
Internal cylindrical gage	A4
Screw thread	M3
Tightening torque, min	0.6 Nm
Tightening torque max	0.8 Nm

classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120

Plug - UP 4/ 3 - 3060131

classifications

eCl@ss

eCl@ss 8.0	27141120

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC002021
ETIM 5.0	EC002021

UNSPSC

UNSPSC 6.01	30211802
UNSPSC 7.0901	39121402
UNSPSC 11	39121402
UNSPSC 12.01	39121402
UNSPSC 13.2	39121402

approvals

UL Recognized / cUL Recognized / cULus Recognized /

Approval details

UL Recognized

Usegroups	**B**	**C**
Nominal voltage UN	600 V	600 V
Nominal current IN	30 A	30 A
mm²/AWG/kcmil	26-10	26-10

cUL Recognized

Usegroups	**B**	**C**
Nominal voltage UN	600 V	600 V
Nominal current IN	30 A	30 A
mm²/AWG/kcmil	26-10	26-10

cULus Recognized

Plug - UP 4/ 3 - 3060131

accessories

Mounting material

PRZ - 3040614



PR - 3040559



PR/2 - 3040630



Strain relief

PZ/2 - 3040627



Shield connection

PSH 3- 6 - 3040591



Plug - UP 4/ 3 - 3060131

accessories

PSH 5-10 - 3040601



Screwdriver tools

SZS 0,6X3,5 - 1205053



End cover

DF-UP 4 - 3060348



Terminal marking

ZBF 8:UNBEDRUCKT - 0808781



UC-TMF 8 - 0818137



Plug - UP 4/ 3 - 3060131

accessories

UCT-TMF 8 - 0828748



Labeled terminal marker

ZBF 8 CUS - 0825030



UC-TMF 8 CUS - 0824654



UCT-TMF 8 CUS - 0829672



Test plug terminal block

MPS-MT - 0201744



Insulating sleeve

Plug - UP 4/ 3 - 3060131

accessories

MPS-IH WH - 0201663



MPS-IH RD - 0201676



MPS-IH BU - 0201689



MPS-IH YE - 0201692



MPS-IH GN - 0201702



MPS-IH GY - 0201728



Plug - UP 4/ 3 - 3060131

accessories

MPS-IH BK - 0201731



Drawings

Circuit diagram



© Phoenix Contact 2013 - all rights reserved
http://www.phoenixcontact.com