

Feed-through terminal block - STU 10/ 4X2,5 BU - 3033142

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Feed-through terminal block, Connection method: Screw connection, Cross section: 0.5 mm² - 16 mm², AWG: 20 - 6, Width: 10.3 mm, Color: blue, Mounting type: NS 35/7,5, NS 35/15

Product Features

- ✓ The STU 10/4x2,5 spring-cage hybrid terminal block is a space-saving potential distributor that distributes a 10 mm² supply line to four 2.5 mm² connections
- ✓ Supplied using a 10 mm² screw connection
- ✓ The double bridge shaft supports further potential distributions
- ✓ Can be consistently bridged to standard terminal blocks in the ST spring-cage terminal block series
- ✓ The system-internal distribution is via four spring-cage connections with a nominal cross section of 2.5 mm²

Key commercial data

package_quantity	50
GTIN	4046356148023

Technical data

General

Number of levels	1
Number of connections	1
Color	blue
Insulating material	PA
Inflammability class according to UL 94	V0

General

Rated surge voltage	8 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 60947-7-1
Nominal current I _N	55 A
Nominal voltage U _N	800 V
Open side panel	ja

Dimensions

Width	10.3 mm
Length	68 mm

Feed-through terminal block - STU 10/ 4X2,5 BU - 3033142

Technical data

Dimensions

Height NS 35/7,5	48.3 mm
Height NS 35/15	55.8 mm
End cover width	2.2 mm

Connection data

Connection method	Screw connection
Stripping length	10 mm
Internal cylindrical gage	A6
Tightening torque, min	1.5 Nm
Tightening torque max	1.8 Nm
Conductor cross section solid min.	0.5 mm ²
Conductor cross section solid max.	16 mm ²
Conductor cross section stranded min.	0.5 mm ²
Conductor cross section stranded max.	16 mm ²
Conductor cross section AWG/kcmil min.	20
Conductor cross section AWG/kcmil max	6
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.5 mm ²
Value	0.5 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	10 mm ²
Value	10 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.5 mm ²
Value	0.5 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	10 mm ²
Value	10 mm ²
2 conductors with same cross section, solid min.	0.5 mm ²
2 conductors with same cross section, solid max.	4 mm ²
2 conductors with same cross section, stranded min.	0.5 mm ²
2 conductors with same cross section, stranded max.	4 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	0.5 mm ²
Value	0.5 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	2.5 mm ²
Value	2.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.5 mm ²
Value	0.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	6 mm ²
Value	6 mm ²

Feed-through terminal block - STU 10/ 4X2,5 BU - 3033142

Technical data

Connection data

Connection method	Spring-cage connection
Stripping length	10 mm
Conductor cross section solid min.	0.08 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section AWG/kcmil min.	28
Conductor cross section AWG/kcmil max	12
Conductor cross section stranded min.	0.08 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.14 mm ²
Value	0.14 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	2.5 mm ²
Value	2.5 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.14 mm ²
Value	0.14 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	2.5 mm ²
Value	2.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	0.5 mm ²
Value	0.5 mm ²

classifications

eCl@ss

eCl@ss 4.0	27141121
eCl@ss 4.1	27141121
eCl@ss 5.0	27141120
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27141120

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC000897
ETIM 5.0	EC000897

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410

Feed-through terminal block - STU 10/ 4X2,5 BU - 3033142

classifications

UNSPSC

UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

approvals

UL Recognized / cUL Recognized / GOST / GOST / cULus Recognized /

Approval details

UL Recognized 		
Usegroups	B	C
Nominal voltage UN	600 V	600 V
Nominal current IN	50 A	50 A
mm ² /AWG/kcmil	20-8	20-8

cUL Recognized 		
Usegroups	B	C
Nominal voltage UN	600 V	600 V
Nominal current IN	50 A	50 A
mm ² /AWG/kcmil	20-8	20-8

GOST 



cULus Recognized 

accessories

End cover

Feed-through terminal block - STU 10/ 4X2,5 BU - 3033142

accessories

D-STU 10/ 4X2,5 - 3033197



DP PS-5 - 3036725



Screwdriver tools

SZS 1,0X4,0 VDE - 1205066



SZF 2-0,8X4,0 - 1204520



SZF 1-0,6X3,5 - 1204517



Labeled terminal marker

Feed-through terminal block - STU 10/ 4X2,5 BU - 3033142

accessories

WST 2,5 - 3030941



ZB 5 CUS - 0824962



UC-TM 5 CUS - 0824581



UCT-TM 5 CUS - 0829595



ZBF 5 CUS - 0825025



UC-TMF 5 CUS - 0824638



Feed-through terminal block - STU 10/ 4X2,5 BU - 3033142

accessories

UCT-TMF 5 CUS - 0829658



ZB 10 CUS - 0824941



UC-TM 10 CUS - 0824605



UCT-TM 10 CUS - 0829623



ZBF10 CUS - 0825031



Feed-through terminal block - STU 10/ 4X2,5 BU - 3033142

accessories

UC-TMF 10 CUS - 0824662



UCT-TMF 10 CUS - 0829679



Warning label printed

WS UT 10 - 3047361



Pick-off terminal block

AGK 4-UT 10 - 3047112



Bridge

RB ST (2,5/4)-1,5 - 3038943



Feed-through terminal block - STU 10/ 4X2,5 BU - 3033142

accessories

FBS 2-5 - 3030161



FBS 3-5 - 3030174



FBS 4-5 - 3030187



FBS 5-5 - 3030190



FBS 10-5 - 3030213



FBS 20-5 - 3030226



Feed-through terminal block - STU 10/ 4X2,5 BU - 3033142

accessories

Documentation

ST-IL - 3039900



Mounting rail

NS 35/ 7,5 PERF 2000MM - 0801733



NS 35/ 7,5 UNPERF 2000MM - 0801681



NS 35/ 7,5 WH PERF 2000MM - 1204119



NS 35/ 7,5 WH UNPERF 2000MM - 1204122



Feed-through terminal block - STU 10/ 4X2,5 BU - 3033142

accessories

NS 35/ 7,5 AL UNPERF 2000MM - 0801704



NS 35/ 7,5 ZN PERF 2000MM - 1206421



NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



NS 35/ 7,5 CU UNPERF 2000MM - 0801762



NS 35/ 7,5 CAP - 1206560



NS 35/15 PERF 2000MM - 1201730



Feed-through terminal block - STU 10/ 4X2,5 BU - 3033142

accessories

NS 35/15 UNPERF 2000MM - 1201714



NS 35/15 WH PERF 2000MM - 0806602



NS 35/15 WH UNPERF 2000MM - 1204135



NS 35/15 AL UNPERF 2000MM - 1201756



NS 35/15 ZN PERF 2000MM - 1206599



Feed-through terminal block - STU 10/ 4X2,5 BU - 3033142

accessories

NS 35/15 ZN UNPERF 2000MM - 1206586



NS 35/15 CU UNPERF 2000MM - 1201895



NS 35/15 CAP - 1206573



NS 35/15-2,3 UNPERF 2000MM - 1201798



Terminal marking

ZB 5 :UNBEDRUCKT - 1050004



Feed-through terminal block - STU 10/ 4X2,5 BU - 3033142

accessories

UC-TM 5 - 0818108



UCT-TM 5 - 0828734



ZBF 5:UNBEDRUCKT - 0808642



UC-TMF 5 - 0818153



UCT-TMF 5 - 0828744



ZB 10:UNBEDRUCKT - 1053001



Feed-through terminal block - STU 10/ 4X2,5 BU - 3033142

accessories

UC-TM 10 - 0818069



UCT-TM 10 - 0829142



ZBF10:UNBEDRUCKT - 0809997



UC-TMF 10 - 0818124



UCT-TMF 10 - 0829204



Test plug terminal block

Feed-through terminal block - STU 10/ 4X2,5 BU - 3033142

accessories

MPS-MT - 0201744



PS-5 - 3030983



PS-5/2,3MM RD - 3038723



PAI-4-FIX-5/6 BU - 3035975



PAI-4-FIX-5/6 OG - 3035974



PAI-4-FIX-5/6 YE - 3035977



Feed-through terminal block - STU 10/ 4X2,5 BU - 3033142

accessories

PAI-4-FIX-5/6 RD - 3035976



PAI-4-FIX-5/6 GN - 3035978



PAI-4-FIX-5/6 BK - 3035980



PAI-4-FIX-5/6 GY - 3035982



PAI-4-FIX-5/6 VT - 3035979



Feed-through terminal block - STU 10/ 4X2,5 BU - 3033142

accessories

PAI-4-FIX-5/6 BN - 3035981



Insulating sleeve

MPS-IH WH - 0201663



MPS-IH RD - 0201676



MPS-IH BU - 0201689



MPS-IH YE - 0201692



Feed-through terminal block - STU 10/ 4X2,5 BU - 3033142

accessories

MPS-IH GN - 0201702



MPS-IH GY - 0201728



MPS-IH BK - 0201731



ISH 2,5/0,2 - 3002843



ISH 2,5/0,5 - 3002856



ISH 2,5/1,0 - 3002869



Feed-through terminal block - STU 10/ 4X2,5 BU - 3033142

accessories

End block

CLIPFIX 35 - 3022218



CLIPFIX 35-5 - 3022276



E/NS 35 N - 0800886



E/UK - 1201442



E/UK 1 - 1201413



Drawings

Feed-through terminal block - STU 10/ 4X2,5 BU - 3033142

Circuit diagram



© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>