

Component terminal block - UT 2,5-MTD-DIO/R-L - 3064140

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Component terminal block, Connection method: Screw connection, Cross section: 0.14 mm² - 4 mm², AWG: 26 - 12, Width: 5.2 mm, Color: gray, Mounting type: NS 35/7,5, NS 35/15

Product Features

- ✓ The component terminal blocks can be used to perform a wide range of switching tasks
- ✓ Versions with 1N 4007 diodes are available with conducting direction from left to right or from right to left

Key commercial data

package_quantity	50
GTIN	4046356285933

Technical data

General

Note	The max. current is determined by the diode. Installed: Diode 1N 4007, reverse voltage: 1300 V, maximum continuous current: 0.5 A.
Number of levels	1
Number of connections	2
Color	gray
Insulating material	PA
Inflammability class according to UL 94	V0

General

Maximum load current	0.5 A
Rated surge voltage	8 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Nominal current I _N	0.5 A
Nominal voltage U _N	800 V
Open side panel	ja

Dimensions

Width	5.2 mm
Length	57.8 mm
Height NS 35/7,5	47.5 mm

Component terminal block - UT 2,5-MTD-DIO/R-L - 3064140

Technical data

Dimensions

Height NS 35/15	55 mm
-----------------	-------

Connection data

Conductor cross section solid min.	0.14 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section stranded min.	0.14 mm ²
Conductor cross section stranded max.	4 mm ²
Conductor cross section AWG/kcmil min.	26
Conductor cross section AWG/kcmil max	12
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.14 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	2.5 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.14 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	2.5 mm ²
2 conductors with same cross section, solid min.	0.14 mm ²
2 conductors with same cross section, solid max.	1.5 mm ²
2 conductors with same cross section, stranded min.	0.14 mm ²
2 conductors with same cross section, stranded max.	1.5 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	0.14 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	1.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	1.5 mm ²
Connection method	Screw connection
Stripping length	9 mm
Internal cylindrical gage	A3
Screw thread	M3
Tightening torque, min	0.5 Nm
Tightening torque max	0.6 Nm

classifications

eCl@ss

eCl@ss 4.0	27141117
eCl@ss 4.1	27141117
eCl@ss 5.0	27141126
eCl@ss 5.1	27141126
eCl@ss 6.0	27141126
eCl@ss 7.0	27141126

Component terminal block - UT 2,5-MTD-DIO/R-L - 3064140

classifications

eCl@ss

eCl@ss 8.0	27141126
------------	----------

ETIM

ETIM 2.0	EC000902
ETIM 3.0	EC000902
ETIM 4.0	EC000902
ETIM 5.0	EC000903

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

approvals

UL Recognized / cUL Recognized / CSA / cULus Recognized /

Approval details

UL Recognized 		
Usegroups	B	C
Nominal voltage UN	600 V	600 V
Nominal current IN	0.5 A	0.5 A
mm²/AWG/kcmil	26-12	26-12


cUL Recognized 			
Usegroups	B	C	D
Nominal voltage UN	600 V	600 V	600 V
Nominal current IN	0.5 A	0.5 A	0.5 A
mm²/AWG/kcmil	26-12	26-12	26-12

CSA 		
Usegroups	B	C
Nominal voltage UN	600 V	600 V
Nominal current IN	0.5 A	0.5 A

Component terminal block - UT 2,5-MTD-DIO/R-L - 3064140

approvals

Usegroups	B	C
mm²/AWG/kcmil	26-12	26-12



accessories

End cover

D-UT 2,5/4-TWIN - 3047141



DP PS-5 - 3036725



Partition plate

ATP-UT-TWIN - 3047183



Screwdriver tools

SZS 0,6X3,5 - 1205053



Component terminal block - UT 2,5-MTD-DIO/R-L - 3064140

accessories

Marker pen

X-PEN 0,35 - 0811228



Bridge

FBS 2-5 - 3030161



FBS 3-5 - 3030174



FBS 4-5 - 3030187



FBS 5-5 - 3030190



Component terminal block - UT 2,5-MTD-DIO/R-L - 3064140

accessories

FBS 10-5 - 3030213



FBS 20-5 - 3030226



FBS 50-5 - 3038930



Mounting rail

NS 35/ 7,5 PERF 2000MM - 0801733



NS 35/ 7,5 UNPERF 2000MM - 0801681



Component terminal block - UT 2,5-MTD-DIO/R-L - 3064140

accessories

NS 35/ 7,5 WH PERF 2000MM - 1204119



NS 35/ 7,5 WH UNPERF 2000MM - 1204122



NS 35/ 7,5 AL UNPERF 2000MM - 0801704



NS 35/ 7,5 ZN PERF 2000MM - 1206421



NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



NS 35/ 7,5 CU UNPERF 2000MM - 0801762



Component terminal block - UT 2,5-MTD-DIO/R-L - 3064140

accessories

NS 35/ 7,5 CAP - 1206560



NS 35/15 PERF 2000MM - 1201730



NS 35/15 UNPERF 2000MM - 1201714



NS 35/15 WH PERF 2000MM - 0806602



NS 35/15 WH UNPERF 2000MM - 1204135



Component terminal block - UT 2,5-MTD-DIO/R-L - 3064140

accessories

NS 35/15 AL UNPERF 2000MM - 1201756



NS 35/15 ZN PERF 2000MM - 1206599



NS 35/15 ZN UNPERF 2000MM - 1206586



NS 35/15 CU UNPERF 2000MM - 1201895



NS 35/15 CAP - 1206573



NS 35/15-2,3 UNPERF 2000MM - 1201798



Component terminal block - UT 2,5-MTD-DIO/R-L - 3064140

accessories

Terminal marking

ZB 5 :UNBEDRUCKT - 1050004



UC-TM 5 - 0818108



UCT-TM 5 - 0828734



Labeled terminal marker

ZB 5 CUS - 0824962



UC-TM 5 CUS - 0824581



Component terminal block - UT 2,5-MTD-DIO/R-L - 3064140

accessories

UCT-TM 5 CUS - 0829595



Test plug terminal block

MPS-MT - 0201744



PAI-4-N GY - 3032871



PS-5 - 3030983



PS-5/2,3MM RD - 3038723



Insulating sleeve

Component terminal block - UT 2,5-MTD-DIO/R-L - 3064140

accessories

MPS-IH WH - 0201663



MPS-IH RD - 0201676



MPS-IH BU - 0201689



MPS-IH YE - 0201692



MPS-IH GN - 0201702



MPS-IH GY - 0201728



Component terminal block - UT 2,5-MTD-DIO/R-L - 3064140

accessories

MPS-IH BK - 0201731



End block

CLIPFIX 35 - 3022218



CLIPFIX 35-5 - 3022276



E/NS 35 N - 0800886



Drawings

Circuit diagram



