

## Feed-through terminal block - UT 4-TG-P/P BU - 3073296

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Feed-through terminal block, Connection type: Screw connection, Cross section: 0.14 mm<sup>2</sup> - 6 mm<sup>2</sup>, AWG: 26 - 10, Nominal current: 20 A, Nominal voltage: 500 V, Length: 57.8 mm, Width: 6.2 mm, Color: blue, Assembly: NS 35/7,5, NS 35/15

### Key commercial data

|                  |               |
|------------------|---------------|
| package_quantity | 50            |
| GTIN             | 4046356334907 |

### Technical data

#### General

|                                         |                                                      |
|-----------------------------------------|------------------------------------------------------|
| Note                                    | Current and voltage are determined by the plug used. |
| Number of levels                        | 1                                                    |
| Number of connections                   | 2                                                    |
| Color                                   | blue                                                 |
| Insulating material                     | PA                                                   |
| Inflammability class according to UL 94 | V0                                                   |

#### General

|                                  |               |
|----------------------------------|---------------|
| Rated surge voltage              | 6 kV          |
| Pollution degree                 | 3             |
| Surge voltage category           | III           |
| Insulating material group        | I             |
| Connection in acc. with standard | IEC 60947-7-1 |
| Nominal current I <sub>N</sub>   | 20 A          |
| Nominal voltage U <sub>N</sub>   | 500 V         |
| Open side panel                  | nein          |

#### Dimensions

|                  |         |
|------------------|---------|
| Width            | 6.2 mm  |
| Length           | 57.8 mm |
| Height NS 35/7,5 | 47.5 mm |
| Height NS 35/15  | 55 mm   |

#### Connection data

|                                    |                      |
|------------------------------------|----------------------|
| Conductor cross section solid min. | 0.14 mm <sup>2</sup> |
| Conductor cross section solid max. | 6 mm <sup>2</sup>    |

# Feed-through terminal block - UT 4-TG-P/P BU - 3073296

## Technical data

### Connection data

|                                                                                         |                      |
|-----------------------------------------------------------------------------------------|----------------------|
| Conductor cross section AWG/kcmil min.                                                  | 26                   |
| Conductor cross section AWG/kcmil max                                                   | 10                   |
| Conductor cross section stranded min.                                                   | 0.14 mm <sup>2</sup> |
| Conductor cross section stranded max.                                                   | 6 mm <sup>2</sup>    |
| Min. AWG conductor cross section, stranded                                              | 26                   |
| Max. AWG conductor cross section, stranded                                              | 10                   |
| Conductor cross section stranded, with ferrule without plastic sleeve min.              | 0.14 mm <sup>2</sup> |
| Conductor cross section stranded, with ferrule without plastic sleeve max.              | 4 mm <sup>2</sup>    |
| Conductor cross section stranded, with ferrule with plastic sleeve min.                 | 0.14 mm <sup>2</sup> |
| Conductor cross section stranded, with ferrule with plastic sleeve max.                 | 4 mm <sup>2</sup>    |
| 2 conductors with same cross section, solid min.                                        | 0.14 mm <sup>2</sup> |
| 2 conductors with same cross section, solid max.                                        | 1.5 mm <sup>2</sup>  |
| 2 conductors with same cross section, stranded min.                                     | 0.14 mm <sup>2</sup> |
| 2 conductors with same cross section, stranded max.                                     | 1.5 mm <sup>2</sup>  |
| 2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min. | 0.5 mm <sup>2</sup>  |
| 2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max. | 2.5 mm <sup>2</sup>  |
| 2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.   | 0.14 mm <sup>2</sup> |
| 2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.   | 1.5 mm <sup>2</sup>  |
| Connection method                                                                       | Screw connection     |
| Stripping length                                                                        | 9 mm                 |
| Internal cylindrical gage                                                               | A4                   |
| Screw thread                                                                            | M3                   |
| Tightening torque, min                                                                  | 0.6 Nm               |
| Tightening torque max                                                                   | 0.8 Nm               |

## classifications

### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 27141199 |
| eCl@ss 4.1 | 27141199 |
| eCl@ss 5.0 | 27141145 |
| eCl@ss 5.1 | 27141145 |
| eCl@ss 6.0 | 27141120 |
| eCl@ss 7.0 | 27141120 |
| eCl@ss 8.0 | 27141120 |

### ETIM

# Feed-through terminal block - UT 4-TG-P/P BU - 3073296

## classifications

### ETIM

|                 |          |
|-----------------|----------|
| <b>ETIM 2.0</b> | EC000886 |
| <b>ETIM 3.0</b> | EC000886 |
| <b>ETIM 4.0</b> | EC000897 |
| <b>ETIM 5.0</b> | EC000897 |

### UNSPSC

|                      |          |
|----------------------|----------|
| <b>UNSPSC 6.01</b>   | 30211827 |
| <b>UNSPSC 7.0901</b> | 39121424 |
| <b>UNSPSC 11</b>     | 39121424 |
| <b>UNSPSC 12.01</b>  | 39121424 |
| <b>UNSPSC 13.2</b>   | 39121424 |

## approvals

CSA / UL Recognized / cUL Recognized / cULus Recognized /

### Approval details

| <b>CSA</b>  |       |       |
|------------------------------------------------------------------------------------------------|-------|-------|
| Usegroups                                                                                      | B     | C     |
| Nominal voltage UN                                                                             | 300 V | 300 V |
| Nominal current IN                                                                             | 16 A  | 16 A  |
| mm²/AWG/kcmil                                                                                  | 26-10 | 26-10 |

| <b>UL Recognized</b>  |       |
|----------------------------------------------------------------------------------------------------------|-------|
|                                                                                                          |       |
| Nominal voltage UN                                                                                       | 300 V |
| Nominal current IN                                                                                       | 16 A  |
| mm²/AWG/kcmil                                                                                            | 26-10 |

| <b>cUL Recognized</b>  |       |
|-----------------------------------------------------------------------------------------------------------|-------|
|                                                                                                           |       |
| Nominal voltage UN                                                                                        | 300 V |
| Nominal current IN                                                                                        | 16 A  |
| mm²/AWG/kcmil                                                                                             | 26-10 |

## Feed-through terminal block - UT 4-TG-P/P BU - 3073296

approvals

cULus Recognized  US

accessories

**Screwdriver tools**

SZS 0,6X3,5 - 1205053



---

**Bridge**

FBS 2-6 - 3030336



---

FBS 3-6 - 3030242



---

FBS 4-6 - 3030255



## Feed-through terminal block - UT 4-TG-P/P BU - 3073296

### accessories

FBS 5-6 - 3030349



FBS 10-6 - 3030271



FBS 20-6 - 3030365



FBS 50-6 - 3032224



### Mounting rail

NS 35/ 7,5 PERF 2000MM - 0801733



## Feed-through terminal block - UT 4-TG-P/P BU - 3073296

### accessories

NS 35/ 7,5 UNPERF 2000MM - 0801681



---

NS 35/ 7,5 WH PERF 2000MM - 1204119



---

NS 35/ 7,5 WH UNPERF 2000MM - 1204122



---

NS 35/ 7,5 AL UNPERF 2000MM - 0801704



---

NS 35/ 7,5 ZN PERF 2000MM - 1206421



---

NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



## Feed-through terminal block - UT 4-TG-P/P BU - 3073296

accessories

---

NS 35/ 7,5 CU UNPERF 2000MM - 0801762



NS 35/ 7,5 CAP - 1206560



NS 35/15 PERF 2000MM - 1201730



NS 35/15 UNPERF 2000MM - 1201714



NS 35/15 WH PERF 2000MM - 0806602



## Feed-through terminal block - UT 4-TG-P/P BU - 3073296

### accessories

NS 35/15 WH UNPERF 2000MM - 1204135



NS 35/15 AL UNPERF 2000MM - 1201756



NS 35/15 ZN PERF 2000MM - 1206599



NS 35/15 ZN UNPERF 2000MM - 1206586



NS 35/15 CU UNPERF 2000MM - 1201895



NS 35/15 CAP - 1206573



## Feed-through terminal block - UT 4-TG-P/P BU - 3073296

accessories

---

NS 35/15-2,3 UNPERF 2000MM - 1201798



---

### Test plug terminal block

MPS-MT - 0201744



---

PAI-4-FIX-5/6 BU - 3035975



---

PAI-4-FIX-5/6 OG - 3035974



---

PAI-4-FIX-5/6 YE - 3035977



## Feed-through terminal block - UT 4-TG-P/P BU - 3073296

### accessories

PAI-4-FIX-5/6 RD - 3035976



---

PAI-4-FIX-5/6 GN - 3035978



---

PAI-4-FIX-5/6 BK - 3035980



---

PAI-4-FIX-5/6 GY - 3035982



---

PAI-4-FIX-5/6 VT - 3035979



---

PAI-4-FIX-5/6 BN - 3035981



## Feed-through terminal block - UT 4-TG-P/P BU - 3073296

### accessories

---

PS-6 - 3030996



PS-6/2,3MM RD - 3038736



### Insulating sleeve

---

MPS-IH WH - 0201663



MPS-IH RD - 0201676



MPS-IH BU - 0201689



## Feed-through terminal block - UT 4-TG-P/P BU - 3073296

### accessories

MPS-IH YE - 0201692



MPS-IH GN - 0201702



MPS-IH GY - 0201728



MPS-IH BK - 0201731



### End cover

DP PS-6 - 3036738



### End block

## Feed-through terminal block - UT 4-TG-P/P BU - 3073296

### accessories

CLIPFIX 35 - 3022218



CLIPFIX 35-5 - 3022276



E/NS 35 N - 0800886



### Drawings

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>