Printed-circuit board connector - PC 16/ 6-STF-10,16 - 1967498

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://download.phoenixcontact.com)



The figure shows a 5-pos. version of the product

Plug component, Nominal current: 76 A, Rated voltage (III/2): 1000 V, Number of positions: 6, Pitch: 10.16 mm, Connection method: Screw connection, Color: green, Contact surface: Silver

Product Features

- Can be plugged into PC 6-16 headers and IPC 16 plugs
- High-capacity plugs with a current carrying capacity of 76 A and a connection capacity of 16 mm², stranded
- Unlimited 600 V UL approval
- Maximum contact reliability due to integrated double steel spring
- CP-PC RD coding profile

Key commercial data

package_quantity	50
GTIN	4017918939359

Technical data

Dimensions

Pitch	10.16 mm
Dimension a	50.8 mm

General

Range of articles	PC 16/..-STF
Insulating material group	I
Rated surge voltage (III/3)	8 kV
Rated surge voltage (III/2)	8 kV
Rated surge voltage (II/2)	6 kV
Rated voltage (III/3)	1000 V
Rated voltage (III/2)	1000 V
Rated voltage (II/2)	1000 V
Connection in acc. with standard	EN-VDE
Nominal current I_N	76 A
Nominal cross section	16 mm²
Maximum load current	76 A
Insulating material	PA
Inflammability class according to UL 94	V0

Printed-circuit board connector - PC 16/ 6-STF-10,16 - 1967498

Technical data

General

Internal cylindrical gage	A6
Stripping length	12 mm
Number of positions	6
Screw thread	M4
Tightening torque, min	1.7 Nm
Tightening torque max	1.8 Nm

Connection data

Conductor cross section solid min.	0.75 mm²
Conductor cross section solid max.	16 mm²
Conductor cross section stranded min.	0.75 mm²
Conductor cross section stranded max.	16 mm²
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.5 mm²
Conductor cross section stranded, with ferrule without plastic sleeve max.	16 mm² Only in connection with CRIMPFOX 16 S
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.5 mm²
Conductor cross section stranded, with ferrule with plastic sleeve max.	10 mm² Only in connection with CRIMPFOX 16 S
Conductor cross section AWG/kcmil min.	18
Conductor cross section AWG/kcmil max	6
2 conductors with same cross section, solid min.	0.75 mm²
2 conductors with same cross section, solid max.	6 mm²
2 conductors with same cross section, stranded min.	0.75 mm²
2 conductors with same cross section, stranded max.	6 mm²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	0.5 mm²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	4 mm²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.5 mm²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	6 mm²
Minimum AWG according to UL/CUL	20
Maximum AWG according to UL/CUL	6

classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260704

Printed-circuit board connector - PC 16/ 6-STF-10,16 - 1967498

classifications

eCl@ss

eCl@ss 7.0	27440402
eCl@ss 8.0	27440402

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002638
ETIM 5.0	EC002638

UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

approvals

UL Recognized / SEV / cUL Recognized / CCA / IECEE CB Scheme / GOST / GOST / cULus Recognized /

Approval details

UL Recognized

Usegroups	**B**	**C**
Nominal voltage UN	600 V	600 V
Nominal current IN	55 A	55 A
mm²/AWG/kcmil	20-6	20-6

SEV	
Nominal voltage UN	1000 V
Nominal current IN	76 A
mm²/AWG/kcmil	16

cUL Recognized

Usegroups	**B**	**C**
Nominal voltage UN	600 V	600 V
Nominal current IN	55 A	55 A
mm²/AWG/kcmil	20-6	20-6

Printed-circuit board connector - PC 16/ 6-STF-10,16 - 1967498

approvals

CCA	
Nominal voltage UN	1000 V
Nominal current IN	76 A
mm²/AWG/kcmil	

IECEE CB Scheme	
Nominal voltage UN	1000 V
Nominal current IN	76 A
mm²/AWG/kcmil	

GOST

cULus Recognized

accessories

Coding element


CP-PC RD - 1701967



Drawings


Printed-circuit board connector - PC 16/ 6-STF-10,16 - 1967498

Diagram



Derating curve for: PC 16/..-ST-10,16 with PC 6-16/..-G1-10,16


Diagram



Derating curve for: PC 16/..-ST-10,16 with DFK-PC 6-16/..-G-10,16

Printed-circuit board connector - PC 16/ 6-STF-10,16 - 1967498

Dimensioned drawing



The illustration shows the 3-pos. version

© Phoenix Contact 2013 - all rights reserved
http://www.phoenixcontact.com