


Base strip - MCV 0,5/ 4-G-2,5 - 1881574

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Header, Nominal current: 4 A, Rated voltage (III/2): 160 V, Number of positions: 4, Pitch: 2.5 mm, Color: green, Contact surface: Tin, Assembly: Soldering

The figure shows a 10-position version of the product

Product Features

- ✓ Low-profile pin strips with a compact MICRO pitch of 2.5 mm
- ✓ Plug-in direction parallel and vertical to the PCB
- ✓ Individual position coding by inserting coding profiles

Key commercial data

package_quantity	50
GTIN	4017918156817

Technical data

Dimensions

Length	8.1 mm
Pitch	2.5 mm
Dimension a	7.5 mm
Pin dimensions	0,8 x 0,8 mm
Hole diameter	1.2 mm

General

Range of articles	MCV 0,5/...-G
Insulating material group	I
Rated surge voltage (III/3)	1.5 kV
Rated surge voltage (III/2)	2.5 kV
Rated surge voltage (II/2)	2.5 kV
Rated voltage (III/3)	80 V
Rated voltage (III/2)	160 V
Rated voltage (II/2)	320 V
Connection in acc. with standard	EN-VDE
Nominal current I _N	4 A
Maximum load current	4 A
Insulating material	PA
Inflammability class according to UL 94	V0

Base strip - MCV 0,5/ 4-G-2,5 - 1881574

Technical data

General

Color	green
Number of positions	4

classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402
eCl@ss 8.0	27440402

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002637
ETIM 5.0	EC002637

UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

approvals

UL Recognized / VDE Gutachten mit Fertigungsüberwachung / cUL Recognized / GOST / IECEE CB Scheme / GOST / CCA / cULus Recognized /

Approval details

UL Recognized 	
Usegroups	B
Nominal voltage UN	125 V
Nominal current IN	4 A
mm²/AWG/kcmil	

Base strip - MCV 0,5/ 4-G-2,5 - 1881574

approvals

VDE Gutachten mit Fertigungsüberwachung 	
Nominal voltage UN	80 V
Nominal current IN	4 A
mm²/AWG/kcmil	

cUL Recognized 	
Usegroups	B
Nominal voltage UN	125 V
Nominal current IN	4 A
mm²/AWG/kcmil	

GOST 
--

IECEE CB Scheme 	
Nominal voltage UN	80 V
Nominal current IN	4 A
mm²/AWG/kcmil	



CCA	
Nominal voltage UN	80 V
Nominal current IN	4 A
mm²/AWG/kcmil	

cULus Recognized 	
--	--

Base strip - MCV 0,5/ 4-G-2,5 - 1881574

accessories

Coding element

CP-MC 0,5 - 1881435



Labeled terminal marker


SK 2,54/2,8:FORTL.ZAHLEN - 0804853



Drawings

Base strip - MCV 0,5/ 4-G-2,5 - 1881574

Drilling diagram




Diagram

Type: FK-MC 0,5/...-ST-2,5 with MCV 0,5/...-G-2,5

Base strip - MCV 0,5/ 4-G-2,5 - 1881574

Dimensioned drawing



© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>