

PCB terminal block - MKDSP 10HV/ 2-12,7 - 1929533

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



PCB terminal block, Nominal current: 76 A, Nom. voltage: 1000 V, Pitch: 12.7 mm, Number of positions: 2, Connection method: Screw connection, Mounting: Soldering, Conductor/PCB connection direction: 0 °, Color: green, The article can be aligned to create different nos. of positions!

Product Features

- ✓ Integrated test connection
- ✓ High-capacity PCB terminal blocks with screw connection up to 16 mm², stranded, and a current carrying capacity of 76 A
- ✓ Terminal block bases that can be mounted side by side to create any number of positions
- ✓ Individual adjustment of voltage requirements using RZ pitch spacers

Key commercial data

package_quantity	50
GTIN	4017918819651

Technical data

Dimensions

Length	22 mm
Pitch	12.7 mm
Dimension a	12.7 mm
Pin dimensions	1 x 0,9 mm
Hole diameter	1.5 mm

General

Range of articles	MKDSP 10HV
Insulating material group	I
Rated surge voltage (III/3)	8 kV
Rated surge voltage (III/2)	8 kV
Rated surge voltage (II/2)	6 kV
Rated voltage (III/3)	1000 V
Rated voltage (III/2)	1000 V
Rated voltage (II/2)	1000 V
Connection in acc. with standard	EN-VDE
Nominal current I _N	76 A
Nominal cross section	10 mm ²
Maximum load current	76 A (with 16 mm ² conductor cross section)
Insulating material	PA

PCB terminal block - MKDSP 10HV/ 2-12,7 - 1929533

Technical data

General

Solder pin surface	Sn
Inflammability class according to UL 94	V0
Internal cylindrical gage	B 6
Stripping length	10 mm
Number of positions	2
Screw thread	M4
Tightening torque, min	1.2 Nm
Tightening torque max	1.5 Nm

Connection data

Conductor cross section solid min.	0.5 mm ²
Conductor cross section solid max.	16 mm ²
Conductor cross section stranded min.	0.5 mm ²
Conductor cross section stranded max.	16 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.5 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	16 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.5 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	16 mm ²
Conductor cross section AWG/kcmil min.	20
Conductor cross section AWG/kcmil max	6
2 conductors with same cross section, solid min.	0.5 mm ²
2 conductors with same cross section, solid max.	4 mm ²
2 conductors with same cross section, stranded min.	0.5 mm ²
2 conductors with same cross section, stranded max.	4 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	0.5 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	2.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	6 mm ²
Minimum AWG according to UL/CUL	20
Maximum AWG according to UL/CUL	6

classifications

eCl@ss

eCl@ss 4.0	27141109
eCl@ss 4.1	27141109
eCl@ss 5.0	27141190

PCB terminal block - MKDSP 10HV/ 2-12,7 - 1929533

classifications

eCl@ss

eCl@ss 5.1	27141190
eCl@ss 6.0	27261101
eCl@ss 7.0	27440401
eCl@ss 8.0	27440401

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002643
ETIM 5.0	EC002643

UNSPSC

UNSPSC 6.01	30211801
UNSPSC 7.0901	39121432
UNSPSC 11	39121432
UNSPSC 12.01	39121432
UNSPSC 13.2	39121432

approvals

UL Recognized / SEV / cUL Recognized / GOST / CCA / IECCEB Scheme / GOST / cULus Recognized /

Approval details

UL Recognized 		
Usegroups	B	C
Nominal voltage UN	600 V	600 V
Nominal current IN	60 A	60 A
mm²/AWG/kcmil	20-6	20-6

SEV	
Nominal voltage UN	1000 V
Nominal current IN	
mm²/AWG/kcmil	16

cUL Recognized 		
Usegroups	B	C
Nominal voltage UN	600 V	600 V

PCB terminal block - MKDSP 10HV/ 2-12,7 - 1929533

approvals

Usegroups	B	C
Nominal current I _N	60 A	60 A
mm ² /AWG/kcmil	20-6	20-6

GOST 

CCA

IECEE CB Scheme 



cULus Recognized 

accessories

Test plug terminal block

RPS - 0201647



Screwdriver tools

SZS 0,6X3,5 - 1205053



Printed circuit board terminal

PCB terminal block - MKDSP 10HV/ 2-12,7 - 1929533

accessories

MKDSP 10HV/ 3-12,7 - 1929546



Terminal marking

SK 5,0 WH:REEL - 0805221



SK U/5,0 WH:UNBEDRUCKT - 0803922



Marker pen

B-STIFT - 1051993



Pitch spacer

RZ-MKDSP 10 HV-2,54 - 1929672



PCB terminal block - MKDSP 10HV/ 2-12,7 - 1929533


accessories

SK 10/5:SO - 0805179




Drawings

Drilling diagram



PCB terminal block - MKDSP 10HV/ 2-12,7 - 1929533

Dimensioned drawing



© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>