

Base strip - ICV 2,5/10-G-5,08 - 1786022

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Header, Nominal current: 12 A, Rated voltage (III/2): 320 V, Number of positions: 10, Pitch: 5.08 mm, Color: green, Contact surface: Tin, Assembly: Soldering

Product Features

- ☒ Pairs of guide rails can be used as a 90° board-to-board connection
- ☒ Combination with MSTB 2,5 headers for primary/secondary/PCB connection
- ☒ Use in shock-proof applications
- ☒ Clear separation of PCB inputs/outputs

Key commercial data

package_quantity	50
GTIN	4017918042172

Technical data

Dimensions

Length	10.2 mm
Pitch	5.08 mm
Dimension a	45.72 mm
Pin dimensions	1,2 x 0,5
Hole diameter	1.4 mm

General

Range of articles	ICV 2,5/..-G
Insulating material group	I
Rated surge voltage (III/3)	4 kV
Rated surge voltage (III/2)	4 kV
Rated surge voltage (II/2)	4 kV
Rated voltage (III/3)	320 V
Rated voltage (III/2)	320 V
Rated voltage (II/2)	630 V
Connection in acc. with standard	EN-VDE
Nominal current I _N	12 A
Maximum load current	12 A
Insulating material	PA
Inflammability class according to UL 94	V0

Base strip - ICV 2,5/10-G-5,08 - 1786022

Technical data

General

Color	green
Number of positions	10

classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402
eCl@ss 8.0	27440402

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002637
ETIM 5.0	EC002637

UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

approvals

CSA / UL Recognized / VDE Gutachten mit Fertigungsüberwachung / cUL Recognized / GOST / IECEE CB Scheme / GOST / CCA / cULus Recognized /

Approval details

		
Usegroups	B	D
Nominal voltage UN	300 V	300 V
Nominal current IN	10 A	10 A
mm²/AWG/kcmil		

Base strip - ICV 2,5/10-G-5,08 - 1786022

approvals

UL Recognized 		
Usegroups	B	D
Nominal voltage UN	250 V	300 V
Nominal current IN	12 A	10 A
mm²/AWG/kcmil		

VDE Gutachten mit Fertigungsüberwachung 	
Nominal voltage UN	250 V
Nominal current IN	12 A
mm²/AWG/kcmil	

cUL Recognized 		
Usegroups	B	D
Nominal voltage UN	250 V	300 V
Nominal current IN	12 A	10 A
mm²/AWG/kcmil		

GOST 
--

IECEE CB Scheme 	
Nominal voltage UN	250 V
Nominal current IN	12 A
mm²/AWG/kcmil	



CCA	
Nominal voltage UN	250 V

Base strip - ICV 2,5/10-G-5,08 - 1786022

approvals

Nominal current IN	12 A
mm²/AWG/kcmil	

cULus Recognized  US

accessories

Test plug terminal block

RPS - 0201647



MPS-MT - 0201744



Coding element

CP-MSTB - 1734634



accessories


FLRP/ICV 80 - 1808353



Base strip - ICV 2,5/10-G-5,08 - 1786022


Drawings

Drilling diagram



Base strip - ICV 2,5/10-G-5,08 - 1786022

Dimensioned drawing



© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>