

## PCB terminal block - MKDSO 2,5/4-6 SET KMGY - 2713751

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Set, consisting of orthogonal PCB terminal blocks for 6 x 4 positions (24-pos.), color: light gray

### Key commercial data

|                  |               |
|------------------|---------------|
| package_quantity | 1             |
| GTIN             | 4017918914479 |

### Technical data

#### Dimensions

|                |         |
|----------------|---------|
| Pitch          | 5 mm    |
| Pin dimensions | 0,8 x 1 |

#### General

|                                         |                     |
|-----------------------------------------|---------------------|
| Rated surge voltage (III/3)             | 4 kV                |
| Rated surge voltage (III/2)             | 4 kV                |
| Rated surge voltage (II/2)              | 4 kV                |
| Rated voltage (III/3)                   | 250 V               |
| Rated voltage (III/2)                   | 400 V               |
| Rated voltage (II/2)                    | 630 V               |
| Connection in acc. with standard        | EN-VDE              |
| Nominal current I <sub>N</sub>          | 24 A                |
| Nominal cross section                   | 2.5 mm <sup>2</sup> |
| Insulating material                     | PA                  |
| Inflammability class according to UL 94 | V0                  |
| Internal cylindrical gage               | A 2                 |
| Stripping length                        | 8 mm                |
| Number of positions                     | 4                   |
| Screw thread                            | M3                  |
| Tightening torque, min                  | 0.5 Nm              |
| Tightening torque max                   | 0.6 Nm              |

#### Connection data

|                                       |                      |
|---------------------------------------|----------------------|
| Conductor cross section solid min.    | 0.14 mm <sup>2</sup> |
| Conductor cross section solid max.    | 2.5 mm <sup>2</sup>  |
| Conductor cross section stranded min. | 0.14 mm <sup>2</sup> |

# PCB terminal block - MKDSO 2,5/4-6 SET KMGY - 2713751

## Technical data

### Connection data

|                                                                                         |                      |
|-----------------------------------------------------------------------------------------|----------------------|
| Conductor cross section stranded max.                                                   | 2.5 mm <sup>2</sup>  |
| Conductor cross section stranded, with ferrule without plastic sleeve min.              | 0.25 mm <sup>2</sup> |
| Conductor cross section stranded, with ferrule without plastic sleeve max.              | 2.5 mm <sup>2</sup>  |
| Conductor cross section stranded, with ferrule with plastic sleeve min.                 | 0.25 mm <sup>2</sup> |
| Conductor cross section stranded, with ferrule with plastic sleeve max.                 | 2.5 mm <sup>2</sup>  |
| Conductor cross section AWG/kcmil min.                                                  | 26                   |
| Conductor cross section AWG/kcmil max                                                   | 14                   |
| 2 conductors with same cross section, solid min.                                        | 0.14 mm <sup>2</sup> |
| 2 conductors with same cross section, solid max.                                        | 0.75 mm <sup>2</sup> |
| 2 conductors with same cross section, stranded min.                                     | 0.14 mm <sup>2</sup> |
| 2 conductors with same cross section, stranded max.                                     | 0.75 mm <sup>2</sup> |
| 2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.   | 0.25 mm <sup>2</sup> |
| 2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.   | 0.75 mm <sup>2</sup> |
| 2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min. | 0.5 mm <sup>2</sup>  |
| 2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max. | 1.5 mm <sup>2</sup>  |

## classifications

### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 27180401 |
| eCl@ss 4.1 | 27180401 |
| eCl@ss 5.0 | 27180506 |
| eCl@ss 5.1 | 27141190 |
| eCl@ss 6.0 | 27141190 |
| eCl@ss 7.0 | 27141190 |
| eCl@ss 8.0 | 27141190 |

### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC001031 |
| ETIM 3.0 | EC001031 |
| ETIM 4.0 | EC001031 |
| ETIM 5.0 | EC001031 |

### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 31261501 |
| UNSPSC 7.0901 | 31261501 |
| UNSPSC 11     | 31261501 |

# PCB terminal block - MKDSO 2,5/4-6 SET KMGY - 2713751

## classifications

### UNSPSC

|                     |          |
|---------------------|----------|
| <b>UNSPSC 12.01</b> | 31261501 |
| <b>UNSPSC 13.2</b>  | 31261501 |

## approvals

CSA / UL Recognized / VDE Gutachten mit Fertigungsüberwachung / cUL Recognized / CCA / IEC EE CB Scheme / GOST / cULus Recognized /

### Approval details

| CSA  |       |       |
|---------------------------------------------------------------------------------------|-------|-------|
| Usegroups                                                                             | B     | D     |
| Nominal voltage UN                                                                    | 300 V | 300 V |
| Nominal current IN                                                                    | 10 A  | 10 A  |
| mm <sup>2</sup> /AWG/kcmil                                                            | 28-12 | 28-12 |

| UL Recognized  |       |       |
|---------------------------------------------------------------------------------------------------|-------|-------|
| Usegroups                                                                                         | B     | D     |
| Nominal voltage UN                                                                                | 300 V | 300 V |
| Nominal current IN                                                                                | 20 A  | 10 A  |
| mm <sup>2</sup> /AWG/kcmil                                                                        | 30-12 | 30-12 |

|                                                                                                                             |         |
|-----------------------------------------------------------------------------------------------------------------------------|---------|
| VDE Gutachten mit Fertigungsüberwachung  |         |
| Nominal voltage UN                                                                                                          | 450 V   |
| Nominal current IN                                                                                                          | 24 A    |
| mm <sup>2</sup> /AWG/kcmil                                                                                                  | 0.2-2.5 |

| cUL Recognized  |       |       |
|----------------------------------------------------------------------------------------------------|-------|-------|
| Usegroups                                                                                          | B     | D     |
| Nominal voltage UN                                                                                 | 300 V | 300 V |
| Nominal current IN                                                                                 | 20 A  | 10 A  |
| mm <sup>2</sup> /AWG/kcmil                                                                         | 30-12 | 30-12 |

# PCB terminal block - MKDSO 2,5/4-6 SET KMGY - 2713751

## approvals

| CCA                |       |
|--------------------|-------|
|                    |       |
| Nominal voltage UN | 450 V |
| Nominal current IN | 24 A  |
| mm²/AWG/kcmil      | 2.5   |



| IECEE CB Scheme  |       |
|---------------------------------------------------------------------------------------------------|-------|
|                                                                                                   |       |
| Nominal voltage UN                                                                                | 450 V |
| Nominal current IN                                                                                | 24 A  |
| mm²/AWG/kcmil                                                                                     | 2.5   |

|                                                                                         |
|-----------------------------------------------------------------------------------------|
| GOST  |
|-----------------------------------------------------------------------------------------|

|                                                                                                         |
|---------------------------------------------------------------------------------------------------------|
| cULus Recognized  US |
|---------------------------------------------------------------------------------------------------------|

## Drawings



### Schematic diagram



### Pin assignment right

## PCB terminal block - MKDSO 2,5/4-6 SET KMGY - 2713751

Schematic diagram



Pin assignment left

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>