

Base strip - GMSTBVA 2,5/ 3-G BK - 1862849

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Header, Nominal current: 12 A, Rated voltage (III/2): 400 V, Number of positions: 3, Pitch: 7.5 mm, Color: Black, Contact surface: Tin, Assembly: Soldering

Key commercial data

package_quantity	50
GTIN	4017918266035

Technical data

Dimensions

Length	8.6 mm
Pitch	7.5 mm
Dimension a	15 mm
Pin dimensions	1 x 1 mm
Hole diameter	1.4 mm

General

Range of articles	GMSTBVA 2,5/...-G
Insulating material group	I
Rated surge voltage (III/3)	6 kV
Rated surge voltage (III/2)	6 kV
Rated surge voltage (II/2)	6 kV
Rated voltage (III/3)	400 V
Rated voltage (III/2)	400 V
Rated voltage (II/2)	1000 V
Connection in acc. with standard	EN-VDE
Nominal current I_N	12 A
Maximum load current	12 A
Insulating material	PA
Inflammability class according to UL 94	V0
Color	Black
Number of positions	3

Base strip - GMSTBVA 2,5/ 3-G BK - 1862849

classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402
eCl@ss 8.0	27440402

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002637

UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

approvals

CSA / UL Recognized / VDE Gutachten mit Fertigungsüberwachung / cUL Recognized / IECEx CB Scheme / GOST / GOST / CCA / cULus Recognized /

Approval details

CSA 		
Usegroups	B	D
Nominal voltage UN	300 V	300 V
Nominal current IN	10 A	10 A
mm²/AWG/kcmil		

UL Recognized 		
Usegroups	B	D
Nominal voltage UN	300 V	300 V
Nominal current IN	15 A	10 A
mm²/AWG/kcmil		

Base strip - GMSTBVA 2,5/ 3-G BK - 1862849

approvals

VDE Gutachten mit Fertigungsüberwachung 	
Nominal voltage UN	400 V
Nominal current IN	12 A
mm²/AWG/kcmil	

cUL Recognized 		
Usegroups	B	D
Nominal voltage UN	300 V	300 V
Nominal current IN	15 A	10 A
mm²/AWG/kcmil		

IECEE CB Scheme 	
Nominal voltage UN	400 V
Nominal current IN	12 A
mm²/AWG/kcmil	

GOST 
--



CCA	
Nominal voltage UN	400 V
Nominal current IN	12 A
mm²/AWG/kcmil	

cULus Recognized 	
--	--

Base strip - GMSTBVA 2,5/ 3-G BK - 1862849

accessories

Coding element

CR-MSTB - 1734401



Filler plug

MSTB-BL - 1755477



Labeled terminal marker

SK 7,5/3,8:FORTL.ZAHLEN - 0804455



Terminal marking

SK U/3,8 WH:UNBEDRUCKT - 0803906



Marker pen

Base strip - GMSTBVA 2,5/ 3-G BK - 1862849

accessories

B-STIFT - 1051993



accessories

SK 7,5/3,8:SO - 0805137



© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>