

## Accessories - MSTBC-MT 0,5-1,0 BA - 3190645

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Module female contact, is inserted into the MSTBC connector shell after the conductor has been crimped, for conductors from 0.5 - 1.0 mm<sup>2</sup>, ribbon contact

Supplied in tape form - please note the drawing.

### Key commercial data

|                         |               |
|-------------------------|---------------|
| <b>package_quantity</b> | 4000          |
| <b>GTIN</b>             | 4017918117436 |

### Technical data

#### General

|                                               |                                                       |
|-----------------------------------------------|-------------------------------------------------------|
| <b>Nominal current</b>                        | 12 A (with 1 mm <sup>2</sup> conductor cross section) |
| <b>Conductor cross section stranded min.</b>  | 0.5 mm <sup>2</sup>                                   |
| <b>Max. conductor cross section, stranded</b> | 1 mm <sup>2</sup>                                     |

#### Connection data

|                                             |                    |
|---------------------------------------------|--------------------|
| <b>Core diameter including insulation</b>   | 1.4 mm ... 2.31 mm |
| <b>Stripping length of individual wires</b> | 3.5 mm             |

#### Material data

|                                 |            |
|---------------------------------|------------|
| <b>Contact material</b>         | CuFe       |
| <b>Contact surface material</b> | Tin-plated |

### classifications

#### eCl@ss

|                   |          |
|-------------------|----------|
| <b>eCl@ss 4.0</b> | 272607xx |
| <b>eCl@ss 4.1</b> | 27260701 |
| <b>eCl@ss 5.0</b> | 27260701 |
| <b>eCl@ss 5.1</b> | 27260701 |
| <b>eCl@ss 6.0</b> | 27260704 |
| <b>eCl@ss 7.0</b> | 27449202 |
| <b>eCl@ss 8.0</b> | 27449202 |

#### ETIM

|                 |          |
|-----------------|----------|
| <b>ETIM 3.0</b> | EC001121 |
|-----------------|----------|

## Accessories - MSTBC-MT 0,5-1,0 BA - 3190645

### classifications

#### ETIM

|                 |          |
|-----------------|----------|
| <b>ETIM 4.0</b> | EC001121 |
| <b>ETIM 5.0</b> | EC002641 |

#### UNSPSC

|                      |          |
|----------------------|----------|
| <b>UNSPSC 6.01</b>   | 30211810 |
| <b>UNSPSC 7.0901</b> | 39121410 |
| <b>UNSPSC 11</b>     | 39121409 |
| <b>UNSPSC 12.01</b>  | 39121409 |
| <b>UNSPSC 13.2</b>   | 39121409 |

### approvals

GOST /


#### Approval details

|                                                                                                 |
|-------------------------------------------------------------------------------------------------|
|  <b>GOST</b> |
|-------------------------------------------------------------------------------------------------|

### Drawings

## Accessories - MSTBC-MT 0,5-1,0 BA - 3190645

Dimensioned drawing



© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>