

## Housing - MSTBHK 2,5/10-G - 1765085

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Plug component, Nominal current: 12 A, Rated voltage (III/2): 320 V, Number of positions: 10, Pitch: 5 mm, Connection method: Screw connection, Color: green, Contact surface: Tin, Assembly: DIN rail

The figure shows a 10-position version of the product

### Product Features

- ☒ Versions with and without threaded flange
- ☒ MSTBHK 2,5 with foot element for mounting on 15 x 5 mm DIN rails (NS 15) according to EN 60715-TH15

### Key commercial data

|                  |               |
|------------------|---------------|
| package_quantity | 50            |
| GTIN             | 4017918031770 |

### Technical data

#### Dimensions

|             |         |
|-------------|---------|
| Length      | 52.3 mm |
| Width       | 23.1 mm |
| Pitch       | 5 mm    |
| Dimension a | 45 mm   |

#### General

|                                         |                     |
|-----------------------------------------|---------------------|
| Range of articles                       | MSTBHK 2,5/...-G    |
| Insulating material group               | I                   |
| Rated surge voltage (III/3)             | 4 kV                |
| Rated surge voltage (III/2)             | 4 kV                |
| Rated surge voltage (II/2)              | 4 kV                |
| Rated voltage (III/3)                   | 250 V               |
| Rated voltage (III/2)                   | 320 V               |
| Rated voltage (II/2)                    | 630 V               |
| Connection in acc. with standard        | EN-VDE              |
| Nominal current $I_N$                   | 12 A                |
| Nominal cross section                   | 2.5 mm <sup>2</sup> |
| Maximum load current                    | 12 A                |
| Insulating material                     | PA                  |
| Inflammability class according to UL 94 | V0                  |
| Internal cylindrical gage               | A3                  |

# Housing - MSTBHK 2,5/10-G - 1765085

## Technical data

### General

|                        |        |
|------------------------|--------|
| Stripping length       | 7 mm   |
| Number of positions    | 10     |
| Screw thread           | M3     |
| Tightening torque, min | 0.5 Nm |
| Tightening torque max  | 0.6 Nm |

### Connection data

|                                                                                         |                      |
|-----------------------------------------------------------------------------------------|----------------------|
| Conductor cross section solid min.                                                      | 0.2 mm <sup>2</sup>  |
| Conductor cross section solid max.                                                      | 2.5 mm <sup>2</sup>  |
| Conductor cross section stranded min.                                                   | 0.2 mm <sup>2</sup>  |
| Conductor cross section stranded max.                                                   | 2.5 mm <sup>2</sup>  |
| Conductor cross section stranded, with ferrule without plastic sleeve min.              | 0.25 mm <sup>2</sup> |
| Conductor cross section stranded, with ferrule without plastic sleeve max.              | 2.5 mm <sup>2</sup>  |
| Conductor cross section stranded, with ferrule with plastic sleeve min.                 | 0.25 mm <sup>2</sup> |
| Conductor cross section stranded, with ferrule with plastic sleeve max.                 | 2.5 mm <sup>2</sup>  |
| Conductor cross section AWG/kcmil min.                                                  | 24                   |
| Conductor cross section AWG/kcmil max                                                   | 12                   |
| 2 conductors with same cross section, solid min.                                        | 0.2 mm <sup>2</sup>  |
| 2 conductors with same cross section, solid max.                                        | 1 mm <sup>2</sup>    |
| 2 conductors with same cross section, stranded min.                                     | 0.2 mm <sup>2</sup>  |
| 2 conductors with same cross section, stranded max.                                     | 1.5 mm <sup>2</sup>  |
| 2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.   | 0.25 mm <sup>2</sup> |
| 2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.   | 1 mm <sup>2</sup>    |
| 2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min. | 0.5 mm <sup>2</sup>  |
| 2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max. | 1.5 mm <sup>2</sup>  |
| Minimum AWG according to UL/CUL                                                         | 30                   |
| Maximum AWG according to UL/CUL                                                         | 12                   |

## classifications

### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 272607xx |
| eCl@ss 4.1 | 27260701 |
| eCl@ss 5.0 | 27260701 |
| eCl@ss 5.1 | 27260701 |
| eCl@ss 6.0 | 27260704 |
| eCl@ss 7.0 | 27440402 |

# Housing - MSTBHK 2,5/10-G - 1765085

## classifications

eCl@ss

|            |          |
|------------|----------|
| eCl@ss 8.0 | 27440402 |
|------------|----------|

ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC001121 |
| ETIM 4.0 | EC002638 |
| ETIM 5.0 | EC002638 |

UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211810 |
| UNSPSC 7.0901 | 39121409 |
| UNSPSC 11     | 39121409 |
| UNSPSC 12.01  | 39121409 |
| UNSPSC 13.2   | 39121409 |

## approvals

CSA / UL Recognized / VDE Gutachten mit Fertigungsüberwachung / cUL Recognized / IECCEB Scheme / CCA / cULus Recognized /

## Approval details

| CSA  |       |       |
|-----------------------------------------------------------------------------------------|-------|-------|
| Usegroups                                                                               | B     | D     |
| Nominal voltage UN                                                                      | 300 V | 300 V |
| Nominal current IN                                                                      | 10 A  | 10 A  |
| mm <sup>2</sup> /AWG/kcmil                                                              | 28-12 | 28-12 |

| UL Recognized  |       |       |
|---------------------------------------------------------------------------------------------------|-------|-------|
| Usegroups                                                                                         | B     | D     |
| Nominal voltage UN                                                                                | 250 V | 300 V |
| Nominal current IN                                                                                | 12 A  | 10 A  |
| mm <sup>2</sup> /AWG/kcmil                                                                        | 30-12 | 30-12 |

|                                                                                                                             |       |
|-----------------------------------------------------------------------------------------------------------------------------|-------|
| VDE Gutachten mit Fertigungsüberwachung  |       |
| Nominal voltage UN                                                                                                          | 250 V |
| Nominal current IN                                                                                                          | 12 A  |

## Housing - MSTBHK 2,5/10-G - 1765085

### approvals

|               |         |
|---------------|---------|
|               |         |
| mm²/AWG/kcmil | 0.2-2.5 |

| cUL Recognized  |       |       |
|--------------------------------------------------------------------------------------------------|-------|-------|
| Usegroups                                                                                        | B     | D     |
| Nominal voltage UN                                                                               | 250 V | 300 V |
| Nominal current IN                                                                               | 12 A  | 10 A  |
| mm²/AWG/kcmil                                                                                    | 30-12 | 30-12 |

|                                                                                                   |         |
|---------------------------------------------------------------------------------------------------|---------|
| IECEE CB Scheme  |         |
|                                                                                                   |         |
| Nominal voltage UN                                                                                | 250 V   |
| Nominal current IN                                                                                | 12 A    |
| mm²/AWG/kcmil                                                                                     | 0.2-2.5 |

|                    |         |
|--------------------|---------|
| CCA                |         |
|                    |         |
| Nominal voltage UN | 250 V   |
| Nominal current IN | 12 A    |
| mm²/AWG/kcmil      | 0.2-2.5 |

|                                                                                                      |  |
|------------------------------------------------------------------------------------------------------|--|
| cULus Recognized  |  |
|------------------------------------------------------------------------------------------------------|--|

### accessories

#### Filler plug

MSTB-BL - 1755477



#### End block

## Housing - MSTBHK 2,5/10-G - 1765085

accessories

E/MBK - 1401637



---

### Screwdriver tools

SZS 0,6X3,5 - 1205053



---

### Labeled terminal marker

SK 5,08/3,8:FORTL.ZAHLEN - 0804293



---

### Coding element

CR-MSTB - 1734401



---

### Mounting rail

NS 15 PERF 2000MM - 1401682



## Housing - MSTBHK 2,5/10-G - 1765085

### accessories

---

NS 15 UNPERF 2000MM - 1401695



### accessories

---

MSTBHK 2,5/ 2 AH - 5030185



## Drawings

Dimensioned drawing

