

Printed-circuit board connector - MCC 1/ 4-STZ-3,81 - 1852192

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Plug component, Nominal current: 8 A, Rated voltage (III/2): 160 V, Number of positions: 4, Pitch: 3.81 mm, Connection method: Crimp connection, Color: green, Corresponding female crimp contacts with current [A] and conductor cross section range [mm²] data: 5A/MCC-MT 0,2-0,35 (1859988); 8A/MCC-MT 0,5-1,0 (1859991)

The illustration shows a 16-position version

Product Features

- ☒ Can be combined with MC 1,5 base strips and IMC 1,5 plugs
- ☒ Low design height of the MCC 1 plug range
- ☒ With snap-lock option for pull-out aid
- ☒ Two different crimp contacts can be used:

Key commercial data

package_quantity	50
GTIN	4017918125837

Technical data

Dimensions

Pitch	3.81 mm
Dimension a	11.43 mm

General

Range of articles	MCC 1/...STZ
Insulating material group	I
Rated surge voltage (III/3)	2.5 kV
Rated surge voltage (III/2)	2.5 kV
Rated surge voltage (II/2)	2.5 kV
Rated voltage (III/3)	160 V
Rated voltage (III/2)	160 V
Rated voltage (II/2)	320 V
Connection in acc. with standard	EN-VDE
Nominal current I _N	8 A
Nominal cross section	1 mm ²
Maximum load current	8 A
Insulating material	PA
Inflammability class according to UL 94	V0
Number of positions	4

Printed-circuit board connector - MCC 1/ 4-STZ-3,81 - 1852192

Technical data

Connection data

Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	1 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	18
Minimum AWG according to UL/CUL	20
Maximum AWG according to UL/CUL	18

classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402
eCl@ss 8.0	27440402

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002638
ETIM 5.0	EC002638

UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

approvals

UL Recognized / cUL Recognized / cULus Recognized /

Approval details

UL Recognized 		
Usegroups	B	D
Nominal voltage UN	300 V	300 V
Nominal current IN	5 A	5 A
mm ² /AWG/kcmil	24-22	24-22

Printed-circuit board connector - MCC 1/ 4-STZ-3,81 - 1852192

approvals

cUL Recognized 		
Usegroups	B	D
Nominal voltage UN	300 V	300 V
Nominal current IN	5 A	5 A
mm²/AWG/kcmil	24-22	24-22

cULus Recognized  US		
---	--	--

accessories

Crimp contact

MCC-MT 0,2-0,35 - 1859988



MCC-MT 0,5-1,0 - 1859991



Crimping tool

CRIMPFOX-1,6-ER-1,50-GH - 1772793



Screwdriver tools

Printed-circuit board connector - MCC 1/ 4-STZ-3,81 - 1852192

accessories

SZS 0,4X2,5 VDE - 1205037



Labeled terminal marker

SK 3,81/2,8:FORTL.ZAHLEN - 0804109



accessories

STZ 2-PCC 4-7,62 - 1840214



STZ 3-PCC 4-7,62 - 1840227

STZ 5-PCC 4-7,62 GN - 1842005

Printed-circuit board connector - MCC 1/ 4-STZ-3,81 - 1852192

accessories

STZ 8-PCC 4-7,62 - 1840230

MCC-MT 0,2-0,35 (0,0) BA - 1923717




MCC-MT 0,5-1,0 BAND - 1898622



Drawings

Printed-circuit board connector - MCC 1/ 4-STZ-3,81 - 1852192

Diagram



Type: MCC 1/...-ST-3,81 with MC 1,5/...-G-3,81; contact: MCC-MT 0,5 - 1,0

Dimensioned drawing

