

Printed-circuit board connector - MSTBO 2,5/ 3-6 ST SET KMGY - 2713748

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Kit consisting of COMBICON header and screw connectors for 6x3 positions (18-pos.), color: Light gray

Key commercial data

package_quantity	1
GTIN	4017918914486

classifications

eCl@ss

eCl@ss 4.0	27180401
eCl@ss 4.1	27180401
eCl@ss 5.0	27180506
eCl@ss 5.1	27260701
eCl@ss 6.0	27180802
eCl@ss 7.0	27182702
eCl@ss 8.0	27182702

ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC001031

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

approvals

CSA / VDE Gutachten mit Fertigungsüberwachung / IECEx CB Scheme / UL Recognized / cUL Recognized / CCA / cULus Recognized /

Printed-circuit board connector - MSTBO 2,5/ 3-6 ST SET KMGY - 2713748

approvals

Approval details

CSA 		
Usegroups	B	D
Nominal voltage UN	300 V	300 V
Nominal current IN	10 A	10 A
mm²/AWG/kcmil	28-12	28-12

VDE Gutachten mit Fertigungsüberwachung 	
Nominal voltage UN	250 V
Nominal current IN	8 A
mm²/AWG/kcmil	

IECEE CB Scheme 	
Nominal voltage UN	250 V
Nominal current IN	8 A
mm²/AWG/kcmil	

UL Recognized 		
Usegroups	B	D
Nominal voltage UN	300 V	300 V
Nominal current IN	15 A	10 A
mm²/AWG/kcmil	30-12	30-12

cUL Recognized 		
Usegroups	B	D
Nominal voltage UN	300 V	300 V
Nominal current IN	15 A	10 A
mm²/AWG/kcmil	30-12	30-12

Printed-circuit board connector - MSTBO 2,5/ 3-6 ST SET
KMGY - 2713748

approvals

CCA	
Nominal voltage UN	250 V
Nominal current IN	8 A
mm²/AWG/kcmil	



accessories



Coding element

CR MSTBO-G1 - 2199618



Drawings



Schematic diagram



Pin assignment right



Printed-circuit board connector - MSTBO 2,5/ 3-6 ST SET KMGY - 2713748

Schematic diagram



Pin assignment right

Schematic diagram



Pin assignment left