


Printed-circuit board connector - ISPC 16/ 2-ST-10,16 - 1748545

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Plug component, Nominal current: 76 A, Rated voltage (III/2): 1000 V, Number of positions: 2, Pitch: 10.16 mm, Connection method: Spring-cage conn., Color: green, Contact surface: Silver

The illustration shows the 5-pos. version

Product Features

- ✓ Can be plugged into (S)PC 16 plugs or inverted IPC 16 headers
- ✓ Unlimited 600 V UL approval
- ✓ Inverted Push-in spring-cage plugs with pin contacts for touch-proof device outputs (with IPC 16 G) or free-hanging cable/cable connections
- ✓ Increased vibration protection thanks to screw-on STF plugs with screw flange

Key commercial data

package_quantity	50
GTIN	4046356310604

Technical data

Dimensions

Pitch	10.16 mm
Dimension a	10.16 mm

General

Range of articles	ISPC 16/...-ST
Insulating material group	I
Rated surge voltage (III/3)	8 kV
Rated surge voltage (III/2)	8 kV
Rated surge voltage (II/2)	6 kV
Rated voltage (III/3)	1000 V
Rated voltage (III/2)	1000 V
Rated voltage (II/2)	1000 V
Connection in acc. with standard	EN-VDE
Nominal current I _N	76 A
Nominal cross section	16 mm ²
Maximum load current	76 A (with 16 mm ² conductor cross section)
Insulating material	PA
Inflammability class according to UL 94	V0

Printed-circuit board connector - ISPC 16/ 2-ST-10,16 - 1748545

Technical data

General

Stripping length	18 mm
Number of positions	2
Screw thread	M4
Tightening torque, min	1.8 Nm

Connection data

Conductor cross section solid min.	0.75 mm ²
Conductor cross section solid max.	16 mm ²
Conductor cross section stranded min.	0.75 mm ²
Conductor cross section stranded max.	16 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.75 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	16 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.75 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	10 mm ²
Conductor cross section AWG/kcmil min.	18
Conductor cross section AWG/kcmil max	4
2 conductors with same cross section, solid min.	0.75 mm ²
2 conductors with same cross section, solid max.	6 mm ²
2 conductors with same cross section, stranded min.	0.75 mm ²
2 conductors with same cross section, stranded max.	6 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	0.75 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.75 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	4 mm ²
Minimum AWG according to UL/CUL	20
Maximum AWG according to UL/CUL	4

classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402
eCl@ss 8.0	27440402

ETIM

Printed-circuit board connector - ISPC 16/ 2-ST-10,16 - 1748545

classifications

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002638
ETIM 5.0	EC002638

UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

approvals

UL Recognized / cUL Recognized / GOST / SEV / CCA / IECEE CB Scheme / GOST / cULus Recognized /

Approval details

UL Recognized 		
Usegroups	B	C
Nominal voltage UN	600 V	600 V
Nominal current IN	66 A	66 A
mm²/AWG/kcmil	20-4	20-4

cUL Recognized 		
Usegroups	B	C
Nominal voltage UN	600 V	600 V
Nominal current IN	66 A	66 A
mm²/AWG/kcmil	20-4	20-4

GOST 	
---	--


SEV	
Nominal voltage UN	1000 V
Nominal current IN	76 A
mm²/AWG/kcmil	16

Printed-circuit board connector - ISPC 16/ 2-ST-10,16 - 1748545

approvals

CCA	
Nominal voltage UN	1000 V
Nominal current IN	76 A
mm²/AWG/kcmil	

IECEE CB Scheme 	
Nominal voltage UN	1000 V
Nominal current IN	76 A
mm²/AWG/kcmil	



cULus Recognized  US	

accessories

Coding element

CP-PC RD - 1701967



Crimping tool


CRIMPFOX 16 S - 1207983




Drawings

Printed-circuit board connector - ISPC 16/ 2-ST-10,16 - 1748545

Diagram




Diagram




Printed-circuit board connector - ISPC 16/ 2-ST-10,16 - 1748545

Diagram



Derating curve for: ISPC 16/...-ST-10,16 with IPCV 16/...-G-10,16


Diagram



Type: ISPC 16/...-ST-10,16 with DFK-IPC 16/...-ST-10,16

Printed-circuit board connector - ISPC 16/ 2-ST-10,16 - 1748545

Dimensioned drawing



© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>