

PCB terminal block - PTSM 0,5/ 4-2,5-H SMD R24 - 1702474

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



PCB terminal block, Nominal current: 6 A, Nom. voltage: 160 V, Pitch: 2.5 mm, Number of positions: 4, Connection method: Spring-cage conn., Mounting: SMD/THT/THR, Conductor/PCB connection direction: 0 °, Color: black

The illustration shows the 3-pos. version

Product Features

- ✓ Compact low-profile SMD PCB terminal block with 2.5 mm pitch
- ✓ High current carrying capacity for high power transmission
- ✓ Supplied in tape-on-reel packing according to IEC 60286-3 for automated mounting
- ✓ Rugged solder anchor for secure, mechanical fixing to the surface
- ✓ Spring-cage connection with direct plug-in technology with a release mechanism
- ✓ Specifically designed for use in dedicated SMT processes

Key commercial data

package_quantity	770
GTIN	4046356592314

Technical data

Dimensions

Length	9 mm
Pitch	2.5 mm
Dimension a	7.5 mm
Pin spacing	2.5 mm

General

Range of articles	PTSM 0,5/...-H-SMD
Insulating material group	IIIa
Rated surge voltage (III/3)	2.5 kV
Rated surge voltage (III/2)	2.5 kV
Rated surge voltage (II/2)	2.5 kV
Rated voltage (III/3)	32 V
Rated voltage (III/2)	160 V
Rated voltage (II/2)	160 V
Connection in acc. with standard	EN-VDE
Nominal current I _N	6 A
Nominal cross section	0.5 mm ²

PCB terminal block - PTSM 0,5/ 4-2,5-H SMD R24 - 1702474

Technical data

General

Maximum load current	6 A
Insulating material	LCP
Solder pin surface	Sn
Inflammability class according to UL 94	V0
Stripping length	6 mm
Number of positions	4

Connection data

Conductor cross section solid min.	0.14 mm ²
Conductor cross section solid max.	0.5 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	0.5 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.25 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	0.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	20

classifications

eCl@ss

eCl@ss 4.0	27141109
eCl@ss 4.1	27141109
eCl@ss 5.0	27141190
eCl@ss 5.1	27141190
eCl@ss 6.0	27261101
eCl@ss 7.0	27440401
eCl@ss 8.0	27440401

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002643
ETIM 5.0	EC002637

UNSPSC

UNSPSC 6.01	30211801
UNSPSC 7.0901	39121432
UNSPSC 11	39121432
UNSPSC 12.01	39121432
UNSPSC 13.2	39121432

PCB terminal block - PTSM 0,5/ 4-2,5-H SMD R24 - 1702474

approvals

GOST / GOST / UL Recognized / cUL Recognized / UL Recognized / cULus Recognized /

Approval details

GOST 



UL Recognized 

Usegroups	B
Nominal voltage UN	150 V
Nominal current IN	5 A
mm²/AWG/kcmil	26-20

cUL Recognized 

Usegroups	B
Nominal voltage UN	150 V
Nominal current IN	5 A
mm²/AWG/kcmil	26-20



Usegroups	B
Nominal voltage UN	150 V
Nominal current IN	5 A
mm²/AWG/kcmil	26-20

cULus Recognized 

accessories

Screwdriver tools

PCB terminal block - PTSM 0,5/ 4-2,5-H SMD R24 - 1702474


accessories

SZS 0,4X2,0 - 1205202



Drawings


Drilling diagram




Dimension M: 12.7 mm

PCB terminal block - PTSM 0,5/ 4-2,5-H SMD R24 - 1702474

Diagram




Dimensioned drawing



PCB terminal block - PTSM 0,5/ 4-2,5-H SMD R24 - 1702474

Dimensioned drawing



© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>