

Base strip - DFK-MSTBVA 2,5/ 6-GF-5,08 - 1899320

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Header, Nominal current: 12 A, Rated voltage (III/2): 320 V, Number of positions: 6, Pitch: 5.08 mm, Color: green, Contact surface: Tin, Assembly: Soldering

The figure shows a 10-position version of the product

Product Features

- ✓ Outside: plug-in connection for the corresponding MSTB 2,5 or FKC 2,5 plugs
- ✓ Inside: with horizontal or vertical solder connection
- ✓ Inside of the housing is protected against dust by the seal provided
- ✓ Mounting from the inside of the device through the housing panel
- ✓ Headers for assembly in a device/housing panel

Key commercial data

package_quantity	50
GTIN	4017918186340

Technical data

Dimensions

Length	12 mm
Pitch	5.08 mm
Dimension a	25.4 mm

General

Range of articles	DFK-MSTBVA 2,5/..-GF
Insulating material group	IIIa
Rated surge voltage (III/3)	4 kV
Rated surge voltage (III/2)	4 kV
Rated surge voltage (II/2)	4 kV
Rated voltage (III/3)	250 V
Rated voltage (III/2)	320 V
Rated voltage (II/2)	400 V
Connection in acc. with standard	EN-VDE
Nominal current I _N	12 A
Maximum load current	12 A
Insulating material	PBT
Inflammability class according to UL 94	V0

Base strip - DFK-MSTBVA 2,5/ 6-GF-5,08 - 1899320

Technical data

General

Color	green
Number of positions	6

classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27141190
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402
eCl@ss 8.0	27440402

ETIM

ETIM 3.0	EC001283
ETIM 4.0	EC001283
ETIM 5.0	EC001283

UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

approvals

VDE Gutachten mit Fertigungsüberwachung / GOST / IEC EE CB Scheme / GOST / CCA /

Approval details


VDE Gutachten mit Fertigungsüberwachung 	
Nominal voltage UN	250 V
Nominal current IN	12 A
mm²/AWG/kcmil	

GOST 

Base strip - DFK-MSTBVA 2,5/ 6-GF-5,08 - 1899320

approvals

IECEE CB Scheme 	
Nominal voltage UN	250 V
Nominal current IN	12 A
mm²/AWG/kcmil	



CCA	
Nominal voltage UN	250 V
Nominal current IN	12 A
mm²/AWG/kcmil	

accessories

Mounting material

DFK-MSTB-SS - 0708263



Coding element

CR-MSTB - 1734401



Filler plug

Base strip - DFK-MSTBVA 2,5/ 6-GF-5,08 - 1899320


accessories

MSTB-BL - 1755477




Drawings

Drilling diagram




Base strip - DFK-MSTBVA 2,5/ 6-GF-5,08 - 1899320

Dimensioned drawing



Dimensioned drawing



Dimension b: $10,49 \text{ mm} + (\text{no. of pos.} \times 5,08 \text{ mm})$ Dimension c: $\text{Dim. b} + 9,27 \text{ mm}$

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>