

Base strip - IC 2,5/11-G-5,08 - 1786491

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Header, Nominal current: 12 A, Rated voltage (III/2): 320 V, Number of positions: 11, Pitch: 5.08 mm, Color: green, Contact surface: Tin, Assembly: Soldering

The figure shows a 10-position version of the product

Product Features

- ☒ Pairs of guide rails can be used as a 90° board-to-board connection
- ☒ Combination with MSTB 2,5 headers for primary/secondary/PCB connection
- ☒ Use in shock-proof applications
- ☒ Clear separation of PCB inputs/outputs

Key commercial data

package_quantity	50
GTIN	4017918042646

Technical data

Dimensions

Length	19 mm
Pitch	5.08 mm
Dimension a	50.8 mm
Pin dimensions	1,2 x 0,5
Hole diameter	1.4 mm

General

Range of articles	IC 2,5/..-G
Insulating material group	I
Rated surge voltage (III/3)	4 kV
Rated surge voltage (III/2)	4 kV
Rated surge voltage (II/2)	4 kV
Rated voltage (III/3)	320 V
Rated voltage (III/2)	320 V
Rated voltage (II/2)	630 V
Connection in acc. with standard	EN-VDE
Nominal current I_N	12 A
Maximum load current	12 A
Insulating material	PA

Base strip - IC 2,5/11-G-5,08 - 1786491

Technical data

General

Inflammability class according to UL 94	V0
Color	green
Number of positions	11

classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402
eCl@ss 8.0	27440402

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002637
ETIM 5.0	EC002637

UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

approvals

CSA / UL Recognized / VDE Gutachten mit Fertigungsüberwachung / cUL Recognized / GOST / IECCE CB Scheme / GOST / CCA / cULus Recognized /

Approval details

		
Usegroups	B	D
Nominal voltage UN	300 V	300 V
Nominal current IN	10 A	10 A
mm ² /AWG/kcmil		

Base strip - IC 2,5/11-G-5,08 - 1786491

approvals

UL Recognized 		
Usegroups	B	D
Nominal voltage UN	250 V	300 V
Nominal current IN	12 A	10 A
mm²/AWG/kcmil		

VDE Gutachten mit Fertigungsüberwachung 	
Nominal voltage UN	250 V
Nominal current IN	12 A
mm²/AWG/kcmil	

cUL Recognized 		
Usegroups	B	D
Nominal voltage UN	250 V	300 V
Nominal current IN	12 A	10 A
mm²/AWG/kcmil		

GOST 
--

IECEE CB Scheme 	
Nominal voltage UN	250 V
Nominal current IN	12 A
mm²/AWG/kcmil	



CCA	
Nominal voltage UN	250 V

Base strip - IC 2,5/11-G-5,08 - 1786491

approvals

Nominal current I _N	12 A
mm ² /AWG/kcmil	

cULus Recognized  US

accessories

Test plug terminal block

MPS-MT - 0201744



RPS - 0201647



Coding element


CP-MSTB - 1734634



Drawings

Base strip - IC 2,5/11-G-5,08 - 1786491

Drilling diagram



Dimensioned drawing

