

Feed-through terminal block - ST 1,5-TWIN BK - 3037300

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Feed-through terminal block, Connection method: Spring-cage connection, Cross section: 0.08 mm² - 1.5 mm², AWG: 28 - 16, Width: 4.2 mm, Color: black, Mounting type: NS 35/7,5, NS 35/15

The illustration shows version ST 1,5-TWIN in gray

Product Features

- The consistent double function shaft offers every opportunity for time-saving potential distribution and accommodating test accessories
- User-friendly implementation of all potential branching tasks
- Space-saving and practical multi-conductor connection without additional bridges



Key commercial data

package_quantity	50
GTIN	4017918599676

Technical data

General

Number of levels	1
Number of connections	2
Color	black
Insulating material	PA
Inflammability class according to UL 94	V0

General

Maximum load current	17.5 A (with 1.5 mm ² conductor cross section)
Rated surge voltage	6 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 60947-7-1
Nominal current I _N	17.5 A (the maximum load current must not be exceeded by the total current of all connected conductors)
Nominal voltage U _N	500 V
Open side panel	ja

Feed-through terminal block - ST 1,5-TWIN BK - 3037300

Technical data

Dimensions

Width	4.2 mm
Length	60.5 mm
Height NS 35/7,5	36.5 mm
Height NS 35/15	44 mm

Connection data

Conductor cross section solid min.	0.08 mm ²
Conductor cross section solid max.	1.5 mm ²
Conductor cross section AWG/kcmil min.	28
Conductor cross section AWG/kcmil max	16
Conductor cross section stranded min.	0.08 mm ²
Conductor cross section stranded max.	1.5 mm ²
Min. AWG conductor cross section, stranded	28
Max. AWG conductor cross section, stranded	16
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.14 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	1.5 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.14 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	1.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	0.5 mm ²
Connection method	Spring-cage connection
Stripping length	10 mm
Internal cylindrical gage	A 1

classifications

eCl@ss

eCl@ss 4.0	27141121
eCl@ss 4.1	27141121
eCl@ss 5.0	27141120
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27141120

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC000897
ETIM 5.0	EC000897

Feed-through terminal block - ST 1,5-TWIN BK - 3037300

classifications

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

approvals

IECEX / ATEX / CSA / UL Recognized / VDE Gutachten mit Fertigungsüberwachung / cUL Recognized / GOST / LR / GL / BV / DNV / KR / NK / IECEE CB Scheme / GOST / cULus Recognized /

Approval details

IECEX	
Nominal voltage UN	440 V
Nominal current IN	17.5 A
mm ² /AWG/kcmil	0.08-1.5

ATEX	
Nominal voltage UN	440 V
Nominal current IN	17.5 A
mm ² /AWG/kcmil	0.08-1.5

CSA		
Usegroups	B	C
Nominal voltage UN	300 V	300 V
Nominal current IN	15 A	15 A
mm ² /AWG/kcmil	26-14	26-14

UL Recognized		
Usegroups	B	C
Nominal voltage UN	300 V	300 V
Nominal current IN	15 A	15 A
mm ² /AWG/kcmil	26-14	26-14

Feed-through terminal block - ST 1,5-TWIN BK - 3037300

approvals

VDE Gutachten mit Fertigungsüberwachung

Nominal voltage UN	500 V
Nominal current IN	17.5 A
mm ² /AWG/kcmil	1.5

cUL Recognized

Usegroups	B	C
Nominal voltage UN	300 V	300 V
Nominal current IN	15 A	15 A
mm ² /AWG/kcmil	26-14	26-14

GOST

LR

GL

Nominal voltage UN	500 V
Nominal current IN	17.5 A
mm ² /AWG/kcmil	1.5

BV

DNV

KR

NK


IECEE CB Scheme

Nominal voltage UN	500 V
--------------------	-------

Feed-through terminal block - ST 1,5-TWIN BK - 3037300

approvals

Nominal current IN	
mm ² /AWG/kcmil	1.5



accessories

Marker pen

B-STIFT - 1051993



X-PEN 0,35 - 0811228



End cover

D-ST 2,5-TWIN - 3030488



Feed-through terminal block - ST 1,5-TWIN BK - 3037300

accessories

DS-ST 2,5 - 3036602



D-ST 2,5-TWIN-0,8 OG - 3030512



DP PS-4 - 3036712



Partition plate

ATP-ST-TWIN - 3030789



Screwdriver tools

SZF 0-0,4X2,5 - 1204504



Test plug terminal block

Feed-through terminal block - ST 1,5-TWIN BK - 3037300

accessories

RPS - 0201647



MPS-MT - 0201744



PAI-4 - 3030925



PS-4 - 3030970



Documentation

ST-IL - 3039900



Bridge

Feed-through terminal block - ST 1,5-TWIN BK - 3037300

accessories

FBS 4-4 - 3030132



FBS 3-4 - 3030129



FBS 2-4 - 3030116



FBS 5-4 - 3030145



FBS 20-4 - 3030352



FBS 10-4 - 3030158



Feed-through terminal block - ST 1,5-TWIN BK - 3037300

accessories

Mounting rail

NS 35/ 7,5 PERF 2000MM - 0801733



NS 35/ 7,5 UNPERF 2000MM - 0801681



NS 35/ 7,5 WH PERF 2000MM - 1204119



NS 35/ 7,5 WH UNPERF 2000MM - 1204122



NS 35/ 7,5 AL UNPERF 2000MM - 0801704



Feed-through terminal block - ST 1,5-TWIN BK - 3037300

accessories

NS 35/ 7,5 ZN PERF 2000MM - 1206421



NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



NS 35/ 7,5 CU UNPERF 2000MM - 0801762



NS 35/ 7,5 CAP - 1206560



NS 35/15 PERF 2000MM - 1201730



NS 35/15 UNPERF 2000MM - 1201714



Feed-through terminal block - ST 1,5-TWIN BK - 3037300

accessories

NS 35/15 WH PERF 2000MM - 0806602



NS 35/15 WH UNPERF 2000MM - 1204135



NS 35/15 AL UNPERF 2000MM - 1201756



NS 35/15 ZN PERF 2000MM - 1206599



NS 35/15 ZN UNPERF 2000MM - 1206586



Feed-through terminal block - ST 1,5-TWIN BK - 3037300

accessories

NS 35/15 CU UNPERF 2000MM - 1201895



NS 35/15 CAP - 1206573



NS 35/15-2,3 UNPERF 2000MM - 1201798



Terminal marking

ZB 4 :UNBEDRUCKT - 0805001



UC-TM 4 - 0818111



Feed-through terminal block - ST 1,5-TWIN BK - 3037300

accessories

UCT-TM 4 - 0828732



ZBF 4:UNBEDRUCKT - 0808587



UC-TMF 4 - 0818166



UCT-TMF 4 - 0828742



Labeled terminal marker

ZB 4 CUS - 0824951



Feed-through terminal block - ST 1,5-TWIN BK - 3037300

accessories

UC-TM 4 CUS - 0824573



UCT-TM 4 CUS - 0829588



ZBF 4 CUS - 0825023



UC-TMF 4 CUS - 0824630



UCT-TMF 4 CUS - 0829651



Insulating sleeve

Feed-through terminal block - ST 1,5-TWIN BK - 3037300

accessories

MPS-IH WH - 0201663



MPS-IH RD - 0201676



MPS-IH BU - 0201689



MPS-IH YE - 0201692



MPS-IH GN - 0201702



MPS-IH GY - 0201728



Feed-through terminal block - ST 1,5-TWIN BK - 3037300

accessories

MPS-IH BK - 0201731



ISH 1,5/0,2 - 3206131



ISH 1,5/0,5 - 3031034



End block

CLIPFIX 35 - 3022218



CLIPFIX 35-5 - 3022276



Feed-through terminal block - ST 1,5-TWIN BK - 3037300

accessories

E/NS 35 N - 0800886



E/UK - 1201442



E/UK 1 - 1201413



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>