


Bolt connection terminal block - RTO 8 - 3049343

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Feed-through terminal block with bolt connection, cross section: 2.5 - 35 mm², AWG: 14 - 2, width 20.2 mm, color: Gray

Product Features

- ✓ Four bridge shafts per terminal block
- ✓ Terminal point always freely accessible

Key commercial data

package_quantity	25
GTIN	4046356140058

Technical data

General

Note	Note: the BE-RT... path extension is to be used for non-insulated cable lugs (see accessories).
Number of levels	1
Number of connections	2
Color	gray
Insulating material	PA
Inflammability class according to UL 94	V0

General

Maximum load current	125 A (with 35 mm ² conductor cross section)
Rated surge voltage	8 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 60947-7-1
Nominal current I _N	125 A
Nominal voltage U _N	1000 V
Open side panel	ja
Number of positions	1
Surge voltage test setpoint	9.8 kV
Result of surge voltage test	Test passed
Power frequency withstand voltage setpoint	2.2 kV

Bolt connection terminal block - RTO 8 - 3049343

Technical data

General

Result of power-frequency withstand voltage test	Test passed
Checking the mechanical stability of terminal points (5 x conductor connection)	Test passed
Tight fit on carrier	NS 35
Setpoint	10 N
Result of tight fit test	Test passed
Requirements, voltage drop	≤ 3.2 mV
Result of voltage drop test	Test passed
Temperature-rise test	Test passed
Conductor cross section short circuit testing	35 mm ²
Short-time current	4.2 kA
Short circuit stability result	Test passed
Proof of thermal characteristics (needle flame) effective duration	30 s
Result of thermal test	Test passed
Test specification, oscillation, broadband noise	DIN EN 50155 (VDE 0115-200):2008-03
Test spectrum	Service life test category 1, class B, body mounted
Test frequency	$f_1 = 5$ Hz to $f_2 = 150$ Hz
ASD level	0.02 g ² /Hz
Acceleration	0.8 g
Test duration per axis	5 h
Test directions	X-, Y- and Z-axis
Oscillation, broadband noise test result	Test passed
Test specification, shock test	DIN EN 50155 (VDE 0115-200):2008-03
Shock form	Half-sine
Acceleration	5 g
Shock duration	30 ms
Number of shocks per direction	3
Test directions	X-, Y- and Z-axis (pos. and neg.)
Shock test result	Test passed
Temperature index, insulating material (DIN EN 60216-1 (VDE 0304-21))	120 °C

Dimensions

Width	20.2 mm
Length	84 mm
Height NS 35/7,5	62.2 mm
Height NS 35/15	69.7 mm

Connection data

Note	Connection bolts
Conductor cross section solid min.	2.5 mm ²
Conductor cross section solid max.	35 mm ²

Bolt connection terminal block - RTO 8 - 3049343

Technical data

Connection data

Conductor cross section AWG/kcmil min.	14
Conductor cross section AWG/kcmil max	2
Conductor cross section stranded min.	2.5 mm ²
Conductor cross section stranded max.	35 mm ²
Min. AWG conductor cross section, stranded	14
Max. AWG conductor cross section, stranded	2
Min. cross section for cable lug connection	2.5 mm ²
Max. cross section for cable lug connection	35 mm ²
Connection method	Bolt connection
Screw thread	M8
Tightening torque, min	6 Nm
Tightening torque max	10 Nm

classifications

eCl@ss

eCl@ss 4.0	27141120
eCl@ss 4.1	27141120
eCl@ss 5.0	27141120
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27141120

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC000897
ETIM 5.0	EC000897

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

approvals

ATEX / IECEx / UL Recognized / VDE Zeichengenehmigung / cUL Recognized / ABS / UL Recognized / VDE Zeichengenehmigung /
IECEE CB Scheme / cULus Recognized /

Bolt connection terminal block - RTO 8 - 3049343

approvals

Approval details

ATEX 	
Nominal voltage UN	690 V
Nominal current IN	125 A
mm²/AWG/kcmil	2.5-35

IECEX	
Nominal voltage UN	690 V
Nominal current IN	125 A
mm²/AWG/kcmil	2.5-35

UL Recognized 		
Usegroups	B	C
Nominal voltage UN	600 V	600 V
Nominal current IN	115 A	115 A
mm²/AWG/kcmil		

VDE Zeichengenehmigung 	
Nominal voltage UN	1000 V
Nominal current IN	125 A
mm²/AWG/kcmil	2.5-35

cUL Recognized 		
Usegroups	B	C
Nominal voltage UN	600 V	600 V
Nominal current IN	115 A	115 A
mm²/AWG/kcmil		

ABS

Bolt connection terminal block - RTO 8 - 3049343

approvals

UL Recognized 			
Usegroups	B	C	D
Nominal voltage UN	600 V	600 V	300 V
Nominal current IN	115 A	115 A	10 A
mm²/AWG/kcmil			

	
Nominal voltage UN	1000 V
Nominal current IN	125 A
mm²/AWG/kcmil	2.5-35

IECEE CB Scheme 

cULus Recognized 
--

accessories

End cover

D-RT 8 - 3049194



BE-RT 8 - 3049916



Bolt connection terminal block - RTO 8 - 3049343

accessories

Screwdriver tools

SZS 1,0X4,0 VDE - 1205066



Partition plate

TPN-UK - 3003062



Bridge

FBS 2-10 - 3005947



Mounting rail

NS 35/ 7,5 PERF 2000MM - 0801733



NS 35/ 7,5 UNPERF 2000MM - 0801681



Bolt connection terminal block - RTO 8 - 3049343

accessories

NS 35/ 7,5 WH PERF 2000MM - 1204119



NS 35/ 7,5 WH UNPERF 2000MM - 1204122



NS 35/ 7,5 AL UNPERF 2000MM - 0801704



NS 35/ 7,5 ZN PERF 2000MM - 1206421



NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



Bolt connection terminal block - RTO 8 - 3049343

accessories

NS 35/ 7,5 CU UNPERF 2000MM - 0801762



NS 35/ 7,5 CAP - 1206560



NS 35/15 PERF 2000MM - 1201730



NS 35/15 UNPERF 2000MM - 1201714



NS 35/15 WH PERF 2000MM - 0806602



NS 35/15 WH UNPERF 2000MM - 1204135



Bolt connection terminal block - RTO 8 - 3049343

accessories

NS 35/15 AL UNPERF 2000MM - 1201756



NS 35/15 ZN PERF 2000MM - 1206599



NS 35/15 ZN UNPERF 2000MM - 1206586



NS 35/15 CU UNPERF 2000MM - 1201895



NS 35/15 CAP - 1206573



Bolt connection terminal block - RTO 8 - 3049343

accessories

NS 35/15-2,3 UNPERF 2000MM - 1201798



Terminal marking

ZB 16,3:UNPRINTED - 0820222



ZB 20,3:UNPRINTED - 0820248



Labeled terminal marker

ZB 16,3 CUS - 0824946



ZB 20,3 CUS - 0824948



End block

Bolt connection terminal block - RTO 8 - 3049343

accessories

CLIPFIX 35 - 3022218



CLIPFIX 35-5 - 3022276



E/NS 35 N - 0800886



E/UK - 1201442



E/UK 1 - 1201413



Drawings

Bolt connection terminal block - RTO 8 - 3049343

Circuit diagram



© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>