

Printed-circuit board connector - GMVSTBW 2,5/ 4-ST - 1737835

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Plug component, Nominal current: 12 A, Rated voltage (III/2): 630 V, Number of positions: 4, Pitch: 7.5 mm, Connection method: Screw connection, Color: green, Contact surface: Tin

The figure shows a 10-position version of the product

Product Features

- ☒ Versions with screw flange and 7.62 mm pitch
- ☒ Plug-in direction vertical to the conductor axis
- ☒ Conductor entry on the rippled side of the plug
- ☒ Plugs for 630 V applications (III/2)

Key commercial data

package_quantity	50
GTIN	4017918028077

Technical data

Dimensions

Height	17.7 mm
Pitch	7.5 mm
Dimension a	22.5 mm

General

Range of articles	GMVSTBW 2,5/...-ST
Insulating material group	I
Rated surge voltage (III/3)	6 kV
Rated surge voltage (III/2)	6 kV
Rated surge voltage (II/2)	6 kV
Rated voltage (III/3)	500 V
Rated voltage (III/2)	630 V
Rated voltage (II/2)	1000 V
Connection in acc. with standard	EN-VDE
Nominal current I_N	12 A
Nominal cross section	2.5 mm ²
Maximum load current	12 A
Insulating material	PA
Inflammability class according to UL 94	V0

Printed-circuit board connector - GMVSTBW 2,5/ 4-ST - 1737835

Technical data

General

Internal cylindrical gage	A3
Stripping length	7 mm
Number of positions	4
Screw thread	M3
Tightening torque, min	0.5 Nm
Tightening torque max	0.6 Nm

Connection data

Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	2.5 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.25 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	2.5 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.25 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
2 conductors with same cross section, solid min.	0.2 mm ²
2 conductors with same cross section, solid max.	1 mm ²
2 conductors with same cross section, stranded min.	0.2 mm ²
2 conductors with same cross section, stranded max.	1.5 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	0.25 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	1 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	1 mm ²
Minimum AWG according to UL/CUL	30
Maximum AWG according to UL/CUL	12

classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260704

Printed-circuit board connector - GMVSTBW 2,5/ 4-ST - 1737835

classifications

eCl@ss

eCl@ss 7.0	27440402
eCl@ss 8.0	27440402

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002638
ETIM 5.0	EC002638

UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

approvals

CSA / UL Recognized / VDE Gutachten mit Fertigungsüberwachung / cUL Recognized / GOST / IECCE CB Scheme / GOST / IECCE CB Scheme / cULus Recognized /

Approval details

CSA 		
Usegroups	B	D
Nominal voltage UN	300 V	300 V
Nominal current IN	10 A	10 A
mm²/AWG/kcmil	28-12	28-12

UL Recognized 		
Usegroups	B	D
Nominal voltage UN	300 V	300 V
Nominal current IN	15 A	10 A
mm²/AWG/kcmil	30-12	30-12

VDE Gutachten mit Fertigungsüberwachung 	
Nominal voltage UN	400 V

Printed-circuit board connector - GMVSTBW 2,5/ 4-ST - 1737835

approvals

Nominal current I _N	12 A
mm ² /AWG/kcmil	0.2-2.5

cUL Recognized 		
Usegroups	B	D
Nominal voltage U _N	300 V	300 V
Nominal current I _N	15 A	10 A
mm ² /AWG/kcmil	30-12	30-12

GOST 
--

IECEE CB Scheme 	
Nominal voltage U _N	400 V
Nominal current I _N	12 A
mm ² /AWG/kcmil	0.2-2.5



CB 	
Nominal voltage U _N	400 V
Nominal current I _N	12 A
mm ² /AWG/kcmil	0.2-2.5

cULus Recognized 	
--	--

accessories

Screwdriver tools

Printed-circuit board connector - GMVSTBW 2,5/ 4-ST - 1737835

accessories

SZS 0,6X3,5 - 1205053



Coding element

CP-MSTB - 1734634



Labeled terminal marker

SK 7,5/3,8:FORTL.ZAHLEN - 0804455



SK 7,5/3,8:FORTL.ZAHLEN - 0804455



Terminal marking

SK U/3,8 WH:UNBEDRUCKT - 0803906



Printed-circuit board connector - GMVSTBW 2,5/ 4-ST - 1737835

accessories


Marker pen

B-STIFT - 1051993



Drawings

Dimensioned drawing



© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>