

DULUX[®] S/E

SLIM DESIGN MAKING THEM EXTREMELY
VERSATILE FOR ALMOST UNIVERSAL USE



DULUX[®] S/E



QTP-ECO 2x5-11/220-240 S


Benefits

- Extremely economical
- Outstanding quality of light
- Low power consumptions (7W, 9W, 11W)
- Long service life time¹
- Environmental friendly

Product Features

- Improved average lamp life: up to 20.000 h (with QUICKTRONIC®)
- Extremely flat dimensions
- Improved lumen maintenance
- Dimmable from 3...100%
- For operation on electronic control gear (ECG)
- Available light colors: Cool White (840), Warm White (830), Extra Warm White (827)

Dimensions



Description	Base	Max Length L1 [mm]	Max Length L1 IEC [mm]
DULUX® S/E 7 W	2G7	114	115
DULUX® S/E 9 W	2G7	144	145
DULUX® S/E 11 W	2G7	214	215

¹ Service life time is the mathematical life time (maintenance multiplied with the % of failed lamps e.g. B10) for lamps in an installation after which the installation luminous flux (100 h value) decreased with 30 % (decrease in luminous flux and failed lamps) for indoor lighting.

Edition 01.2014. Subject to change without notice. Errors and omissions excepted. Always make sure to use the most recent release.

LP LPD MK

Electrical Data²

Lamps operated with **HF³** reference control gear at 25 °C (100 h aged) ambient temperature

DULUX® S/E	Lamp Voltage rated [V]	Lamp Current rated [mA]	Lamp Power rated [W]
7 W	37	175	6.5
9 W	48	170	8.0
11 W	75	150	11.0

Photometrical Data at 25 °C (100 h aged) ambient temperature⁴

DULUX® S/E	Light Color LUMILUX®	Color Rendering Index (CRI), Ra	Lumi-nance (LC ⁵ 840) [cd/cm ²]	Target Color Coordinate X	Target Color Coordinate Y	Nominal Luminous Flux [lm]	Efficacy 25 °C [lm/W]
7 W	827 INTERNA	80 ... 89	2.6	0.455	0.415	400	62
7 W	830 Warm White	80 ... 89	2.6	0.440	0.403	400	62
7 W	840 Cool White	80 ... 89	2.6	0.380	0.380	400	62
9 W	827 INTERNA	80 ... 89	2.8	0.455	0.415	600	75
9 W	830 Warm White	80 ... 89	2.8	0.440	0.403	600	75
9 W	840 Cool White	80 ... 89	2.8	0.380	0.380	600	75
11 W	827 INTERNA	80 ... 89	2.7	0.455	0.415	900	82
11 W	830 Warm White	80 ... 89	2.7	0.440	0.403	900	82
11 W	840 Cool White	80 ... 89	2.7	0.380	0.380	900	82

² According to IEC 60901

³ High Frequency

⁴ Measurement in accordance with IEC 60901, annex C and the relevant annex on rated colour characteristics in IEC 60081.

⁵ Light Color

Edition 01.2014. Subject to change without notice. Errors and omissions excepted. Always make sure to use the most recent release.

LP LPD MK

Lifetime⁶

	ECG ⁷ preheated IEC switching cycle ⁸
B50⁹	20,000 h
Service life time¹⁰	13,000 h
LLMF¹¹ 2.000 h	0.89
LLMF 4.000 h	0.86
LLMF 6.000 h	0.84
LLMF 8.000 h	0.82
LLMF 12.000 h	0.79
LLMF 16.000 h	0.78
LLMF 20.000 h	0.76
LSF¹² 2.000 h	0.99
LSF 4.000 h	0.99
LSF 6.000 h	0.99
LSF 8.000 h	0.99
LSF 12.000 h	0.95
LSF 16.000 h	0.81
LSF 20.000 h	0.50

⁶ Measurement in accordance with IEC 60901

⁷ Electronic Control Gear

⁸ Switching cycle 165 min. on, 15 min. off (according to IEC)

⁹ Average rated lamp life (B50) is the average value of the life time for an entity of lamps operated under standardized conditions until 50% failure. In other words, this is the operation time at which, for a standardized 3-hour switching cycle (165 minutes on / 15 minutes off (according to IEC)), 50% of a sample population of lamps have failed.

¹⁰ Service life time is the mathematical life time (maintenance multiplied with the % of failed lamps e.g. B10) for lamps in an installation after which the installation luminous flux (100 h value) decreased by 30% (decrease in luminous flux and failed lamps) for indoor lighting

¹¹ Lamp Lumen Maintenance Factor (Lamp luminous flux in %): Ratio of the luminous flux of a specific quantity of lamps at a defined number of hours of operation to their luminous flux at 100 h

¹² Lamp Survival Factor (Lamp Survival in %): Ratio of the number of electrically intact lamps to the total number of lamps
Edition 01.2014. Subject to change without notice. Errors and omissions excepted. Always make sure to use the most recent release.

LP LPD MK

Energy labelling¹³

Description	Energy efficiency class	Weighted energy consumption E _c [kWh/1000h]
DULUX® S/E 7W/827	A	8
DULUX® S/E 7W/830	A	8
DULUX® S/E 7W/840	A	8
DULUX® S/E 9W/827	A	10
DULUX® S/E 9W/830	A	10
DULUX® S/E 9W/840	A	10
DULUX® S/E 11W/827	A	13
DULUX® S/E 11W/830	A	13
DULUX® S/E 11W/840	A	13

Logistic Data

Description	EAN 10	EAN 40	Packaging Unit
DULUX® S/E 7W/827	4050300017648	4050300251233	10
DULUX® S/E 7W/830	4050300591988	4050300591995	10
DULUX® S/E 7W/840	4050300020167	4050300252971	10
DULUX® S/E 9W/827	4050300017655	4050300251264	10
DULUX® S/E 9W/830	4050300589398	4050300589404	10
DULUX® S/E 9W/840	4050300020174	4050300252988	10
DULUX® S/E 11W/827	4050300017662	4050300251295	10
DULUX® S/E 11W/830	4050300589374	4050300589381	10
DULUX® S/E 11W/840	4050300020181	4050300252995	10

¹³ According to Regulation (EU) No 874/2012 of July 12, 2012
Edition 01.2014. Subject to change without notice. Errors and omissions excepted. Always make sure to use the most recent release.
LP LPD MK

Lamp/ECG System Combination

Lamp	ECG	EAN 10 ECG	Luminous flux @25°C [lm]	System power [W]	I _N [A]	Power Factor ECG [λ]	System luminous efficacy [lm/W]	Length [mm]	Width [mm]	Height [mm]	Distance between holes [mm]	T _a [°C]
DULUX® S/E 7 W	DT-S/E 5-11/220-240 L	4008321181473	400	9	0.07	0.60 c	44	89	40	45	30	-15...+50
	DT-S/E 5-11/220-240 S	4008321181459	400	9	0.07	0.60 c	44	75	55	34	67	-15...+50
	QT-ECO 1x4-16/220-240 L	4050300660370	400	9	0.06	0.60 c	44	150	22	22	140	-15...+50
	QT-ECO 1x4-16/220-240 S	4050300638584	400	9	0.06	0.60 c	44	80	40	22	72-75	-15...+50
	QT-ECO 2x5-11/220-240 S	4050300821504	800	15	0.11	0.60 c	53	80	40	22	72-75	-15...+50
	QT-T/E 1x14-17/220-240 HE	4008321327345	400	8	0.04	0.85 c	50	103	67	30	110	-15...+50
DULUX® S/E 9 W	DT-S/E 5-11/220-240 L	4008321181473	600	10.5	0.08	0.60 c	57	89	40	45	30	-15...+50
	DT-S/E 5-11/220-240 S	4008321181459	600	10.5	0.08	0.60 c	57	75	55	34	67	-15...+50
	QT-ECO 1x4-16/220-240 L	4050300660370	600	10	0.07	0.60 c	60	150	22	22	140	-15...+50
	QT-ECO 1x4-16/220-240 S	4050300638584	600	10	0.07	0.60 c	60	80	40	22	72-75	-15...+50
	QT-ECO 2x5-11/220-240 S	4050300821504	1100	18	0.13	0.60 c	61	80	40	22	72-75	-15...+50
	QTP-D/E 1x10-13	4008321181572	600	9.5	0.05	0.92 c	63	93	58	29	96	-20...+50
	QTP-D/E 2x10-13	4008321181596	1200	18	0.09	0.92 c	67	123	79	33	129.5	-20...+50
DULUX® S/E 11 W	DT-S/E 5-11/220-240 L	4008321181473	900	13.5	0.10	0.60 c	67	89	40	45	30	-15...+50
	DT-S/E 5-11/220-240 S	4008321181459	900	13.5	0.10	0.60 c	67	75	55	34	67	-15...+50
	QT-ECO 1x4-16/220-240 L	4050300660370	900	13	0.09	0.60 c	69	150	22	22	140	-15...+50
	QT-ECO 1x4-16/220-240 S	4050300638584	900	13	0.09	0.60 c	69	80	40	22	72-75	-15...+50
	QT-ECO 2x5-11/220-240 S	4050300821504	1400	24	0.16	0.60 c	58	80	40	22	72-75	-15...+50
	QTP-D/E 1x10-13	4008321181572	900	14	0.06	0.95	64	93	58	29	96	-20...+50
	QTP-D/E 2x10-13	4008321181596	1900	28	0.12	0.95	68	123	79	33	129.5	-20...+50

For more information on ECG refer to <http://www.osram.com/ecg>

In case of lamp breakage: www.osram.com/brokenlamp

For more information technical Information see Technical guide. Free download at www.osram.com