


257/S  
257/C

G13

2A-250V



T130  
Tm110



IP20 LAMPHOLDERS WITH BRACKET

- With lampholder 347/FAU
- With starterholder 16/A

347/FAU, 16/A




### Legend

#### SCREW FIXING




screw fixing

#### CHARACTERISTICS




metal plate thickness




lamp centre height (from the bottom of the metal plate)



PBT green rotor with position of...




rigid conductor section



rigid wires stripping

## TERMINALS



push-wire terminals with 2 holes