

Connector - SACC-MS-17PCON SCO - 1559602

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Sensor/actuator connector, male connector, straight, 17-pos., M12 SPEEDCON, metal knurl, Piercecon®, maximum cable diameter of 8.2 mm

Product Features

- ✓ Safe use in the field, thanks to a high degree of protection
- ✓ Flexible: connectors for on-site assembly
- ✓ Save time, thanks to installation with SPEEDCON rapid interlock system
- ✓ Piercecon® connection: maximum contact density in a connector that can be assembled
- ✓ Save space – with high-pos. connectors



Key commercial data

package_quantity	1
GTIN	4046356314831

Technical data

Dimensions

Wrench size, union nut	13 mm
External diameter	5.4 mm ... 8.2 mm
Stripping length of the sheath	≥ 60 mm

Ambient conditions

Ambient temperature (operation)	-25 °C ... 85 °C (Plug / socket)
Degree of protection	IP67

General

Rated current at 40°C	1.5 A
Rated voltage	30 V
Number of positions	17
Contact resistance	≤ 5 mΩ
Insulation resistance	≥ 100 MΩ
Coding	A - standard
Standards/regulations	M12 connector IEC 61076-2-101
Status display	No
Surge voltage category	II

Connector - SACC-MS-17PCON SCO - 1559602

Technical data

General

Pollution degree	3
Connection method	Piercecon® fast connection
Conductor cross section	0.14 mm ²
AWG conductor cross section	26
Wire diameter including insulation	0.95 mm ... 1.05 mm
Frequency of connections between conductors of the same cross section	≥ 5
Wire insulation material	PUR/PVC
Structure of individual litz in acc. with VDE 0295 / smallest wire diameter	VDE 0295 Class 6
Insertion/withdrawal cycles	≥ 100
Torque	0.4 Nm (M12 knurl)

Material

Inflammability class according to UL 94	V0
Contact material	CuZn
Contact surface material	Ni/Au
Contact carrier material	PA
Material of grip body	Zinc die-cast, nickel-plated
Material, knurls	Zinc die-cast, nickel-plated
Sealing material	FKM

classifications

eCl@ss

eCl@ss 4.0	27140815
eCl@ss 4.1	27140815
eCl@ss 5.0	27143423
eCl@ss 5.1	27143423
eCl@ss 6.0	27279221
eCl@ss 7.0	27440104
eCl@ss 8.0	27440104

ETIM

ETIM 2.0	EC001121
ETIM 3.0	EC002062
ETIM 4.0	EC002062
ETIM 5.0	EC002062

UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	39121413
UNSPSC 11	39121413
UNSPSC 12.01	39121413

Connector - SACC-MS-17PCON SCO - 1559602

classifications

UNSPSC

UNSPSC 13.2	39121413
-------------	----------

approvals

GOST /

Approval details



accessories

Cable by the meter

SAC-17P-100,0-PVC/0,14 - 1441545



Electronics pliers

MICROFOX-SP-1 - 1212487



Torque tool

TSD 04 SAC - 1208429



Connector - SACC-MS-17PCON SCO - 1559602

accessories

TSD-M 1,2NM - 1212224



Screwdriver tools

SAC BIT M12-D15 - 1208432



TSD-M SAC-BIT ADAPTER - 1212600



Protective cap


PROT-M12 FS-PA-CHAIN - 1430873



Drawings

Connector - SACC-MS-17PCON SCO - 1559602


Dimensioned drawing



M12 x 1 plug, straight

Connector - SACC-MS-17PCON SCO - 1559602

Schematic diagram



Pin assignment M12 male connector, 17-pos., male side view

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>