

Shield connection terminal block - SKS 20 - 3240212

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Shield connection terminal block, for applying the shield to busbars

Product Features

- ✓ The SKS ... spring shield connection clamps are available for cable and conductor diameters of 3 to 20 mm
- ✓ According to the requirements of the directive and standards for electrical equipment in potentially explosive areas, as components, shield connections are not able to gain certification. As such, shield connection clamps of type SKS can be used in the Ex area even without appropriate approval and identification.
- ✓ The SKS ... spring shield connection clamps are available for cable and conductor diameters of 3 to 20 mm
- ✓ Three different mounting types supported: on NS 35 DIN rails, on busbars or directly on conductive mounting plates

Key commercial data

package_quantity	10
GTIN	4046356458917

Technical data

General

Number of levels	1
Number of connections	1
Color	silver

Dimensions

Length	27 mm
Width	24.7 mm

Connection data

Conductor cross section solid min.	10 mm ²
Conductor cross section solid max.	20 mm ²
Conductor cross section stranded min.	10 mm ²
Conductor cross section stranded max.	20 mm ²
Conductor cross section AWG/kcmil min.	8
Conductor cross section AWG/kcmil max	4
Connection method	Spring-cage

classifications

eCl@ss

Shield connection terminal block - SKS 20 - 3240212

classifications

eCl@ss

eCl@ss 4.0	27141131
eCl@ss 4.1	27141131
eCl@ss 5.0	27141131
eCl@ss 5.1	27141131
eCl@ss 6.0	27141150
eCl@ss 7.0	27141150
eCl@ss 8.0	27141150

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC000001
ETIM 5.0	EC002020

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

approvals

GOST /

Approval details

GOST 

Drawings