


Cylinder with pneumatic cushioning $\varnothing 32 \div 200$



Cyl. \varnothing	A	AM (Note 1)	B e11	BG	DD	E	EE (Note 2)	I_2	I_8		KK (Note 1)	M	PL	SW	TG		VD	VA	WH	ZM
									Nom.	Toll.					Nom.	Toll.				
32	12	22	30	14	M6	48	G 1/8	16	94	$\pm 0,4$	M10 x 1,25	4,5	15	10	32,5	$\pm 0,5$	5	3	26	146