

Marker for terminal blocks - UCT2-TM 5/6 - 0829249

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



UniCard materials for thermal transfer printers, for labeling Wago terminal blocks, 72-section, can be labeled with THERMOMARK CARD and BLUEMARK LED, color: white

Product Features

- The UCT2-TM 5/6 UniCard markers are suitable for Wago terminal blocks
- The multi-section marking strips are easy to fit and can be easily separated if required
- The markers, which are supplied in uniform sheets, can be labeled quickly, easily, and precisely using the THERMOMARK CARD and the BLUEMARK LED
- Labeling service: Phoenix Contact can custom-label all UniCard markers according to your requirements
- The sheets provide space for including function texts
- The markers support multi-line labeling

Key commercial data

package_quantity	10
GTIN	4046356606318

Technical data

Dimensions

Length (b)	10.2 mm
Height	2.65 mm
Width (a)	4.35 mm

Ambient conditions

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Ambient temperature (operation)	-40 °C ... 120 °C

General

Note	Can be labeled via thermal transfer
Color	white
Components	free from silicone and halogen
Inflammability class according to UL 94	V0
Material	PC
Material	PC
Number of individual labels	72
Number of individual labels per row	12
RoHS compliant	Yes

Marker for terminal blocks - UCT2-TM 5/6 - 0829249

Technical data

General

Printability	Thermal transfer
Printability	Inkjet printing
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 min
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	DIN 50018:1997-06
Climate level	KFW 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result	Test passed

classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27141137
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Marker for terminal blocks - UCT2-TM 5/6 - 0829249

accessories

Magazine

THERMOMARK CARD-UCT-MAG5 - 5146615



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>