

Flush-type connector - SACC-E-FS-17CON-M16/0,5 SCO - 1556294

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Sensor/actuator flush-type socket, 17-pos., M12 SPEEDCON, front/screw mounting with M16 thread, with 0.5 m PVC litz wire, 17 x 0.14 mm²



Key commercial data

package_quantity	1
GTIN	4046356176774

Technical data

Dimensions

Length of cable	0.5 m
-----------------	-------

Ambient conditions

Ambient temperature (operation)	-25 °C ... 85 °C (Plug / socket)
Degree of protection	IP67

General

Rated current at 40°C	1.5 A
Rated voltage	30 V
Number of positions	17
Contact resistance	≤ 3 mΩ
Insulation resistance	≥ 100 MΩ
Coding	A - standard
Standards/regulations	M12 connector IEC 61076-2-101
Signal type/category	Universal
Status display	No
Surge voltage category	II
Pollution degree	3
Connection method	Individual wires
Mounting type	Front mounting M16 x 1.5

Material

Inflammability class according to UL 94	V0
---	----

Flush-type connector - SACC-E-FS-17CON-M16/0,5 SCO - 1556294

Technical data

Material

Contact material	CuZn
Contact surface material	Ni/Au
Contact carrier material	PA 66
Material, knurls	Zinc die-cast, nickel-plated
Sealing material	NBR

Cable

Cable type	TPE litz wire
Conductor cross section	0.14 mm ²
AWG signal line	26
Wire colors	Color-coded DIN 47100
Material conductor insulation	TPE
Conductor material	Tin-plated Cu litz wires
Ambient temperature (operation)	-25 °C ... 85 °C (cable, fixed installation)

classifications

eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27143423
eCl@ss 5.1	27143423
eCl@ss 6.0	27143423
eCl@ss 7.0	27449001
eCl@ss 8.0	27449001

ETIM

ETIM 3.0	EC002061
ETIM 4.0	EC002062
ETIM 5.0	EC002062

UNSPSC

UNSPSC 6.01	31251501
UNSPSC 7.0901	31251501
UNSPSC 11	31251501
UNSPSC 12.01	31251501
UNSPSC 13.2	31251501

approvals

UL Recognized / GOST / GOST /

Flush-type connector - SACC-E-FS-17CON-M16/0,5 SCO - 1556294

approvals

Approval details

UL Recognized 	
Nominal voltage UN	30 V
Nominal current IN	1.5 A
mm²/AWG/kcmil	26-20


GOST 
--


--

Drawings

Flush-type connector - SACC-E-FS-17CON-M16/0,5 SCO - 1556294


Dimensioned drawing



M12 flush-type connector

Flush-type connector - SACC-E-FS-17CON-M16/0,5 SCO - 1556294


Dimensioned drawing



Housing cutout for M16 fastening thread, mounting panel with thread

Flush-type connector - SACC-E-FS-17CON-M16/0,5 SCO - 1556294


Dimensioned drawing



Housing cutout for M16 fastening thread, mounting panel with feed-through hole (alternatively with surface as protection against rotation)

Flush-type connector - SACC-E-FS-17CON-M16/0,5
SCO - 1556294


Circuit diagram



Contact assignment of the M12 socket

Flush-type connector - SACC-E-FS-17CON-M16/0,5 SCO - 1556294

Schematic diagram



Pin assignment M12, 17-pos., socket side view

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>