

Think Automation and beyond...




LH1D Series Surface Mount Indicators IDEC LED Spider




IDEC CORPORATION

(100506)


New ø66 Jumbo Dome Ideal for Mounting on




Excellent Visibility
From the front and the side.




IP67 Protection
Can be used in environments subject to washdown.




Cable Wiring
Integrated wiring ensures waterproof characteristics.




Connector Wiring *New*
Connector types available for easy maintenance.
*Jumbo dome type only




Direct Surface Mounting
Requires only a small space behind the mounting surface, and can be installed without concern for other components behind.




Red/Green
Two-color alternate illumination available.




Three-color Alternate Illumination *New*
Two combinations available: red, green and white; and red, green and pure white.
*Jumbo dome type only




Seven Colors
Amber, green, pure white, red, blue, white, and yellow



Legends
Marking film can be inserted into the flat type.
*Flat type only.




Slim Profile
Can be installed in small areas. Only 10.8 mm in height.
*Flat type only.



Direct Mounting on Aluminum Frames *New*
Installation is improved by the increased number of mounting holes.
*Jumbo dome type only


ø66 Jumbo Dome Type



| Color Variation | | | |
|-----------------|-------|------------|-----|
| | | | |
| Amber | Green | Pure White | Red |
| | | | |
| Blue | White | Yellow | |


Two- and three-color alternate illumination also available.

Application Examples



Robot Arm Status Indicator

Indicates the operating status of the motor.




AGV Status Indicator

Can be used as a directional indicator on automatic guided vehicles.


Indicators with Excellent Visibility. Large Equipment.

With increasing awareness on safety at production sites, equipment must be designed to be clearly visible and capable of delivering correct information. With an innovative design, slim and stylish IDEC LED Spiders are ideal for various applications.




Dimensions in mm.


Dome Type



Flat Type




Two-color alternate illumination also available.




Picking System

Can be used to select picking locations.



Door Monitoring

Indicates whether a door can be opened or closed.



Roller Shutter Status Indicator

Indicates the operating status of a roller shutter.

LH series Surface Mount Indicators

**Innovative indicators with IP67 protection and integrated cable wiring.
Directly mountable on equipment and aluminum frames (jumbo dome types).**

- Surface mount style does not affect the location of other components. Requires only a small space behind the mounting surface.
- Integrated cable wiring ensures waterproof characteristics. 1m, 3m, and 5m cables available. M12 connector cable (30 cm) available for jumbo dome type.
- IP67 (IEC60529) rated. Can be used in environments subject to washdown.
- Slim design well suited for installation in small spaces.
- Excellent visibility from the front and from the side.
- Legends and symbols can be printed on marking film to customize flat type.
- Two-color alternate illumination available for all types. Three-color alternate illumination available with jumbo dome type.



Standards

| Standards | Marks | File No. or Organization |
|----------------------------|-------|--------------------------|
| UL508 CSA C22.2 No.14 | | UL/c-UL File No. E68961 |
| EN60598-2-1 | | TÜV SÜD |
| EN60598-2-1 EN60947-5-1 | | EC Low Voltage Directive |

- LH series surface mount indicators are approved by TÜV as class III lighting fixtures.

Specifications

| Type | Cable | Connector |
|-------------------------------|----------------|-------------|
| Rated Insulation Voltage (Ui) | 32V | |
| Rated Voltage | 24V AC/DC | 24V DC |
| Operating Voltage Range | 24V AC/DC ±10% | 24V DC ±10% |
| Rated Current | 17 mA | |
| Maximum Current Draw | 0.6W | |

- Use Class 2 power supply when using the LH1D as a UL compliant product.
- Use Class III circuit when using the LH1D as an EN compliant product.
- 24V AC, 50/60 Hz
- M12 connectors are available for jumbo dome types only.

| Type | Jumbo Dome | Dome / Flat |
|---------------------|-----------------------|---|
| Illumination Colors | Single Color | A (amber), G (green), PW (pure white), R (red), S (blue), W (white), Y (yellow) |
| | Two-Color Alternate | A/G, A/W, A/PW, R/G, R/W, R/PW, G/W, G/PW |
| | Three-Color Alternate | R/G/W, R/G/PW |

| Type | Jumbo Dome | Dome/Flat |
|-----------|--|--|
| Cable | Single Color | UL20276, 21 AWG, 3-core Cable outside diameter: ϕ 4.9 mm Allowable cable bending radius: 30 mm |
| | Two-Color Alternate | UL20276, 24AWG, 3-core Cable outside diameter: ϕ 4.1 mm Allowable cable bending radius: 24.6 mm |
| | Three-Color Alternate | UL20276, 22AWG, 4-core Cable outside diameter: ϕ 5.0 mm Allowable cable bending radius: 30 mm |
| Connector | 20AWG, 4-core Cable length: 0.3m Cable outside diameter: ϕ 6.0 mm Allowable cable bending radius: 40 mm M12 one-touch connector | |

Specifications




| | |
|---|--|
| Applicable Standards | IEC60947-5-1, IEC60947-1 EN60947-5-1, EN60947-1 EN60598-2-1 UL508, CSA C22.2 No.14 |
| Operating Temperature | -20 to +55°C (no freezing) |
| Operating Humidity | 45 to 85% RH (no condensation) |
| Storage Temperature | -30 to +80°C (no freezing) |
| Impulse Withstand Voltage (illuminating part) | 800V |
| Insulation Resistance | Between live and dead parts: 100 M Ω minimum |
| Dielectric Strength | Between live and dead parts: 2000V, 50/60 Hz, 1 minute |
| Pollution Degree | 3 |
| Vibration Resistance | 5 to 55 Hz, amplitude 0.5 mm |
| Shock Resistance | 1000 m/s ² |
| Degree of Protection | IP67 (IEC60529) NEMA Type 4X Indoor Use Only (Note) |
| Housing Color | Black |
| LED Lamp Life | Approx. 50,000 hours (When used on complete DC at 25°C, brightness reduces to 50% of the initial intensity.) |
| Weight | 140g (jumbo dome type, 1m cable) 50g (dome type, 1m cable) 50g (flat type, 1m cable) |

Note: Jumbo dome type is NEMA Type 1 under UL listing.

Jumbo Dome Type

Types

Package Quantity: 1

| Shape | Types | Ordering Type No. | Illumination Color |
|--|-----------|-------------------|--------------------|
|  Jumbo Dome (ø66) One color | Cable | 1m | LH1D-D3HQ4C10① |
| | | 3m | LH1D-D3HQ4C30① |
| | Connector | | LH1D-D3HQ4CN1① |
|  Jumbo Dome (ø66) 2-color alternate | Cable | 1m | LH1D-D3HQ4C10①② |
| | | 3m | LH1D-D3HQ4C30①② |
| | Connector | | LH1D-D3HQ4CN1①② |
|  Jumbo Dome (ø66) 3-color alternate | Cable | 1m | LH1D-D3HQ4C10①②③ |
| | | 3m | LH1D-D3HQ4C30①②③ |
| | Connector | | LH1D-D3HQ4CN1①②③ |



Specify a color code in place of ① in the Type No.
Color code: A, G, PW, R, S, W, Y

Specify a color code in place of ①/② in the Type No.
Color code: R/G, G/W, R/W, A/G, A/W, R/PW, G/PW, A/PW
(Two-color alternate)

Specify a color code in place of ①/②/③ in the Type No.
Color code: R/G/W, R/G/PW
(Three-color alternate)

- Color code: A (amber), G (green), PW (pure white), R (red), S (blue), W (white), Y (yellow).
- For orange, specify "A" (for amber).

Dimensions




Lens Colors


| | Illumination Color | Lens Color |
|-----------------------|--|---|
| One Color | Amber (A) Green (G) Pure White (PW) Red (R) Blue (S) White (W) Yellow (Y) | Amber Green White Red Blue White Yellow |
| Two-color Alternate | Red (R) / Green (G) Green (G) / White (W) Red (R) / White (W) Amber (A) / Green (G) Amber (A) / White (W) Red (R) / Pure White (PW) Green (G) / Pure White (PW) Amber (A) / Pure White (PW) | White White White White White White White |
| Three-color Alternate | Red (R) / Green (G) / White (W) Red (R) / Green (G) / Pure White (PW) | White White |

Internal Circuit


• One-color Illumination



• Two-color Alternate Illumination




• Three-color Alternate Illumination



LED Module Internal Circuit

The schematic of the LED module internal circuit differ depending on the illumination color.

• Illumination color: A, R, W • Illumination color: G, PW, S





Note: For the schematic of the LED module, see "LED Module Internal Circuit" on the right.

LH Series Surface Mount Indicators

Dome Type


Types

Package Quantity: 1

| Shape | Cable | Ordering Type No. | Illumination Color |
|--|-------|-------------------|--|
| Dome ø37 One Color  | 1m | LH1D-D2HQ4C10① | Specify a color code in place of ① in the Type No. A: amber G: green PW: pure white R: red S: blue W: white Y: yellow |
| | 3m | LH1D-D2HQ4C30① | |
| | 5m | LH1D-D2HQ4C50① | |
| Dome ø37 Red/Green 2-color alternate  | 1m | LH1D-D2HQ4C10RG | R (red) / G (green) 2-color alternate illumination |
| | 3m | LH1D-D2HQ4C30RG | |
| | 5m | LH1D-D2HQ4C50RG | |

•For orange, specify "A" (for amber).


Dimensions




All dimensions in mm.

Internal Circuit

• One-color Illumination



• Two-color Alternate Illumination




Lens Colors

| Illumination Type | Illumination Color | Lens Color |
|---------------------|---------------------|--------------|
| One Color | Amber (A) | Amber |
| | Green (G) | Green |
| | Pure White (PW) | Clear (Note) |
| | Red (R) | Red |
| | Blue (S) | Blue |
| | White (W) | Clear (Note) |
| | Yellow (Y) | Yellow |
| Two-color Alternate | Red (R) / Green (G) | Clear (Note) |

Note: Because lenses have a white diffusion cover inside, pure white, white, and red/green types appear white when the light is off.

LED Module Internal Circuit





Note: For the schematic of the LED module, see "LED Module Internal Circuit" on the right.

Flat Type


Types

Package Quantity: 1

| Shape | Cable | Ordering Type No. | Illumination Color |
|---|-------|------------------------|--|
| Flat One Color  | 1m | LH1D-H2HQ4C10 ⓪ | Specify a color code in place of ⓪ in the Type No. A: amber G: green PW: pure white R: red S: blue W: white Y: yellow |
| | 3m | LH1D-H2HQ4C30 ⓪ | |
| | 5m | LH1D-H2HQ4C50 ⓪ | |
| Flat Red/Green 2-color Alternate  | 1m | LH1D-H2HQ4C10RG | R (red) / G (green) 2-color alternate illumination |
| | 3m | LH1D-H2HQ4C30RG | |
| | 5m | LH1D-H2HQ4C50RG | |


• For orange, specify "A" (for amber).

Dimensions



Internal Circuit


• One-color Illumination



Cable color: White


Cable color: Brown

• Two-color Alternate Illumination



Cable color: White
LED color: Green


Cable color: Brown (common)



Cable color: Green
LED color: Red


Lens Colors

| Illumination Type | Illumination Color | Lens Color |
|---------------------|--------------------|------------|
| One Color | Amber (A) | Amber |
| | Green (G) | Green |
| | Pure White (PW) | Clear |
| | Red (R) | Red |
| | Blue (S) | Blue |
| | White (W) | Clear |
| | Yellow (Y) | Yellow |
| Two-color Alternate | Red/Green | Clear |



All dimensions in mm.

Replacement Parts

| Shape | Material | Ordering Type No. | Lens Color |
|---|-------------|---------------------|--|
| Lens (flat type)  | Polyarylate | LH9Z-1DLH2 ⓪ | For flat type. Specify a color code in place of ⓪ in the Type No. A: amber C: clear G: green R: red S: blue Y: yellow Note: Use C (clear) lens for R / G (red/green alternate), W (white), or PW (pure white) illumination. |


LH Series Surface Mount Indicators

Safety Precautions

- Do not disassemble, repair, or modify the LH1D indicator, otherwise electric shock, damage, fire, or malfunction may occur.
- Do not pull out or push in the cable of the LH1D indicator, otherwise damage may occur. Provide a slack in the cable while wiring.
- The LH1D indicator is a general-purpose and industrial electronic device. Do not use the LH1D indicator for electronic equipment which may damage the human body or threaten life in case of malfunction or failure.


Operating Instructions

- LED elements may vary in colors and brightness.
- The LH1D indicator is vulnerable to static electricity. Take sufficient protection against static electricity and spikes.
- For one-color illumination of cable types, the green wire is cut short because it is not used. When cutting the cable for shorter wiring, cut the green wire short or make sure that the green wire is not used.
- The pin layout of connector type is shown at the right.



- Excessive shock to the LH1D may cause damage or failure, and the internal lens may fall off even if no detects are found externally. The internal lens may have fallen off when:
 - The illumination varies greatly when viewed from the side.
 - The indicator makes a rattling sound when shaken lightly.
 When any of the above is observed, contact IDEC.


Note: Do not remove the lens.
The specified degree of protection cannot be assured when the lens is removed.



Panel Mounting

Using two M3 screws (M5 screws for jumbo dome types), install the LH1D indicator to a mounting surface. Tighten the screws to a torque of 0.6 N·m maximum (1.0 to 1.4 N·m for jumbo dome types). Mounting screws are not provided and must be supplied by the user.

Jumbo Dome Type




Note 1: Take into account the thickness of the base (10.5 mm), when selecting the length of the screws.

Note 2: Take appropriate anti-loosening measures such as spring washers and screw locks.


Note 3: Install the LH1D using two M5 screws, one each on the top and the bottom.

Dome Type



Note: The dome lens is not removable. Do not attempt to remove the lens, otherwise damage will occur.

Flat Type




Note 1: Do not install the LH1D indicator by attaching only the lens, such as by taping down the lens. Otherwise internal components may come loose.


Note 2: Make sure that the back of the indicator is securely attached to the mounting surface, so that the lens cannot be easily removed.

Inserting Marking Film into Flat Type Lens


- Insert a flat screwdriver into the groove between the base and lens. Do not use flat screwdrivers with a tip width of 1.0 mm or more.




- Twist the screwdriver and disengage the lens from the base.




- Remove the lens from the base.



- Insert the edge of a marking film into the gap between the base and the diffusion plate, and place the marking film on top of the diffusion plate.




- Install the lens. Ensure that the lens is installed snugly.



Note 1: Do not touch the gasket, as this may affect its waterproof characteristics.
Note 2: Do not touch the diffusion plate.

Markings

Legends and symbols can be printed on marking film for the flat lens. One 0.1mm-thick film can be installed. Marking film is not attached and must be supplied by the user. Recommended marking film: Polyester



Specifications and other descriptions in this catalog are subject to change without notice.



IDEC CORPORATION

IDEC CORPORATION (USA)
Tel: +1-408-747-0550 / (800) 262-1DEEC (4332)
E-mail: opencontact@idec.com

IDEC CANADA LIMITED
Tel: +1-905-890-8561, Toll Free: (888) 317-4332
E-mail: sales@ca.idec.com

IDEC AUSTRALIA PTY. LTD.
Tel: +61-3-9763-3244, Toll Free: 1800-68-4332
E-mail: sales@au.idec.com

IDEC ELECTRONICS LIMITED
Tel: +44-1256-321000 E-mail: sales@uk.idec.com

IDEC ELEKTROTECHNIK GmbH
Tel: +49-40-25 30 54 - 0 E-mail: service@idec.de

IDEC (SHANGHAI) CORPORATION
Tel: +86-21-5353-1000 E-mail: idec@cn.idec.com

IDEC (BEIJING) CORPORATION
Tel: +86-10-6581-6131

IDEC (SHENZHEN) CORPORATION
Tel: +86-755-8356-2977

IDEC IZUMI (H.K.) CO., LTD.
Tel: +852-2803-8989 E-mail: info@hk.idec.com

IDEC TAIWAN CORPORATION
Tel: +886-2-2698-3929 E-mail: service@tw.idec.com

IDEC IZUMI ASIA PTE. LTD.
Tel: +65-6746-1155 E-mail: info@sg.idec.com