

Contact insert - HC-B 24-I-CT-M - 1648335

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



HEAVYCON male insert, B24 series, 24-pos., for crimp contacts. PE connection using tension sleeve technology.

Product Features

- ✓ For fast coding with plastic profile
- ✓ PE connection using tension sleeve technology

Key commercial data

package_quantity	10
GTIN	4046356092463

Technical data

General

Note	For HEAVYCON ADVANCE and HEAVYCON housing of B24 type, crimp contacts CK 2,5-ED (crimp contacts not included in the scope of supply).
Connection method	Crimp connection
Pollution degree	3
Surge voltage category	III
Constructional and testing regulations	DIN EN 61984
Constructional and testing regulations	DIN EN 60664
Constructional and testing regulations	IEC 60352
Number of positions	24+PE
Insertion/withdrawal cycles	≥ 500
Design	B24
Connection in acc. with standard	IEC / EN
Conductor cross section	0.5 mm ² ... 4 mm ²
Connection cross section AWG	20 ... 12
Stripping length of the individual wire	7.5 mm
Assembly instructions	Coding also using the CP-HC (1686478) coding profiles. HC-B6../HC-B10..for two coding profiles. HC-B16../HC-B24..for four coding profiles.
Connection	For housing design B24. Connectors may only be inserted when there is no load/the power is switched off. Use a screwdriver to remove the crimp contacts. The opening for the screwdriver is next to the opening where the conductor is inserted.

Contact insert - HC-B 24-I-CT-M - 1648335

Technical data

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C (including heating up of contacts)
Degree of protection	IP20

Material data

Inflammability class according to UL 94	V0
Contact material	Copper alloy
Contact surface material	Ag (alternatively Au)
Contact carrier material	PA

Electrical characteristics

Rated voltage (III/3)	500 V
Rated surge voltage	6 kV
Rated current	16 A

classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440209

ETIM

ETIM 3.0	EC000438
ETIM 4.0	EC000438
ETIM 5.0	EC000438

UNSPSC

UNSPSC 6.01	30211923
UNSPSC 7.0901	39121522
UNSPSC 11	39121522
UNSPSC 12.01	39121522
UNSPSC 13.2	39121522

approvals

CSA / UL Recognized / cUL Recognized / cULus Recognized /

Approval details

Contact insert - HC-B 24-I-CT-M - 1648335

approvals

CSA 	
Nominal voltage UN	600 V
Nominal current IN	20 A
mm ² /AWG/kcmil	20-12

UL Recognized 	
Nominal voltage UN	600 V
Nominal current IN	13 A
mm ² /AWG/kcmil	22-14

cUL Recognized 	
Nominal voltage UN	600 V
Nominal current IN	13 A
mm ² /AWG/kcmil	22-14

cULus Recognized 	
--	--

accessories

Mounting material

HC-B-PES - 1604997



Contact insert - HC-B 24-I-CT-M - 1648335

accessories

HC-B-3PE - 1644326



HC-B-ZG - 1685327



HC-B-ZS - 1685330



Coding element

CP-HC - 1686478



HC-CBU - 1676860



Contact insert - HC-B 24-I-CT-M - 1648335

accessories

HC-CB - 1772722



HC-CST - 1676857



Plug assembly frame

HC-SMR-B24 - 1687985



Plug mounting plate

HC-SMP 150-B24-AMQ - 1660944



Docking frame

HC-B 24-ANDOCK - 1586141



Contact insert - HC-B 24-I-CT-M - 1648335

accessories

Assembly tool

CK2,5-EWZ - 1662722



Crimping tool

CRIMPFOX-1,6/2,5-ED-4,0 - 1687419



Crimp contact

CK2,5-ED-0,50ST AG - 1663572



CK2,5-ED-0,75ST AG - 1663585



CK2,5-ED-1,00ST AG - 1663598



Contact insert - HC-B 24-I-CT-M - 1648335

accessories

CK2,5-ED-1,50ST AG - 1663608



CK2,5-ED-2,50ST AG - 1663611



CK2,5-ED-3,00ST AG - 1663624



CK2,5-ED-4,00ST AG - 1663637



CK2,5-ED-0,50ST AU - 1674804



CK2,5-ED-1,00ST AU - 1674781



Contact insert - HC-B 24-I-CT-M - 1648335

accessories

CK2,5-ED-1,50ST AU - 1674778



CK2,5-ED-2,50ST AU - 1674817



CK2,5-ED-4,00ST AU - 1674794



accessories

CK2,5-ED-0,37ST AG - 1585650




CK2,5-ED-0,37ST AU - 1585663



Drawings


Contact insert - HC-B 24-I-CT-M - 1648335

Diagram



Derating diagram


Dimensioned drawing



Male insert

Contact insert - HC-B 24-I-CT-M - 1648335


Dimensioned drawing



Panel cutout

Contact insert - HC-B 24-I-CT-M - 1648335

Schematic diagram



Connector pin assignment, connection side

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>