

Label - EML (26,5X18,5)R SR - 0816906

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Label, Roll, silver/matt, Unlabeled, Can be labeled with: THERMOMARK ROLL, THERMOMARK X, THERMOMARK S1.1, Mounting type: Adhesive, Lettering field: 26.5 x 18.5 mm

The figure shows the EML (15X9)R SR product variant

Product Features

- ✓ A wide range of marker sizes and colors are available for custom designs
- ✓ Precise printing quality and good adhesive properties
- ✓ If high-quality ink ribbons are used, the labeling is resistant to solvents and suitable for use even under harsh industrial conditions
- ✓ The EML ... materials are UL-listed
- ✓ The special packaging protects rolls that have already been started from the dirt found in industrial environments
- ✓ The EML ... self-adhesive device markers have been specifically developed for marking various types of operating equipment in control, system, and control cabinet engineering

Key commercial data

package_quantity	1
GTIN	4046356107822

Technical data

Dimensions

Length (b)	26.5 mm
Width (a)	18.5 mm

Ambient conditions

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Ambient temperature (operation)	-40 °C ... 150 °C
Ambient temperature (assembly)	5 °C
Recommended storage conditions	22 °C / 50 % relative humidity

General

Color	silver/matt
Components	free from silicone and halogen
Material	Polyester
Material	Polyester
Number of individual labels	2500
Number of individual labels per row	3

Label - EML (26,5X18,5)R SR - 0816906

Technical data

General

RoHS compliant	Yes
Adhesive	Acrylic
File number	MH 48542
Printability	Thermal transfer
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN ISO 9227:2012-09
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	DIN 50018:1997-06
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result	Test passed
Foil strength	50 µm
Adhesive strength	24 µm

classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27149103
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410

Label - EML (26,5X18,5)R SR - 0816906

classifications

UNSPSC

UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

approvals

UL Recognized /

Approval details

UL Recognized 

accessories

Ink ribbon

THERMOMARK-RIBBON 110 - 5145384



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>