

Bus system connector - SACC-M12MRD-4Q SH PN - 1554539

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Bus system connector, PROFINET CAT5, PROFINET CAT5e, 4-position, shielded, Plug angled M12, D-coded, Insulation displacement connection, Knurl material: Nickel-plated brass, External cable diameter 4 mm ... 8 mm

Product Features

- ✓ Safe use in the field, thanks to a high degree of protection
- ✓ Flexible: connectors for on-site assembly
- ✓ Insulation displacement connection: innovative and time-saving assembly without stripping the single wire
- ✓ Reliable signal transmission - 360° shielding in environments with electromagnetic interference



Key commercial data

package_quantity	1
GTIN	4046356166225

Technical data

Dimensions

External diameter	4 mm ... 8 mm
Stripping length of the sheath	35 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
Degree of protection	IP67

General

Note	This product corresponds to the PROFINET Cabling and Interconnection Technology Guideline for PROFINET regulations, version 2.00, order no: 2.252, Chapter 8.2 Connectors for Outside Environment (Balanced cabling)
Rated current at 40°C	1.75 A
Rated voltage	60 V
Number of positions	4
Contact resistance	≤ 5 mΩ
Insulation resistance	≥ 100 MΩ
Coding	D - data
Standards/regulations	M12 connector IEC 61076-2-101
Signal type/category	PROFINET CAT5 (IEC 11801:2002)

Bus system connector - SACC-M12MRD-4Q SH PN - 1554539

Technical data

General

Signal type/category	PROFINET CAT5e (TIA 568B:2001)
Status display	No
Surge voltage category	II
Pollution degree	3
Connection method	Insulation displacement connection
Conductor cross section	0.14 mm² ... 0.34 mm²
AWG conductor cross section	26 ... 22
Frequency of connections between conductors of the same cross section	≤ 10
Insertion/withdrawal cycles	≥ 100
Torque	0.4 Nm (M12 knurl)
Assembly instructions	The connector pin assignment can be rotated 45° to the cable outlet

Material

Inflammability class according to UL 94	V0
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	PA 66
Material of grip body	Zinc die-cast, nickel-plated
Material, knurls	Nickel-plated brass
Sealing material	Neoprene

classifications

eCl@ss

eCl@ss 4.0	27060306
eCl@ss 4.1	27060306
eCl@ss 5.0	27061801
eCl@ss 5.1	27061801
eCl@ss 6.0	27061801
eCl@ss 7.0	27061801
eCl@ss 8.0	27061801

ETIM

ETIM 3.0	EC002062
ETIM 4.0	EC002062
ETIM 5.0	EC002062

UNSPSC

UNSPSC 6.01	31251501
UNSPSC 7.0901	31251501
UNSPSC 11	31251501
UNSPSC 12.01	31251501

Bus system connector - SACC-M12MRD-4Q SH PN - 1554539

classifications

UNSPSC

UNSPSC 13.2	31251501
-------------	----------

approvals

GOST /

Approval details

GOST



accessories

Torque tool

TSD 04 SAC - 1208429



TSD-M 1,2NM - 1212224



Screwdriver tools

SACC BIT M12-D20 - 1208445



Bus system connector - SACC-M12MRD-4Q SH PN - 1554539

accessories

TSD-M SAC-BIT ADAPTER - 1212600



Protective cap

PROT-M12 FS-PA-CHAIN - 1430873



Data cable by the meter

VS-OE-OE-93B/... - 1417362



VS-OE-OE-93C/... - 1417491



VS-OE-OE-93R/... - 1417388



Bus system connector - SACC-M12MRD-4Q SH PN - 1554539

accessories

VS-OE-OE-936/... - 1417375



VS-OE-OE-937/... - 1402687



Stripping tool

WIREFOX-D 40 - 1212161



accessories


MICROFOX SC - 1205862



Drawings

Bus system connector - SACC-M12MRD-4Q SH PN - 1554539


Dimensioned drawing



M12 x 1 male plug, angled, shielded

Bus system connector - SACC-M12MRD-4Q SH PN - 1554539

Schematic diagram



Pin assignment M12 male connector, 4-pos., D-coded, male side

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>