

Flush-type connector - SACC-DSI-M12MS-12CON-M12 - 1553488

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Sensor/actuator flush-type plug, 12-pos., M12, rear/screw mounting with M12 thread, with straight solder connection

Key commercial data

package_quantity	20
GTIN	4046356157278

Technical data

Ambient conditions

Ambient temperature (operation)	-25 °C ... 85 °C (Plug)
Degree of protection	IP67

General

Rated current at 40°C	1.5 A
Rated voltage	30 V
Number of positions	12
Contact resistance	≤ 3 mΩ
Insulation resistance	≥ 100 MΩ
Standards/regulations	M12 connector IEC 61076-2-101
Signal type/category	Universal
Status display	No
Surge voltage category	II
Pollution degree	3
Connection method	Solder pins

Material

Inflammability class according to UL 94	V0
---	----

classifications

eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27143423
eCl@ss 5.1	27143423

Flush-type connector - SACC-DSI-M12MS-12CON-M12 - 1553488

classifications

eCl@ss

eCl@ss 6.0	27143423
eCl@ss 7.0	27449001
eCl@ss 8.0	27449001

ETIM

ETIM 3.0	EC002061
ETIM 4.0	EC002062
ETIM 5.0	EC002062


UNSPSC

UNSPSC 6.01	31251501
UNSPSC 7.0901	31251501
UNSPSC 11	31251501
UNSPSC 12.01	31251501
UNSPSC 13.2	39121413

Drawings


Flush-type connector - SACC-DSI-M12MS-12CON-M12 - 1553488

Drilling diagram



Flush-type connector - SACC-DSI-M12MS-12CON-M12 - 1553488


Dimensioned drawing



M12 flush-type connector

Flush-type connector - SACC-DSI-M12MS-12CON-M12 - 1553488

Schematic diagram



Pin assignment M12 male connector, 12-pos., male side view

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>