


Ground modular terminal block - MT 1,5-TWIN-PE - 3001705

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Ground modular terminal block, Cross section: 0.14 mm² - 1.5 mm², AWG: 26 - 16, Connection type: Screw connection, Width: 4.2 mm, Color: green-yellow, Mounting type: NS 15

Product Features

- ☒ Low contact resistance
- ☒ Corrosion-free terminal points
- ☒ Green-yellow housing
- ☒ Captive terminal block screws

Key commercial data

package_quantity	50
GTIN	4017918107215

Technical data

General

Note	When aligning with a feed-through terminal block of the same shape, an end cover must be interposed for insulation voltages of > 320 V
Number of levels	2
Number of connections	3
Color	green-yellow
Insulating material	PA
Inflammability class according to UL 94	V0

General

Rated surge voltage	4 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 60947-7-2
Open side panel	nein

Dimensions

Width	4.2 mm
Length	28 mm

Connection data

Ground modular terminal block - MT 1,5-TWIN-PE - 3001705

Technical data

Connection data

Conductor cross section solid min.	0.14 mm ²
Conductor cross section solid max.	1.5 mm ²
Conductor cross section stranded min.	0.14 mm ²
Conductor cross section stranded max.	1.5 mm ²
Conductor cross section AWG/kcmil min.	26
Conductor cross section AWG/kcmil max	16
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.25 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	0.75 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.25 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	0.75 mm ²
2 conductors with same cross section, solid min.	0.14 mm ²
2 conductors with same cross section, solid max.	0.5 mm ²
2 conductors with same cross section, stranded min.	0.14 mm ²
2 conductors with same cross section, stranded max.	0.5 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	0.25 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	0.34 mm ²
Connection method	Screw connection
Stripping length	6 mm
Internal cylindrical gage	A 1
Screw thread	M2
Tightening torque, min	0.22 Nm
Tightening torque max	0.25 Nm

classifications

eCl@ss

eCl@ss 4.0	27141118
eCl@ss 4.1	27141118
eCl@ss 5.0	27141118
eCl@ss 5.1	27141118
eCl@ss 6.0	27141141
eCl@ss 7.0	27141141
eCl@ss 8.0	27141141

ETIM

ETIM 2.0	EC000901
ETIM 3.0	EC000901
ETIM 4.0	EC000901

Ground modular terminal block - MT 1,5-TWIN-PE - 3001705

classifications

ETIM

ETIM 5.0	EC000901
-----------------	----------

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

approvals

CSA / UL Recognized / KEMA-KEUR / GOST / LR / GL / BV / DNV / CCA / GOST /

Approval details

CSA 	
Nominal voltage UN	
Nominal current IN	
mm²/AWG/kcmil	28-14

UL Recognized 	
Nominal voltage UN	
Nominal current IN	
mm²/AWG/kcmil	30-14

KEMA-KEUR 	
Nominal voltage UN	
Nominal current IN	
mm²/AWG/kcmil	1.5

GOST 	
---	--

Ground modular terminal block - MT 1,5-TWIN-PE - 3001705

approvals


LR

GL

BV

DNV

CCA	
Nominal voltage UN	
Nominal current IN	
mm²/AWG/kcmil	1.5



accessories

Screwdriver tools

SZS 0,4X2,5 VDE - 1205037



Mounting rail

NS 15 UNPERF 2000MM - 1401695



Ground modular terminal block - MT 1,5-TWIN-PE - 3001705

accessories

NS 15 PERF 2000MM - 1401682



NS 15 AL PERF 2000MM - 1401763



NS 15 WH PERF 2000MM - 1204096



Terminal marking

ZBF 4:UNBEDRUCKT - 0808587



UC-TMF 4 - 0818166



Ground modular terminal block - MT 1,5-TWIN-PE - 3001705

accessories

UCT-TMF 4 - 0828742



Labeled terminal marker

ZBF 4 CUS - 0825023



UC-TMF 4 CUS - 0824630




UCT-TMF 4 CUS - 0829651



Drawings

Ground modular terminal block - MT 1,5-TWIN-PE - 3001705

Circuit diagram



© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>