

Protective covers - HC-B 32-SD-FQU/FS - 1646120

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



HEAVYCON protective cover, type B32, for supporting base element with double locking latch, with retaining cord, IP54, PA

Key commercial data

package_quantity	10
GTIN	4017918927301

Technical data

Dimensions

Diameter of retaining cord eyelet	30 mm
-----------------------------------	-------

Ambient conditions

Degree of protection	IP54
Ambient temperature (operation)	-20 °C ... 100 °C

General

Design	B32
Type	For supporting base element with double locking latch
Inflammability class according to UL 94	HB
Seal present	No
Connection	Plastic protective cover for short-term protection

classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440209

ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437

Protective covers - HC-B 32-SD-FQU/FS - 1646120

classifications

ETIM


ETIM 4.0	EC000437
ETIM 5.0	EC000437

UNSPSC

UNSPSC 6.01	30212113
UNSPSC 7.0901	39121712
UNSPSC 11	39121712
UNSPSC 12.01	39121712
UNSPSC 13.2	39121712

Drawings

Dimensioned drawing



Protective cover, B32