

## Plastic label - US-EMLP (60X30) - 0828805

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Plastic label, Card, white, Unlabeled, Can be labeled with: THERMOMARK CARD PLUS, THERMOMARK CARD, Mounting type: Adhesive, Lettering field: 60 x 30 mm

The illustration shows a version of the product

### Product Features

- The markers, which are supplied in uniform sheets, can be labeled quickly, easily, and cost-effectively using the THERMOMARK CARD
- The US-EMLP ... UniSheet labeling range includes self-adhesive device markers with good adhesive properties
- The perforated markers are easy to separate and can be easily fitted
- The sheets provide space for including function texts

### Key commercial data

<b>package_quantity</b>	10
<b>GTIN</b>	4046356559133

### Technical data

#### Dimensions

<b>Length (b)</b>	59.7 mm
<b>Height</b>	0.5 mm
<b>Width (a)</b>	14.9 mm

#### Ambient conditions

<b>Wipe resistance</b>	DIN EN 61010-1 (VDE 0411-1)
<b>Ambient temperature (operation)</b>	-30 °C ... 80 °C

#### General

<b>Color</b>	white
<b>Components</b>	Silicone-free
<b>Inflammability class according to UL 94</b>	V0
<b>Material</b>	PVC
<b>Number of individual labels</b>	4
<b>Number of individual labels per row</b>	1

### classifications

eCl@ss

## Plastic label - US-EMLP (60X30) - 0828805

### classifications

#### eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27141137
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

#### ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

#### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

### accessories

#### Magazine

THERMOMARK CARD-US-MAG1 - 5146451



---

### Drawings

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>