

Contact insert - HC-HS 2-D7-EBUS - 1586264

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



HEAVYCON female insert, HS2 series, 2+PE-pos., axial screw connection

Key commercial data

package_quantity	10
GTIN	4046356410212

Technical data

General

Note	For housing HC-D7
Connection method	Axial screw connection
Tightening torque	1.8 Nm
Pollution degree	3
Surge voltage category	III
Constructional and testing regulations	DIN VDE 0627/86
Constructional and testing regulations	DIN VDE 0110/02.79
Constructional and testing regulations	DIN VDE 0110-1/04.97
Constructional and testing regulations	IEC 60664-1, DIN IEC 60512
Constructional and testing regulations	IEC 60352
Number of positions	2+PE
Insertion/withdrawal cycles	≥ 500
Design	D7
Conductor cross section	4 mm² ... 10 mm²
Connection cross section AWG	10 ... 8
Stripping length of the individual wire	8 mm +1
Assembly instructions	-The axial screw connection must be established using a 2 mm Allen wrench.-Use only stranded wires for axial screw connection.- Plug-in connections may only be operated only when there is no load/voltage.
Connection	Note regarding axial connection technology: Only for stranded wires. The specified conductor cross sections refer to the geometric cross section of the cable used.Use of cables with a geometric cross section very different from the cable's nominal cross section should be checked before use.The wiring space of the axial screw method is established for fine strand cables in accordance with VDE 0295 Class 5. Deviating cable structures (e.g., Class 6 cables) should be checked before use.Assembly

Contact insert - HC-HS 2-D7-EBUS - 1586264

Technical data

General

	<p>instructions Before assembly, ensure that the tapered screw is turned back all the way (chamber is open). The cables must not be twisted. The wires should be inserted as far as they will go into the contact chamber (until the insulation touches the contact). Hold the wires in position and use the socket wrench to tighten. The used wire end should be cut off before connecting again. The connection screw may only be retightened once to prevent the litz wires from breaking. To prevent damage to the contact, the wire/cable should be mechanically intercepted at an appropriate distance from the connection point (e.g., by using a plate cutout). DIN VDE 0100-520:2003-06 contains information on how to do this correctly. When not using PE contacts: set the PE contact as far as possible in a clockwise direction.</p>
--	---

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C (including heating up of contacts)
--	--

Material data

Inflammability class according to UL 94	V0
Contact material	Copper alloy
Contact surface material	Ag
Contact carrier material	PC

Electrical characteristics

Rated voltage (III/3)	400 V
Rated surge voltage	6 kV
Rated current	40 A

classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440209

ETIM

ETIM 3.0	EC000438
ETIM 4.0	EC000438
ETIM 5.0	EC000438

UNSPSC

UNSPSC 6.01	30211923
UNSPSC 7.0901	39121522
UNSPSC 11	39121522
UNSPSC 12.01	39121522

Contact insert - HC-HS 2-D7-EBUS - 1586264

classifications

UNSPSC

UNSPSC 13.2	39121522
--------------------	----------

approvals

UL Recognized / cUL Recognized / GOST / cULus Recognized /

Approval details

UL Recognized	
Nominal voltage UN	600 V
Nominal current IN	28 A
mm ² /AWG/kcmil	

cUL Recognized	
Nominal voltage UN	600 V
Nominal current IN	28 A
mm ² /AWG/kcmil	


GOST

cULus Recognized

Drawings


Contact insert - HC-HS 2-D7-EBUS - 1586264

Diagram



Derating diagram: Series HC-HS2-D7-E...S


Dimensioned drawing




Female insert

Contact insert - HC-HS 2-D7-EBUS - 1586264

Schematic diagram



Schematic diagram



Axial connection