

Feed-through terminal block - ST 2,5-TWIN GN - 3037326

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Feed-through terminal block, Connection method: Spring-cage connection, Cross section: 0.08 mm² - 4 mm², AWG: 28 - 12, Width: 5.2 mm, Color: green, Mounting type: NS 35/7,5, NS 35/15

Product Features

- The consistent double function shaft offers every opportunity for time-saving potential distribution and accommodating test accessories
- User-friendly implementation of all potential branching tasks
- Space-saving and practical multi-conductor connection without additional bridges



Key commercial data

package_quantity	50
GTIN	4017918599720

Technical data

General

Number of levels	1
Number of connections	3
Color	green
Insulating material	PA
Inflammability class according to UL 94	V0

General

Maximum load current	28 A (with 4 mm ² conductor cross section)
Rated surge voltage	8 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 60947-7-1
Nominal current I _N	24 A (the maximum load current must not be exceeded by the total current of all connected conductors)
Nominal voltage U _N	800 V
Open side panel	ja

Dimensions

Feed-through terminal block - ST 2,5-TWIN GN - 3037326

Technical data

Dimensions

Width	5.2 mm
Length	60.5 mm
Height NS 35/7,5	36.5 mm

Connection data

Conductor cross section solid min.	0.08 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section AWG/kcmil min.	28
Conductor cross section AWG/kcmil max	12
Conductor cross section stranded min.	0.08 mm ²
Conductor cross section stranded max.	2.5 mm ²
Min. AWG conductor cross section, stranded	28
Max. AWG conductor cross section, stranded	14
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.14 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	2.5 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.14 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	2.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	0.5 mm ²
Connection method	Spring-cage connection
Minimum stripping length	8 mm
Maximum stripping length	10 mm
Internal cylindrical gage	A3

classifications

eCl@ss

eCl@ss 4.0	27141121
eCl@ss 4.1	27141121
eCl@ss 5.0	27141120
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27141120

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC000897
ETIM 5.0	EC000897

Feed-through terminal block - ST 2,5-TWIN GN - 3037326

classifications

UNSPSC


UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410


approvals


IECEX / ATEX / UL Recognized / cUL Recognized / GOST / LR / GL / BV / DNV / NK / GOST / VDE Gutachten mit Fertigungsüberwachung / IECEE CB Scheme / VDE Gutachten mit Fertigungsüberwachung / cULus Recognized /

Approval details

IECEX	
Nominal voltage UN	550 V
Nominal current IN	21.5 A
mm ² /AWG/kcmil	0.08-2.5

ATEX 	
Nominal voltage UN	550 V
Nominal current IN	25 A
mm ² /AWG/kcmil	0.08-4

UL Recognized 		
Usegroups	B	C
Nominal voltage UN	600 V	600 V
Nominal current IN	20 A	20 A
mm ² /AWG/kcmil	28-12	28-12

cUL Recognized 		
Usegroups	B	C
Nominal voltage UN	600 V	600 V
Nominal current IN	20 A	20 A
mm ² /AWG/kcmil	28-12	28-12

Feed-through terminal block - ST 2,5-TWIN GN - 3037326

approvals

GOST

LR

GL	
Nominal voltage UN	800 V
Nominal current IN	24 A
mm ² /AWG/kcmil	2.5

BV

DNV

NK

--

VDE Gutachten mit Fertigungsüberwachung	
Nominal voltage UN	800 V
Nominal current IN	24 A
mm ² /AWG/kcmil	0.2-2.5

IECEE CB Scheme	
Nominal voltage UN	800 V
Nominal current IN	
mm ² /AWG/kcmil	2.5

--

Feed-through terminal block - ST 2,5-TWIN GN - 3037326

approvals

Nominal voltage UN	800 V
Nominal current IN	24 A
mm ² /AWG/kcmil	0.2-2.5



accessories

Marker pen

B-STIFT - 1051993



X-PEN 0,35 - 0811228



End cover

D-ST 2,5-TWIN - 3030488



DS-ST 2,5 - 3036602



Feed-through terminal block - ST 2,5-TWIN GN - 3037326

accessories

D-ST 2,5-TWIN-0,8 OG - 3030512



DP PS-5 - 3036725



Test plug terminal block

RPS - 0201647



MPS-MT - 0201744



PAI-4-FIX-5/6 BU - 3035975



Feed-through terminal block - ST 2,5-TWIN GN - 3037326

accessories

PAI-4-FIX-5/6 OG - 3035974



PAI-4-FIX-5/6 YE - 3035977



PAI-4-FIX-5/6 RD - 3035976



PAI-4-FIX-5/6 GN - 3035978



PAI-4-FIX-5/6 BK - 3035980



PAI-4-FIX-5/6 GY - 3035982



Feed-through terminal block - ST 2,5-TWIN GN - 3037326

accessories

PAI-4-FIX-5/6 VT - 3035979



PAI-4-FIX-5/6 BN - 3035981



PS-5 - 3030983



PS-5/2,3MM RD - 3038723



Partition plate

ATP-ST-TWIN - 3030789



Screwdriver tools

Feed-through terminal block - ST 2,5-TWIN GN - 3037326

accessories

SZF 1-0,6X3,5 - 1204517



Documentation

ST-IL - 3039900



Bridge

FBS 20-5 - 3030226



FBS 10-5 - 3030213



FBS 5-5 - 3030190



Feed-through terminal block - ST 2,5-TWIN GN - 3037326

accessories

FBS 4-5 - 3030187



FBS 3-5 - 3030174



FBS 2-5 - 3030161



FBS 50-5 - 3038930



Mounting rail

NS 35/ 7,5 PERF 2000MM - 0801733



Feed-through terminal block - ST 2,5-TWIN GN - 3037326

accessories

NS 35/ 7,5 UNPERF 2000MM - 0801681



NS 35/ 7,5 WH PERF 2000MM - 1204119



NS 35/ 7,5 WH UNPERF 2000MM - 1204122



NS 35/ 7,5 AL UNPERF 2000MM - 0801704



NS 35/ 7,5 ZN PERF 2000MM - 1206421



NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



Feed-through terminal block - ST 2,5-TWIN GN - 3037326

accessories

NS 35/ 7,5 CU UNPERF 2000MM - 0801762



NS 35/ 7,5 CAP - 1206560



NS 35/15 PERF 2000MM - 1201730



NS 35/15 UNPERF 2000MM - 1201714



NS 35/15 WH PERF 2000MM - 0806602



Feed-through terminal block - ST 2,5-TWIN GN - 3037326

accessories

NS 35/15 WH UNPERF 2000MM - 1204135



NS 35/15 AL UNPERF 2000MM - 1201756



NS 35/15 ZN PERF 2000MM - 1206599



NS 35/15 ZN UNPERF 2000MM - 1206586



NS 35/15 CU UNPERF 2000MM - 1201895



NS 35/15 CAP - 1206573



Feed-through terminal block - ST 2,5-TWIN GN - 3037326

accessories

NS 35/15-2,3 UNPERF 2000MM - 1201798



Terminal marking

ZB 5 :UNBEDRUCKT - 1050004



UC-TM 5 - 0818108



UCT-TM 5 - 0828734



ZBF 5:UNBEDRUCKT - 0808642



Feed-through terminal block - ST 2,5-TWIN GN - 3037326

accessories

UC-TMF 5 - 0818153



UCT-TMF 5 - 0828744



Labeled terminal marker

ZB 5 CUS - 0824962



UC-TM 5 CUS - 0824581



UCT-TM 5 CUS - 0829595



Feed-through terminal block - ST 2,5-TWIN GN - 3037326

accessories

ZBF 5 CUS - 0825025



UC-TMF 5 CUS - 0824638



UCT-TMF 5 CUS - 0829658



Insulating sleeve

MPS-IH WH - 0201663



MPS-IH RD - 0201676



Feed-through terminal block - ST 2,5-TWIN GN - 3037326

accessories

MPS-IH BU - 0201689



MPS-IH YE - 0201692



MPS-IH GN - 0201702



MPS-IH GY - 0201728



MPS-IH BK - 0201731



ISH 2,5/0,2 - 3002843



Feed-through terminal block - ST 2,5-TWIN GN - 3037326

accessories

ISH 2,5/0,5 - 3002856



ISH 2,5/1,0 - 3002869



End block

CLIPFIX 35 - 3022218



CLIPFIX 35-5 - 3022276



E/NS 35 N - 0800886



Feed-through terminal block - ST 2,5-TWIN GN - 3037326

accessories

E/UK - 1201442



E/UK 1 - 1201413



Drawings

Circuit diagram



© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>