


Product Description

Conduit gland with high tensile strength for plastic conduits



Application range

- In combination with protective conduit
- SILVYN® SI
- SILVYN® SP
- SILVYN® SP-PU

Benefits

- Conduit gland with high tensile strength for plastic conduits

Design

- Metric connection thread
- Conduit entry with special grip profile

Note

- Necessary conduit clamp SILVYN® SCH

Product features

- High-tensile
- Robust
- Compact design



Technical Data

Material

Body: nickel-plated brass O-ring: NBR

Article List

Part number	Connection thread M	Clear opening (mm)	Overall length/ C (mm)	Thread length/ D (mm)	SW (mm)	Suitable for SILVYN® SCH	Suitable for SILVYN® SI	Suitable for SILVYN® SP	Suitable for SILVYN® SP-PU	Pieces / PU
SILVYN® SSV-M										
52002827	12 x 1.5/1	7.0	25.0	8.0	16	10 - 16 S	7.0 x 9.0			50
52002828	12 x 1.5/2	9.0	25.0	8.0	19	10 - 16 S	9.0 x 12.0			50
52002840	16/1 x 1.5	8.0	25.0	8.0	19	10 - 16 S	11 x 14	10 x 14	10 x 14	50
52002839	16/2 x 1.5	10.0	25.0	8.0	19	12 - 20 S	13 x 16	12 x 16	12 x 16	50
52002841	20/1 x 1.5	12.0	25.0	8.0	22	16 - 25 S	14 x 18			50
52002842	20/3 x 1.5	15.5	25.0	8.0	25	20 - 32 S	18 x 23			50
52002843	25x1.5	19.0	29.5	8.5	32	20 - 32 S	23 x 28	22 x 27	22 x 27	25
52002844	32 x 1.5	27.0	32.5	9.5	40	32 - 50 S	32 x 38	30 x 36	30 x 36	25
52002845	40x1.5	34.0	36.0	11.0	50	32 - 50 S		38 x 44	38 x 44	10
52002846	50 x 1.5	41.0	39.0	12.0	57	40 - 60 S		45 x 51		5
52002847	63 x 1.5	46.0	43.0	12.0	67	40 - 60 S		50 x 56		5

Footnote:

Photographs are not to scale and do not represent detailed images of the respective products.