



DATA SHEET	0162052
IEC compensating cable KN 5-022 L-CY 2x0,22	valid from : 01.12.2008

Application

The compensating cable KN 5-022 L-CY 2 x 0,22 mm² is a PVC insulated cable which transmits the thermo-electric voltage of NiCr/Ni thermocouples. It is for flexible use and fixed installation in dry and damp rooms. They may only be installed outdoors with UV protection and in observation of the max. permitted temperature range. The copper braiding screens the cable against electromagnetic interference.

Design

Conductor	0,22 mm ² (7 x 0,20 mm)
Conductor material	KCA alloying, accuracy class 2 according IEC 60584 Positive conductor: Fe (iron) Negative conductor: CuNi (cupronickel)
Core insulation	PVC compound
Core identification	Positive conductor: green Negative conductor: white
Core layering	Cores twisted together
Inner sheath	PVC compound, colour: green
Screening	tinned copper braiding
Outer sheath	PVC compound, colour: green

Electrical properties

Limiting deviation class 2 ± 100 µV (± 2,5 °C) / measuring point temperature +900 °C

Mechanical and thermal properties

Temperature range	occasional flexing: -5 °C up to +70 °C
Minimum bending radius	occasional flexing: 15 x cable diameter
Flammability	flame retardant in acc. to IEC 60332-1-2 resp. VDE 0482-332-1-2

Originator: Frank Hörtnagl / PD-KL Approved: Werner Körner / TE	Document: DB0162052EN	page 1 of 1
--------------------------------------------------------------------	----------------------------	-------------