

Product Information

Page 1 of 2


EPIC® ULTRA H-B 10 AG QB Valid: 07.02.2012


Housing H-B ULTRA: for higher functional reliability

Product Description

Optimum, low-resistance 360° screening; All-purpose due to high corrosion resistance and high environmental protection.; Space-saving due to compact dimensions; Faster than any other comparable system; High mechanical resistance









Application range

- In EMC-sensitive environments
- For fixed and flexible applications (e.g. machinery building, wind turbines)
- · Construction machinery
- · Electric motor manufacturing

Benefits

- · Optimum, low-resistance 360° screening
- All-purpose due to high corrosion resistance and high environmental protection.
- Space-saving due to compact dimensions
- · Faster than any other comparable system
- · High mechanical resistance

Product features

- Resistance to cyclic salt spray is tested according to IEC 68-2-52, severity level 2
- The hoods and surface-mount base are supplied with integrated SKINTOP® cable gland
- · Housings with the BRUSH addition come with BRUSH cable screen contacting
- Pluggable with standard housings
- Corrosion-resistant according to DIN EN 6988



Product Information

Page 2 of 2

EPIC® ULTRA H-B 10 AG QB

Valid: 07.02.2012

Technical Data

Material

Housing: nickel-plated zinc die-casting Lever and

bolts: stainless steel Sealing: NBR

Cable gland Body: nickel-plated brass Insert: PA

Seal: special elastomer **Protection rating**

IP 65

Temperature range

-40°C to +100°C

Article List

Part	Article	Pieces
number		/ PU
H-B housing: panel-mount base (double lever)		
70250213	ULTRA H-B 10 AG QB	1