

Feed-through terminal block - UKKB 10 - 2772077

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Feed-through terminal block, Cross section: 0.5 mm² - 16 mm², AWG: 20 - 6, Connection type: Screw connection, Width: 10.2 mm, Color: gray, Mounting type: NS 35/7,5, NS 35/15, NS 32

Product Features

- ✓ Design width of just 10.2 mm

Key commercial data

package_quantity	50
GTIN	4017918068240

Technical data

General

Number of levels	2
Number of connections	4
Color	gray
Insulating material	PA
Inflammability class according to UL 94	V0

General

Rated surge voltage	6 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 60947-7-1
Nominal current I _N	57 A
Nominal voltage U _N	500 V
Open side panel	ja
Shock protection test specification	DIN EN 50274 (VDE 0660-514):2002-11
Back of the hand protection	guaranteed
Finger protection	guaranteed
Surge voltage test setpoint	7.3 kV
Result of surge voltage test	Test passed
Power frequency withstand voltage setpoint	1.89 kV
Result of power-frequency withstand voltage test	Test passed

Feed-through terminal block - UKKB 10 - 2772077

Technical data

General

Checking the mechanical stability of terminal points (5 x conductor connection)	Test passed
Bending test rotation speed	10 rpm
Bending test turns	135
Bending test conductor cross section/weight	0.5 mm ² / 0.3 kg
Bending test conductor cross section/weight	10 mm ² / 2 kg
Bending test conductor cross section/weight	16 mm ² / 2.9 kg
Result of bending test	Test passed
Conductor cross section tensile test	0.5 mm ²
Tractive force setpoint	30 N
Conductor cross section tensile test	10 mm ²
Tractive force setpoint	90 N
Conductor cross section tensile test	16 mm ²
Tractive force setpoint	100 N
Tensile test result	Test passed
Tight fit on carrier	NS 35/NS 32
Setpoint	5 N
Result of tight fit test	Test passed
Requirements, voltage drop	≤ 3.2 mV
Result of voltage drop test	Test passed
Temperature-rise test	Test passed
Conductor cross section short circuit testing	10 mm ²
Short-time current	1.2 kA
Conductor cross section short circuit testing	16 mm ²
Short-time current	1.92 kA
Short circuit stability result	Test passed
Proof of thermal characteristics (needle flame) effective duration	30 s
Result of thermal test	Test passed
Temperature index, insulating material (DIN EN 60216-1 (VDE 0304-21))	130 °C
Static insulating material application in cold	-60 °C

Dimensions

Width	10.2 mm
Length	77.5 mm
Height NS 35/7,5	73 mm
Height NS 35/15	80.5 mm
Height NS 32	78 mm

Connection data

Conductor cross section solid min.	0.5 mm ²
Conductor cross section solid max.	16 mm ²

Feed-through terminal block - UKKB 10 - 2772077

Technical data

Connection data

Conductor cross section stranded min.	0.5 mm ²
Conductor cross section stranded max.	10 mm ²
Conductor cross section AWG/kcmil min.	20
Conductor cross section AWG/kcmil max	6
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.5 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	10 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.5 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	6 mm ²
2 conductors with same cross section, solid min.	0.5 mm ²
2 conductors with same cross section, solid max.	6 mm ²
2 conductors with same cross section, stranded min.	0.5 mm ²
2 conductors with same cross section, stranded max.	4 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	0.5 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	6 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	6 mm ²
Connection method	Screw connection
Stripping length	11 mm
Internal cylindrical gage	B 6
Screw thread	M4
Tightening torque, min	1.5 Nm
Tightening torque max	1.8 Nm

classifications

eCl@ss

eCl@ss 4.0	27141118
eCl@ss 4.1	27141118
eCl@ss 5.0	27141118
eCl@ss 5.1	27141118
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27141120

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897

Feed-through terminal block - UKKB 10 - 2772077

classifications

ETIM

ETIM 4.0	EC000897
ETIM 5.0	EC000897

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

approvals

CSA / UL Recognized / KEMA-KEUR / cUL Recognized / GOST / PRS / CCA / GOST / cULus Recognized /

Approval details

CSA 	
Nominal voltage UN	300 V
Nominal current IN	65 A
mm²/AWG/kcmil	24-6

UL Recognized 	
Nominal voltage UN	600 V
Nominal current IN	65 A
mm²/AWG/kcmil	24-6


KEMA-KEUR 	
Nominal voltage UN	500 V
Nominal current IN	
mm²/AWG/kcmil	10

cUL Recognized 	
--	--

Feed-through terminal block - UKKB 10 - 2772077

approvals

Nominal voltage UN	600 V
Nominal current IN	65 A
mm²/AWG/kcmil	24-6



CCA	
Nominal voltage UN	500 V
Nominal current IN	
mm²/AWG/kcmil	10



accessories

End cover

D-UKKB 10 - 3001394



Warning label printed

WS 5-10 - 1004429



Feed-through terminal block - UKKB 10 - 2772077

accessories

WS 4-10 - 1004225



Short-circuit connector

KSS 10 - 0310541



Terminal marking

SBS10:UNBEDRUCKT - 1007248



ZB 10:UNBEDRUCKT - 1053001



UC-TM 10 - 0818069



Feed-through terminal block - UKKB 10 - 2772077

accessories

UCT-TM 10 - 0829142



Insulating sleeve

IS-K 10 - 1303337



ISSBI 10-10 - 0301521



Bridge

KB- 10 - 0203205



FBI 2-10 - 0203483



Feed-through terminal block - UKKB 10 - 2772077

accessories

FBI 10-10 - 0203276



EB 2-10 - 0203153



EB 3-10 - 0203328



EB 10-10 - 0203137



SB 2-10/15 - 0203234



Mounting rail

Feed-through terminal block - UKKB 10 - 2772077

accessories

NS 32 PERF 2000MM - 1201002



NS 32 UNPERF 2000MM - 1201015



NS 35/ 7,5 PERF 2000MM - 0801733



NS 35/ 7,5 UNPERF 2000MM - 0801681



NS 35/ 7,5 WH PERF 2000MM - 1204119



NS 35/ 7,5 WH UNPERF 2000MM - 1204122



Feed-through terminal block - UKKB 10 - 2772077

accessories

NS 35/ 7,5 AL UNPERF 2000MM - 0801704



NS 35/ 7,5 ZN PERF 2000MM - 1206421



NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



NS 35/ 7,5 CU UNPERF 2000MM - 0801762



NS 35/ 7,5 CAP - 1206560



Feed-through terminal block - UKKB 10 - 2772077

accessories

NS 35/15 PERF 2000MM - 1201730



NS 35/15 UNPERF 2000MM - 1201714



NS 35/15 WH PERF 2000MM - 0806602



NS 35/15 WH UNPERF 2000MM - 1204135



NS 35/15 AL UNPERF 2000MM - 1201756



NS 35/15 ZN PERF 2000MM - 1206599



Feed-through terminal block - UKKB 10 - 2772077

accessories

NS 35/15 ZN UNPERF 2000MM - 1206586



NS 35/15 CU UNPERF 2000MM - 1201895



NS 35/15 CAP - 1206573



NS 35/15-2,3 UNPERF 2000MM - 1201798



Labeled terminal marker

ZB 10 CUS - 0824941



Feed-through terminal block - UKKB 10 - 2772077

accessories

UC-TM 10 CUS - 0824605



UCT-TM 10 CUS - 0829623



End block

CLIPFIX 35 - 3022218



CLIPFIX 35-5 - 3022276



E/NS 35 N - 0800886



Feed-through terminal block - UKKB 10 - 2772077

accessories

E/UK - 1201442



E/UK 1 - 1201413



Test socket

PSBJ 4/15/6 FARBLOS - 0303419



PSBJ 4/15/6 WH - 0303312



PSBJ 4/15/6 RD - 0303325



Feed-through terminal block - UKKB 10 - 2772077

accessories

PSBJ 4/15/6 BU - 0303354



PSBJ 4/15/6 YE - 0303367



PSBJ 4/15/6 GN - 0303370



PSBJ 4/15/6 VT - 0303383



PSBJ 4/15/6 GY - 0303396



PSBJ 4/15/6 BK - 0303406



Feed-through terminal block - UKKB 10 - 2772077

accessories

PSB 4/7/6 - 0303299



Drawings

Circuit diagram



© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>