

# Feed-through terminal block - PT 2,5-TWIN/1P - 3209633

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Feed-through terminal block, Connection method: Push-in / plug connection, Cross section: 0.14 mm<sup>2</sup> - 4 mm<sup>2</sup>, AWG: 26 - 12, Width: 5.2 mm, Height: 35.2 mm, Color: gray, Mounting type: NS 35/7,5, NS 35/15

## Product Features

- The push-in connection terminal blocks are characterized by the system features of the CLIPLINE complete system and by easy and tool-free wiring of conductors with ferrules or solid conductors
- The compact design and front connection enable wiring in a confined space
- In addition to the testing facility in the double function shaft, all terminal blocks provide an additional test connection
- Tested for railway applications

## Key commercial data

package_quantity	50
GTIN	4046356333382

## Technical data

### General

Number of levels	1
Number of connections	3
Color	gray
Insulating material	PA
Inflammability class according to UL 94	V0
Area of application	Railway industry
Area of application	Mechanical engineering
Area of application	Plant engineering

### General

Rated surge voltage	6 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 61984
Nominal current I <sub>N</sub>	24 A
Nominal voltage U <sub>N</sub>	500 V
Open side panel	ja
Insertion/withdrawal cycles mechanical	100

# Feed-through terminal block - PT 2,5-TWIN/1P - 3209633

## Technical data

### General

Surge voltage test setpoint	7.3 kV
Result of surge voltage test	Test passed
Power frequency withstand voltage setpoint	3.31 kV
Result of power-frequency withstand voltage test	Test passed
Tight fit on carrier	NS 35
Setpoint	1 N
Result of tight fit test	Test passed
Conductor cross section short circuit testing	2.5 mm <sup>2</sup>
Short-time current	0.3 kA
Conductor cross section short circuit testing	4 mm <sup>2</sup>
Short-time current	0.48 kA
Short circuit stability result	Test passed
Proof of thermal characteristics (needle flame) effective duration	30 s
Result of thermal test	Test passed
Test specification, oscillation, broadband noise	DIN EN 50155 (VDE 0115-200):2008-03
Test spectrum	Service life test category 1, class B, body mounted
Test frequency	f <sub>1</sub> = 5 Hz to f <sub>2</sub> = 150 Hz
ASD level	1.857 (m/s <sup>2</sup> ) <sup>2</sup> /Hz
Acceleration	0.8 g
Test duration per axis	5 h
Test directions	X-, Y- and Z-axis
Oscillation, broadband noise test result	Test passed
Test specification, shock test	DIN EN 50155 (VDE 0115-200):2008-03
Shock form	Half-sine
Acceleration	5 g
Shock duration	30 ms
Number of shocks per direction	3
Test directions	X-, Y- and Z-axis (pos. and neg.)
Shock test result	Test passed
Temperature index, insulating material (DIN EN 60216-1 (VDE 0304-21))	125 °C
Static insulating material application in cold	-60 °C

### Dimensions

Width	5.2 mm
Length	60.5 mm
Height	35.2 mm
Height NS 35/7,5	36.5 mm
Height NS 35/15	44 mm

### Connection data

Conductor cross section solid min.	0.14 mm <sup>2</sup>
------------------------------------	----------------------

# Feed-through terminal block - PT 2,5-TWIN/1P - 3209633

## Technical data

### Connection data

Conductor cross section solid max.	4 mm <sup>2</sup>
Conductor cross section AWG/kcmil min.	26
Conductor cross section AWG/kcmil max	12
Conductor cross section stranded min.	0.14 mm <sup>2</sup>
Conductor cross section stranded max.	2.5 mm <sup>2</sup>
Min. AWG conductor cross section, stranded	26
Max. AWG conductor cross section, stranded	14
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.14 mm <sup>2</sup>
Conductor cross section stranded, with ferrule without plastic sleeve max.	2.5 mm <sup>2</sup>
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.14 mm <sup>2</sup>
Conductor cross section stranded, with ferrule with plastic sleeve max.	2.5 mm <sup>2</sup>
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	0.5 mm <sup>2</sup>
Connection method	Push-in / plug connection
Minimum stripping length	8 mm
Maximum stripping length	10 mm
Internal cylindrical gage	A3

## classifications

### eCl@ss

eCl@ss 4.0	27141121
eCl@ss 4.1	27141121
eCl@ss 5.0	27141120
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27141120

### ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC000897
ETIM 5.0	EC000897

### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410

# Feed-through terminal block - PT 2,5-TWIN/1P - 3209633

## classifications


### UNSPSC


<b>UNSPSC 13.2</b>	39121410
--------------------	----------


## approvals

UL Recognized / cUL Recognized / GOST / LR / GL / RS / ABS / NK / BV / GOST / CSA / cULus Recognized /

### Approval details

<b>UL Recognized</b> 		
Usegroups	B	C
Nominal voltage UN	300 V	300 V
Nominal current IN	20 A	20 A
mm <sup>2</sup> /AWG/kcmil	26-12	26-12

<b>cUL Recognized</b> 		
Usegroups	B	C
Nominal voltage UN	300 V	300 V
Nominal current IN	20 A	20 A
mm <sup>2</sup> /AWG/kcmil	26-12	26-12

<b>GOST</b> 
-------------------------------------------------------------------------------------------------

LR
----

GL
----

RS
----

ABS
-----

NK
----

BV
----


# Feed-through terminal block - PT 2,5-TWIN/1P - 3209633

approvals



CSA

Usegroups	B	C
Nominal voltage UN	300 V	300 V
Nominal current IN	20 A	20 A
mm <sup>2</sup> /AWG/kcmil	26-12	26-12



accessories

## Partition plate

ATP-ST-TWIN - 3030789



---

## End cover

D-ST 2,5-TWIN - 3030488



D-ST 2,5-TWIN-0,8 OG - 3030512



## Feed-through terminal block - PT 2,5-TWIN/1P - 3209633

### accessories

DP PS-5 - 3036725



---

### Screwdriver tools

SZF 1-0,6X3,5 - 1204517



---

### Marker carriers

STP 5-2-ZB - 3037643



GBS-ZB/26X6 - 0809298



---

### Terminal marking

GBS 5-25X12 - 0810588



# Feed-through terminal block - PT 2,5-TWIN/1P - 3209633

## accessories

ZB 5 :UNBEDRUCKT - 1050004



---

UC-TM 5 - 0818108



---

UCT-TM 5 - 0828734



---

ZBF 5:UNBEDRUCKT - 0808642



---

UC-TMF 5 - 0818153



---

UCT-TMF 5 - 0828744



# Feed-through terminal block - PT 2,5-TWIN/1P - 3209633

accessories

---

## Flange

ST 2,5-TWIN/1P-F - 3209840



ST 2,5-TWIN/1P-FS - 3061389



## Documentation

PT-IL - 3208090



## Bridge

FBS 2-5 - 3030161



FBS 3-5 - 3030174





## Feed-through terminal block - PT 2,5-TWIN/1P - 3209633

### accessories

FBS 4-5 - 3030187



FBS 5-5 - 3030190



FBS 10-5 - 3030213



FBS 20-5 - 3030226



FBS 50-5 - 3038930



RB ST (2,5/4)-1,5 - 3038943



## Feed-through terminal block - PT 2,5-TWIN/1P - 3209633

accessories

---

### Mounting rail

NS 35/ 7,5 PERF 2000MM - 0801733



NS 35/ 7,5 UNPERF 2000MM - 0801681



NS 35/ 7,5 WH PERF 2000MM - 1204119



NS 35/ 7,5 WH UNPERF 2000MM - 1204122



NS 35/ 7,5 AL UNPERF 2000MM - 0801704



## Feed-through terminal block - PT 2,5-TWIN/1P - 3209633

### accessories

NS 35/ 7,5 ZN PERF 2000MM - 1206421



NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



NS 35/ 7,5 CU UNPERF 2000MM - 0801762



NS 35/ 7,5 CAP - 1206560



NS 35/15 PERF 2000MM - 1201730



NS 35/15 UNPERF 2000MM - 1201714



## Feed-through terminal block - PT 2,5-TWIN/1P - 3209633

accessories

---

NS 35/15 WH PERF 2000MM - 0806602



NS 35/15 WH UNPERF 2000MM - 1204135



NS 35/15 AL UNPERF 2000MM - 1201756



NS 35/15 ZN PERF 2000MM - 1206599



NS 35/15 ZN UNPERF 2000MM - 1206586



## Feed-through terminal block - PT 2,5-TWIN/1P - 3209633

### accessories

NS 35/15 CU UNPERF 2000MM - 1201895



NS 35/15 CAP - 1206573



NS 35/15-2,3 UNPERF 2000MM - 1201798



### Labeled terminal marker

ZB 5 CUS - 0824962



UC-TM 5 CUS - 0824581



## Feed-through terminal block - PT 2,5-TWIN/1P - 3209633

### accessories

UCT-TM 5 CUS - 0829595



ZBF 5 CUS - 0825025



UC-TMF 5 CUS - 0824638



UCT-TMF 5 CUS - 0829658



### Test plug terminal block

MPS-MT - 0201744



## Feed-through terminal block - PT 2,5-TWIN/1P - 3209633

### accessories

PAI-4-FIX-5/6 BU - 3035975



PAI-4-FIX-5/6 OG - 3035974



PAI-4-FIX-5/6 YE - 3035977



PAI-4-FIX-5/6 RD - 3035976



PAI-4-FIX-5/6 GN - 3035978



PAI-4-FIX-5/6 BK - 3035980



## Feed-through terminal block - PT 2,5-TWIN/1P - 3209633

### accessories

---

PAI-4-FIX-5/6 GY - 3035982



PAI-4-FIX-5/6 VT - 3035979



PAI-4-FIX-5/6 BN - 3035981



PS-5 - 3030983



PS-5/2,3MM RD - 3038723



### Insulating sleeve



# Feed-through terminal block - PT 2,5-TWIN/1P - 3209633

## accessories

MPS-IH WH - 0201663



MPS-IH RD - 0201676



MPS-IH BU - 0201689



MPS-IH YE - 0201692



MPS-IH GN - 0201702



MPS-IH GY - 0201728



## Feed-through terminal block - PT 2,5-TWIN/1P - 3209633

accessories

---

MPS-IH BK - 0201731



ISH 2,5/0,2 - 3002843



ISH 2,5/0,5 - 3002856



ISH 2,5/1,0 - 3002869



### Planning and marking software

CLIP-PROJECT ADVANCED - 5146040



# Feed-through terminal block - PT 2,5-TWIN/1P - 3209633

accessories

CLIP-PROJECT PROFESSIONAL - 5146053



---

## End block

CLIPFIX 35 - 3022218



---

CLIPFIX 35-5 - 3022276



---

E/NS 35 N - 0800886




---

## Drawings

## Feed-through terminal block - PT 2,5-TWIN/1P - 3209633

Circuit diagram



© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>