

# Cable marker label - WML 7,5 (25X13)R - 0800075

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Cable marker label, Roll, white, Unlabeled, Can be labeled with: THERMOMARK ROLL, THERMOMARK X, THERMOMARK S1.1, Mounting type: Adhesive, Cable diameter: ≤7.5 mm, Lettering field: 25 x 13 mm

The figure shows the WML 5 (25x10)R version

## Product Features

- High-quality labeling image created by thermal transfer printing
- The cable marker labels do not increase the cross section of the cable, allowing the cable to be subsequently drawn through cable ducts, for example
- Quick and easy handling
- Resistant to solvents
- The protective foil is wound over the labeling and provides permanent protection against dirt and abrasion
- The cable marker labels consist of a labeling field and a transparent protective foil

## Key commercial data

<b>package_quantity</b>	1
<b>GTIN</b>	4046356562089

## Technical data

### Dimensions

<b>Length (b)</b>	36.5 mm
<b>Width (a)</b>	25.4 mm

### Ambient conditions

<b>Wipe resistance</b>	DIN EN 61010-1 (VDE 0411-1)
<b>Ambient temperature (operation)</b>	-50 °C ... 110 °C
<b>Recommended storage conditions</b>	23 °C / 50% relative humidity. Storage in poly bags is recommended prior to processing.

### General

<b>Color</b>	white
<b>Base element material</b>	Vinyl film
<b>Components</b>	Silicone-free
<b>Material</b>	PVC
<b>Number of individual labels</b>	2100
<b>Number of individual labels per row</b>	3
<b>Adhesive</b>	Acrylic

## Cable marker label - WML 7,5 (25X13)R - 0800075

### Technical data

#### General

<b>Printability</b>	Thermal transfer
<b>Test for substances that would hinder coating with paint or varnish</b>	VW PV 3.10.7:2005-02
<b>Result</b>	Test passed
<b>Test specification weathering-resistance</b>	Following ISO 4892-2:2013-03
<b>Test duration</b>	96 h
<b>Wipe resistance test result</b>	Test passed
<b>Salt spray test specification</b>	DIN EN 60068-2-11:2000-02
<b>Test duration</b>	96 h
<b>Salt spray testing result</b>	Test passed
<b>Alternating condensation climate with SO2 test specification</b>	DIN 50018:1997-06
<b>Climate level</b>	KFW 1.0 S
<b>Cycles</b>	2
<b>Condensation test result</b>	Test passed
<b>Wipe resistance of test specification inscriptions</b>	DIN EN 61010-1 (VDE 0411-1):2011-07
<b>Result</b>	Test passed
<b>Foil strength</b>	50 µm
<b>Adhesive strength</b>	25 µm

### classifications

#### eCl@ss

<b>eCl@ss 4.0</b>	24190219
<b>eCl@ss 4.1</b>	24190219
<b>eCl@ss 5.0</b>	27400401
<b>eCl@ss 5.1</b>	27400401
<b>eCl@ss 6.0</b>	27400401
<b>eCl@ss 7.0</b>	27400401
<b>eCl@ss 8.0</b>	27400401

#### ETIM

<b>ETIM 2.0</b>	EC000761
<b>ETIM 3.0</b>	EC000761
<b>ETIM 4.0</b>	EC001530
<b>ETIM 5.0</b>	EC001530

#### UNSPSC

<b>UNSPSC 6.01</b>	30211811
<b>UNSPSC 7.0901</b>	39121410
<b>UNSPSC 11</b>	39121410
<b>UNSPSC 12.01</b>	39121410
<b>UNSPSC 13.2</b>	39121410

## Cable marker label - WML 7,5 (25X13)R - 0800075

accessories

**Ink ribbon**

THERMOMARK-RIBBON 110 - 5145384



---

### Drawings

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>