



## Data sheet Polytronik® Toroidal transformer

Part no.:	<b>RSO 825025</b>
Description:	RKT 100VA/ 230V/ 2x9.0V 2x5.56A
Safety isolating transformer according to:	EN 61558-2-6 / VDE 0570
Power [VA]:	100
Input voltage [AC]:	230 V +-10%
Output voltage [AC]:	2 x 9.00 V
Output current [AC]:	2 x 5.56 A
Frequency [Hz]:	50/60
Dielectric strength PRI - SEC [AC]:	4400 V
Efficiency [%]:	87
Power loss at no-load [W]:	1.11
Maximum ambient temperature $t_a$ [°C]:	60
Temperature class:	B (130°C)
Temperature switch:	120°C (automatically resetting)



### Schematic:



possible interconnections: parallel connection **9.0V / 11.11A** = connect black with violet and red with white  
 series connection **18.0V / 5.56A** = connect red with violet

Approval marks: CE; ENEC; UL508 (E182061)

Connections: primary and secondary strands 200mm long, ends assembled with ferrules

Model: toroidal transformer potted on mounting disc with through-hole 6.3 mm

Appliance class: prepared for class II

Protection class: IP 00

Recommended fuse ratings:	primary	0.800 AT (IEC60127-2-5)
	secondary 1	6.30 AT (IEC60127-2-3)
	secondary 2	6.30 AT (IEC60127-2-3)

Dimensions:	diameter approx. =	90 mm
	height approx. =	55 mm

Weight: approx. 1.27 kg