

EDWANZ group

Data sheet Polytronik[®] Toroidal transformer

Part no.:	RSO 825027	10 MA
Description:	RKT 100VA/ 230V/ 2x15.0V 2x3.34A	A chi think
Safety isolating transformer according to:	EN 61558-2-6 / VDE 0570	
Power [VA]:	100	
Input voltage [AC]:	230 V +-10%	
Output voltage [AC]:	2 x 15.00 V	
Output current [AC]:	2 x 3.34 A	the second second
Frequency [Hz]:	50/60	
Dielectric strength PRI - SEC [AC]:	4400 V	
Efficiency [%]:	87	
Power loss at no-load [W]:	1.11	
Maximum ambient temperature ta [°C]:	60	construction only
Temperature class:	B (130°C)	
Temperature switch:	120°C (automatically resetting)	

Schematic:

temperature s				
0 V blue5	▶ • ■ SEC 1	— black	0 V	
		— red	15.0 V / 3.34 A	U0= 16.88 V
PRI	•	— violet	0 V	
230 V brown	SEC 2	— white	15.0 V / 3.34 A	U0= 16,88 V
possible connection:	parallel connection 15.0V / 6.68 series connection 30.0V / 3.34			red with <u>white</u>
Approval marks:	CE; ENEC; UL508 (E182061)			
Connections:	primary and secondary strands 200mm long, ends assembled with ferrules			
Model:	toroidal transformer pottet on mounting disc with through-hole 6.3 mm			
Appliance class:	prepared for class II			
Protection class:	IP 00			
Recommended fuse ratings:	primary	0.800 AT	(IEC60127-2-5)	
	secondary 1		(IEC60127-2-3)	
	secondary 2	4.00 AT	(IEC60127-2-3)	
Dimensions:	diameter approx. =	90 mm		
	height approx. =	55 mm		
Weight:	approx. 1.27 kg			