

Conductor marking collar - UCT-WMS 3,2 (12X4) YE - 0828572

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Conductor marking collar, Sheet, yellow, Unlabeled, Can be labeled with: THERMOMARK CARD PLUS, THERMOMARK CARD, BLUEMARK CLED, BLUEMARK LED, Mounting type: Slide on, For terminal block width: 5.2 mm, Cable diameter: 1.5-3.2 mm, Lettering field: 12 x 4 mm

Product Features

- ✓ The UCT-WMS ... UniCard labeling range includes markers that can be threaded onto conductors
- ✓ The markers, which are supplied in uniform sheets, can be labeled quickly and easily using the THERMOMARK CARD and the BLUEMARK LED
- ✓ The sheets provide space for including function texts
- ✓ The markers support multi-line labeling
- ✓ The format automatically ensures printing with a high degree of positioning accuracy

Key commercial data

package_quantity	8
GTIN	4046356519687

Technical data

Dimensions

Length (b)	12 mm
Height	5.8 mm
Width (a)	4.3 mm

Ambient conditions

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Ambient temperature (operation)	-40 °C ... 120 °C

General

Note	Can be labeled via thermal transfer
Color	yellow
Components	free from silicone and halogen
Inflammability class according to UL 94	V0
Material	PC V0
Number of individual labels	55
Number of individual labels per row	11
RoHS compliant	Yes
Printability	Thermal transfer
Printability	Inkjet printing

Conductor marking collar - UCT-WMS 3,2 (12X4) YE - 0828572

Technical data

General

Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	DIN 50018:1997-06
Climate level	KFW 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result	Test passed

classifications

eCl@ss

eCl@ss 4.0	24190208
eCl@ss 4.1	24190208
eCl@ss 5.0	27149103
eCl@ss 5.1	27400401
eCl@ss 6.0	27400401
eCl@ss 7.0	27400401
eCl@ss 8.0	27400401

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC001530
ETIM 5.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

accessories

Magazine

Conductor marking collar - UCT-WMS 3,2 (12X4) YE - 0828572

accessories

THERMOMARK CARD-UCT-MAG3 - 5146613



P1 UC-MAG 7 - 5146568



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>