

FI/LS-PROTECTOR TYPE A (PSE/SSF), D=70MM IFN
30MA,6KA, 1+N-POLEE B 10A



Figure similar

Model		
product brand name		SENTRON
Product designation		RCBO
Design of the product		Instantaneous
version		RCCB/MCB

General technical data		
Number of poles		2
Number of poles / Note		1P+N
Number of poles / with protection		1
Tripping characteristic class		B
circuit-breaker / Design		5SU1
Mechanical service life (switching cycles) / typical		10 000
Overvoltage category		III

Voltage		
Surge current resistance / at (8/20) μ s	kA	1

Supply voltage		
Supply voltage		
<ul style="list-style-type: none"> at AC / Rated value 	V	230

<ul style="list-style-type: none"> • for testing equipment / minimum 	V	195
Supply voltage frequency / Rated value	Hz	50
Protection class		
Protection class IP		IP20, if the distribution board is installed, with connected conductors
Energy limiting class		3
Switching capacity		
Switching capacity current		
<ul style="list-style-type: none"> • acc. to EN 60898 / Rated value 	kA	6
<ul style="list-style-type: none"> • acc. to IEC 60947-2 / Rated value 	kA	10
Dissipation		
Active power loss		
<ul style="list-style-type: none"> • for rated value of the current / at AC / in hot operating state / per pole 	W	1.8
Electricity		
Tripping residual current / Rated value	mA	30
rated current I _n / IEC, DIN/VDE / at 40 Cel	A	9.5
Type of fault current		A
Current / at AC / Rated value	A	10
Product details		
Product feature / Touch protection		Yes
Product property		
<ul style="list-style-type: none"> • halogen-free 		Yes
<ul style="list-style-type: none"> • silicon-free 		Yes
Product function		
Product function / neutral conductor switching		Yes
Number		
Number of test cycles / for environmental testing / acc. to IEC 60068-2-30		26
Connections		
Connectable conductor cross-section / stranded		
<ul style="list-style-type: none"> • minimum 	mm ²	0.75
<ul style="list-style-type: none"> • maximum 	mm ²	35
Connectable conductor cross-section		
<ul style="list-style-type: none"> • solid 		
<ul style="list-style-type: none"> — minimum 	mm ²	0.75
<ul style="list-style-type: none"> — maximum 	mm ²	35
<ul style="list-style-type: none"> • finely stranded / with core end processing 		
<ul style="list-style-type: none"> — minimum 	mm ²	0.75
<ul style="list-style-type: none"> — maximum 	mm ²	25

Tightening torque / with screw-type terminals	• minimum	N·m	2.5
	• maximum	N·m	3
Position / of power supply cord			Either top or bottom

Mechanical Design

Height	mm	90
Width	mm	36
Depth	mm	77
mounting position		any
Installation depth	mm	70
Number of width units		2
Net weight	g	265

Environmental conditions

Influence of the surrounding temperature		Max. 95% humidity
Ambient temperature		
• minimum	°C	-25
• maximum	°C	55
• during storage / minimum	°C	-40
• during storage / maximum	°C	75

Certificates

Equipment marking		
• acc. to DIN EN 61346-2		F
• acc. to DIN EN 81346-2		F

General Product Approval



CCC



IMQ



ÖVE



VDE

[sonstig](#)



Declaration of
Conformity

other



EG-Konf.

[Umweltbestätigung](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/5SU13566KK10>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/5SU13566KK10/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SU13566KK10

CAX-Online-Generator


<http://www.siemens.com/cax>

Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>



last modified:



13.08.2015