

**UNITRONIC® LAN 500 S/FTP Cat. 6_A Y
4x2xAWG 23/1****DB2170143**
valid from: 14.02.2012**Application**

Data cable for transmission of digital and analog signals up to 500 MHz. The cable is designed for horizontal cabling systems as connection between a floor distribution and the telecommunication outlets (TO's). According to TIA/EIA-568, ISO/IEC 11801 2nd edition, EN 50173, EN 50288-4-1, IEC 61156-5. For application in LANs like IEEE 802.3: 10Base-T, 100Base-T, 1000Base-T, 10GBase-T; FDDI; ISDN; ATM; Cable sharing.

Design

Conductor	bare copper AWG 23/1, massive
Insulation	Skin-Foam-Skin PE, ca. 1.37 mm outer Ø
Core identification code	acc. to IEC 708-1
Pair screening	plastic laminated aluminium foil
Stranding	4 pairs, stranded to bundle
Screening	braid of copper wire, tinned wire 0,10 mm
Outer sheath	PVC, light ivory similar to RAL 1015, outer Ø: ca. 7.4 mm

Electrical properties at 20° C

Resistance (loop)	max. 150 Ω/km, acc. to VDE 0812
Insulation resistance	min. 5 GΩxkm
Mutual capacitance	nom. 45 nF/km
Characteristic impedance	100 Ω ±5 Ω (at 100 MHz)
Velocity of propagation	ca. 0.79 c
Signal propagation time	<425 ns/100m
Delay difference	<5 ns/100m
Screening attenuation	>75 dB (up to 600 MHz)
Test voltage	700 V (AC)

UNITRONIC® LAN 500 S/FTP Cat. 6A Y
4x2xAWG 23/1DB2170143
valid from: 14.02.2012

Transmission properties

f [MHz]	Attenuation nom. [dB/100m]	NEXT nom. [dB]	ACR nom. [dB/100m]	ELFEXT nom. [dB/100m]	RL nom. [dB]
1	1.8	105	103	95	25
4	3.3	105	103	93	28
10	5.3	105	100	92	30
16	6.7	105	98	91	32
20	7.5	105	97	90	34
31,25	9.6	105	95	86	35
62,5	13.8	103	89	82	34
100	17.3	100	83	77	33
155	22.6	98	75	73	30
200	24.8	95	70	70	29
300	30.7	93	62	67	27
400	35.8	90	54	64	26
500	39.7	87	47	62	24
600	44.2	85	41	60	23

Mechanical and thermal properties

Minimum bending radius	during installation: 8 x cable Ø static: 4 x cable Ø
Permissible temperature range	during installation: 0° C up to +50° C static: -20° C up to +60° C
Flame propagation	flame retardant acc. to IEC 60332-1-2
General requirements	Dangerous and forbidden substances acc. to RoHS directive (2002/95/EG) are not allowed to the manufacturing.